

VERONICA-SQ-O

~55° + 12° oval beam


TECHNICAL SPECIFICATIONS:

Dimensions	Ø 22.5 mm
Height	12.2 mm
Fastening	tape, pin
Colour	clear
Box size	480 x 280 x 300 mm
Box weight	8.2 kg
Quantity in Box	1980 pcs
ROHS compliant	yes ⓘ



MATERIAL SPECIFICATIONS:


Component	Type	Material	Colour
VERONICA-SQ-O	Single lens	PMMA	clear
VERONICA-TAPE	Tape	PU tape	clear



PHOTOMETRIC DATA (MEASURED):



CREE

LED XB-H
 FWHM 45.0 + 16.0°
 Efficiency 77 %
 Peak intensity 2.700 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




CREE

LED XD16
 FWHM 47.0 + 17.0°
 Efficiency 87 %
 Peak intensity 2.200 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



CREE

LED XHP35 HD
 FWHM 45.0 + 20.0°
 Efficiency 73 %
 Peak intensity 2.130 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



CREE


LED XHP35 HI
 FWHM 46.0 + 16.0°
 Efficiency 75 %
 Peak intensity 2.700 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



CREE 

LED XM-L
 FWHM 47.0 + 20.0°
 Efficiency 80 %
 Peak intensity 2.300 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





CREE 

LED XM-L2
 FWHM 47.0 + 20.0°
 Efficiency 80 %
 Peak intensity 2.300 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




CREE 

LED XP-E2
 FWHM 46.0 + 12.0°
 Efficiency 80 %
 Peak intensity 3.500 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



CREE 



LED XP-G2
 FWHM 47.0 + 14.0°
 Efficiency 80 %
 Peak intensity 2.940 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (MEASURED):





LED XP-L2
 FWHM 45.0 + 20.0°
 Efficiency 86 %
 Peak intensity 1.900 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED XT-E
 FWHM 47.0 + 16.0°
 Efficiency 79 %
 Peak intensity 2.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED LUXEON M/MX
 FWHM 45.0 + 28.0°
 Efficiency 76 %
 Peak intensity 1.600 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED LUXEON MZ
 FWHM 47.0 + 23.0°
 Efficiency 73 %
 Peak intensity 2.000 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



LUMILEDS

LED LUXEON Rebel
 FWHM 47.0 + 15.0°
 Efficiency 80 %
 Peak intensity 3.000 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LUMILEDS

LED LUXEON Rebel ES
 FWHM 47.0 + 17.0°
 Efficiency 80 %
 Peak intensity 2.700 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LUMILEDS

LED LUXEON T
 FWHM 47.0 + 17.0°
 Efficiency 80 %
 Peak intensity 2.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LUMILEDS


LED LUXEON TX
 FWHM 46.0 + 16.0°
 Efficiency 77 %
 Peak intensity 2.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (MEASURED):



LUMILEDS

LED LUXEON V
 FWHM 46.0 + 21.0°
 Efficiency 88 %
 Peak intensity 1.900 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LUMILEDS

LED LUXEON V2
 FWHM 47.0 + 17.0°
 Efficiency 87 %
 Peak intensity 2.300 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





NICHIA

LED NVSW219F
 FWHM 48.0 + 16.0°
 Efficiency 88 %
 Peak intensity 2.400 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



NICHIA



LED NVSxx19B/NVSxx19C
 FWHM 47.0 + 18.0°
 Efficiency 80 %
 Peak intensity 2.600 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHOTOMETRIC DATA (MEASURED):





LED NWSx229A
 FWHM 20.0 + 45.0°
 Efficiency 74 %
 Peak intensity 2.000 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED OSLOM Square EC
 FWHM 47.0 + 17.0°
 Efficiency 79 %
 Peak intensity 2.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED LH181A
 FWHM 46.0 + 22.0°
 Efficiency 85 %
 Peak intensity 1.700 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED LH181B
 FWHM 46.0 + 21.0°
 Efficiency 88 %
 Peak intensity 2.000 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





PHOTOMETRIC DATA (MEASURED):

SAMSUNG



LED LH351Z
 FWHM 47.0 + 15.0°
 Efficiency 78 %
 Peak intensity 2.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





SEOUL SEMICONDUCTOR
 LED MJT 5050
 FWHM 45.0 + 28.0°
 Efficiency 87 %
 Peak intensity 1.600 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



SEOUL SEMICONDUCTOR
 LED Z5M3
 FWHM 47.0 + 18.0°
 Efficiency 89 %
 Peak intensity 2.200 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



SEOUL SEMICONDUCTOR
 LED Z8Y22P
 FWHM 45.0 + 18.0°
 Efficiency 86 %
 Peak intensity 2.200 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




PHOTOMETRIC DATA (MEASURED):




PHOTOMETRIC DATA (SIMULATED):




LED XP-G2 HE
 FWHM 54.0 + 14.0°
 Efficiency 92 %
 Peak intensity 2.821 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED XP-L HD
 FWHM 53.0 + 16.0°
 Efficiency 86 %
 Peak intensity 2.500 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED NV4WB35AM
 FWHM 50.0 + 18.0°
 Efficiency 88 %
 Peak intensity 2.526 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED OSCONIQ P 3030
 FWHM 56.0 + 12.0°
 Efficiency 88 %
 Peak intensity 3.356 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



PHOTOMETRIC DATA (SIMULATED):


OSRAM
Opto Semiconductors

LED OSCONIQ P 7070
 FWHM 49.0 + 25.0°
 Efficiency 84 %
 Peak intensity 1.800 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



OSRAM
Opto Semiconductors


LED OSOLON Square CSSRM2/CSSRM3
 FWHM 56.0 + 12.0°
 Efficiency 88 %
 Peak intensity 3.500 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



SEOL

SEOUL SEMICONDUCTOR

LED Z8Y22T
 FWHM 54.0 + 16.0°
 Efficiency 89 %
 Peak intensity 2.600 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)