

You can view this page in:

EN DE SV FI CS DA EL ES FR HU IT JA KO NL NO PL PT RU SK  
TR ZH

# Detailed information for: 260-1550

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

# 260-1550

## General Information

<b>Extended Product Type:</b>	260-1550
<b>Product ID:</b>	7TCA296230R0071
<b>EAN:</b>	5016947002446
<b>Catalog Description:</b>	INDEX EMC M25 CONT CBL G 14-18MM
<b>Long Description:</b>	Cable Gland, Continuous Cable Sheath Allowing for a Ring of Outer Sheath Only to Be Stripped, M25 Thread, 11mm Thread Length, 33.5mm Gland Diameter, 30mm Across Flats Diameter, 14-18mm Cable Diameter Range, Nickel Plated Brass, Stainless Steel Spring, Rubber Seal, IP68

## Categories

Products » [Low Voltage Products and Systems](#) » [Installation Products](#) » [Cable Protection, Explosion Proof and Lighting](#) » [Flexible Cable Protection Systems](#)

## Additional Information

<b>Application:</b>	Provide Strain Relief and Connection for Conduit Systems
<b>Product Type:</b>	Index EMC Type A Cable Gland

## Ordering

<b>EAN:</b>	5016947002446
<b>UPC:</b>	786210271590
<b>Customs Tariff Number:</b>	8547200000

## Technical

<b>Number of Batteries:</b>	0
<b>Color:</b>	Brass
<b>Material:</b>	Nickel Plated Brass, Stainless Steel Spring, Rubber Seal (TPE-V)
<b>Size:</b>	M25

## Environmental

<b>WEEE Category:</b>	Product Not in WEEE Scope
-----------------------	---------------------------

## Container Information

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Height:</b>	1 in 25 mm
<b>Package Level 1 Depth / Length:</b>	1 in 25 mm
<b>Package Level 1 Width:</b>	1 in 25 mm

## Certificates and Declarations (Document Number)

**Data Sheet, Technical Information:** [260-1550](#)

---

**Instructions and Manuals:** [260-1550](#)

---

**Declaration of Conformity - CE:** [9AKK107492A9618](#)

---

**RoHS Information:** [9AKK107992A8994](#)

---

**REACH Declaration:** [9AKK107992A8994](#)

---

## Classifications

**UNSPSC:** 39121431



---

© Copyright 2022 ABB