



PEG124, Aluminum Electrolytic, 33 uF, -10/+30%, 400 VDC, -40/+105°C



Dimensions	
D	20mm +/-0.5mm
L	37mm +/-1mm
L1	43mm MIN
LL Negative	42mm +3/-2mm
LL Positive	42mm +3/-2mm
F	0.8mm +/-0.03mm

Packaging Specifications	
Weight:	20 g
Packaging:	Bulk, Bag
Packaging Quantity:	125

General Information	
Supplier:	KEMET
Series:	PEG124
Dielectric:	Aluminum Electrolytic
Style:	Axial
Description:	Long Life Axial Aluminum Electrolytic
Features:	Long Life
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Miscellaneous:	Life Calculation Based On Maximum Ripple Current, Please Contact KEMET For More Information
Notes:	L1 is KEMETs recommendation for minimum distance between symmetrical Lead bend. Available only for Customer specific part numbers. Lead bend dimensions must be specified and confirmed per article.
Shelf Life:	156 Weeks

Specifications	
Capacitance:	33 uF
Capacitance Tolerance:	-10/+30%
Voltage DC:	400 VDC
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	22000 Hrs
Resistance:	1600 mOhms (100Hz 20C), 760 mOhms (100kHz 20C)
Ripple Current:	0.304 Amps (100Hz 125C), 1.9 Amps (5kHz 60C), 0.71 Amps (5kHz 125C)
Leakage Current:	40 uA (5min 20°C)
Inductance:	15 nH (ESL)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.