

9037EG8

closed tank - NEMA 1 - flange mounted - 2 NC
DPST-DB contacts

Product availability : Stock - Normally stocked in distribution facility



Price** : 177.00 USD



Main

| | |
|------------------------------|----------------------|
| Range of product | Square D Pumptrol |
| Product or component type | Float switch |
| Device application | Closed tank |
| Device short name | 9037E |
| Product specific application | Liquid level control |
| Electrical circuit type | Power circuit |
| Quantity per set | Set of 1 |
| Type of packing | Individual |

Complementary

| | |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product destination | For closed tank |
| Device mounting | Flange |
| Cable entry number | 3 knock-outs for 1/2" conduit UL 508 |
| Contacts type and composition | 2 NC, snap action, DPST-DB, Form YY |
| Controlled fluid | Fresh water specific gravity of 0.85 in or higher -18...104 °C (0...220 °F) Sea water specific gravity of 0.85 in or higher -18...104 °C (0...220 °F) Hydraulic oil specific gravity of 0.85 in or higher -18...104 °C (0...220 °F) Corrosive fluid specific gravity of 0.85 in or higher -18...104 °C (0...220 °F) |
| Motor power kW | 1.5 kW 2 hp)115 V AC, 1 phase 2.2 kW 3 hp)115 V AC, 3 phase 2.2 kW 3 hp)230 V AC, 1 phase 3.7 kW 5 hp)230 V AC, 3 phase 0.75 kW 1 hp)460 V AC, 3 phase 0.75 kW 1 hp)475 V AC, 3 phase 0.18 kW 0.25 hp)32 V DC 0.37 kW 0.5 hp)115 V DC 0.37 kW 0.5 hp)230 V DC |
| Electrical connection | Screw-clamp terminals 10 AWG |
| Contact operation | Contacts close on liquid rise |

| | |
|---------------------------------|-----------------------------------------------------------------------------------------------------|
| Float movement | Variable fixed |
| Float position | Any |
| Float rod angle | Horizontal |
| Short-circuit protection | 20 A cartridge fuse gG |
| Local signalling | Without |
| Materials in contact with fluid | Nitrile (Buna-N) or equivalent rubber 316 stainless steel 304 stainless steel Yellow brass |
| Enclosure material | Polypropylene or equivalent |
| Operating position | Vertical or horizontal position |
| Electrical durability | 100 cycles 60 cyc/mn |
| Mechanical durability | 300 cycles |
| Terminal block type | 4 terminals |
| Maximum operating rate | 60 cyc/mn |
| [Ui] rated insulation voltage | 575 V UL 508 |
| Net Weight | 4.42 lb(US) (2.00 kg) |
| Terminals description ISO n°1 | Line-load-load-line |
| Factory modification | Without |
| Kit composition | Float switch Rod and float are to be chosen in accessories |

Environment

| | |
|---------------------------------------|-------------------------------------------|
| Standards | UL 508 CE |
| Ambient air temperature for operation | -22...220 °F (-30...104 °C) |
| Ambient air temperature for storage | -22...220 °F (-30...104 °C) |
| NEMA degree of protection | NEMA 1 UL 50 |
| Product certifications | UL listed file E12158 CSA file LR25490 |

Ordering and shipping details

| | |
|---------------------|---------------------------------------------|
| Category | 21601 - 9037,9038 COMMERCIAL FLOAT SWITCHES |
| Discount Schedule | CP7G |
| GTIN | 00785901485438 |
| Package weight(Lbs) | 4.42 lb(US) (2.00 kg) |
| Returnability | Yes |
| Country of origin | MX |

Offer Sustainability

| | |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|