## Assembly

## Features

- 2-channel
- AC version
- Working voltage 10 V at 10 μA
- Series resistance max. 82  $\Omega$
- Fuse rating 100 mA
- · DIN rail mounting
- · High power version


## Function

The Zener Barrier prevents the transfer of unacceptably high energy from the safe area into the hazardous area.

The zener diodes in the Zener Barrier are connected in the reverse direction. The breakdown voltage of the diodes is not exceeded in normal operation. If this voltage is exceeded, due to a fault in the safe area, the diodes start to conduct, causing the fuse to blow. The Zener Barrier has alternating polarities, i. e. interconnected zener diodes are employed and one side is grounded. The Zener Barrier can be used for both alternating voltage signals and direct voltage signals.


This high power version has a smaller serial resistance and therefore provides higher voltage to the field device.

Depending on the application, increased or decreased intrinsic safety parameters apply for serial or parallel connection. For the detailed parameters refer to the Zener Barrier certificate. Application examples can be found in the system description of the Zener Barriers.





## Connection



Pepperl+Fuchs Group US www.pepperl-fuchs.com pa-info

USA: +1 330 486 0002 pa-info@us.pepperl-fuchs.com Germany: +49 621 776 2222 pa-info@de.pepperl-fuchs.com

22 Singapore: +65 6779 9091 om pa-info@sg.pepperl-fuchs.com



General specifications Type Electrical specifications		
		AC version
Electrical specifications		
Nominal resistance		75 Ω
Series resistance		75Ω max. 82 Ω
Fuse rating		100 mA
Ũ		100 mA
Hazardous area connection		terminale 1.0:0.4
Connection Safe area connection		terminals 1, 2; 3, 4
		terminale F_0; 7_0
Connection		terminals 5, 6; 7, 8
Working voltage		max. 11.1 V,10 V at 10 μA
Conformity		
Protection degree		IEC 60529
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-25 70 °C (-13 158 °F)
Relative humidity		max. 75 %, without moisture condensation
Mechanical specifications		
Protection degree		IP20
Connection		self-opening connection terminals, max. core cross-section 2 x 2.5 mm <sup>2</sup>
Mass		approx. 150 g
Dimensions		12.5 x 115 x 110 mm (0.5 x 4.5 x 4.3 in)
Construction type		modular terminal housing, see system description
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection with Ex-areas		
EC-Type Examination Certificate		BAS 01 ATEX 7005 , for additional certificates see www.pepperl-fuchs.com
Group, category, type of protection		$\langle x \rangle$ II (1)GD, I (M1) [Ex ia Ga] IIC, [Ex ia Da] IIIC, [Ex ia Ma] I (-20 °C $\leq T_{amb} \leq 60$ °C) [circuit(s) in zone 0/1/2]
Voltage	Uo	12 V
Current	I <sub>o</sub>	164 mA
Power	Po	490 mW
Supply		
Maximum safe voltage	U <sub>m</sub>	250 V
Series resistance		min. 73.5 Ω
Statement of conformity		TÜV 99 ATEX 1484 X , observe statement of conformity
Group, category, type of protection, temperature class		(x) II 3G Ex nA IIC T4 Gc [device in zone 2]
Directive conformity		
Directive 94/9/EC		EN 60079-0:2009, EN 60079-11:2007, EN 61241-11:2006 , EN 60079-15:2010
International approvals		
FM approval		
Control drawing		116-0118
UL approval		
Control drawing		116-0139
CSA approval		
Control drawing		116-0119
IECEx approval		IECEx BAS 09.0142
Approved for		[Ex ia Ga] IIC, [Ex ia Da] IIIC, [Ex ia Ma] I
General information		נבא וע סען ווס, נבא וע סען ווס, נבא וע וווען ו
Supplementary information		EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-

USA: +1 330 486 0002 pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222 pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 pa-info@sg.pepperl-fuchs.com

