THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WIRTTEN CONSENT OF CAL TEST ELECTRONICS, INC.

NOTES:

1. MATERIAL:

TUBE BODY: CERAMIC (NON-TRANSPARENT) CAP: BRASS, NICKEL PLATED ELEMENT: METAL WIRE FILLER: QUARTZ SAND

2. SPECIFICATIONS:

RATED VOLTAGE: 1,000 V AC / DC

RATED CURRENT: SEE PART NUMBER TABLE

FUSING TIME LIMIT: 4 In: 60 ms MAX. 10 In: 6 ms MAX.

BREAKING CAPACITY: 50 kA MIN.

OPERATING TEMPERATURE: -55°C TO +125°C

3. UL AND / OR TUV RECOGNIZED

4. RoHS 2 COMPLIANT; EXEMPTION ANNIX III 6(c)


5. WEIGHT:

INDIVIDUAL: 1.2 g/pc



ISOMETRIC VIEW

REVISIONS				
REV.	DESCRIPTION	DATE	APPROVED	
-	CLASS A RELEASED	3/14/18		
Α	REVISED NOTE 2. BREAKING CAPACITY WAS 10 KA MIN. CONVERTED TO SW FORMAT	1/17/2019		
В	ADDED 2.0 A FUSE TO MODEL NUMBER TABLE	7/18/2019		



CT4049-2.0A	2.0 A	-		
CT4049-1.5A	1.5 A	-		
CT4049-1.0A	1.0 A	-		
CT4049-0.5A	0.5 A	-		
MODEL NUMBER	CURRENT RATING	NOTES / REFERENCE		
MODEL NUMBER TABLE				

METRIC

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: PER DIN ISO 2768m


FINISH NONE C306

PROJECT NO.

Cal Test Electronics

22820 Savi Ranch Parkway Yorba Linda, CA 92887

THIRD ANGLE PROJECTION



FUSE, MINATURE, CERAMIC, 6X32, 1000 V, VERY FAST-ACTING

SIZE CAGE CODE DWG. NO. P404900

SCALE

1:1

SHEET 1 OF 1

REV.