



Order-No.	Shell Size / for No. of Contacts	B	C	D	E	∅F1 min - max	max I Rubber bushing	∅F2	H	U	V	W
FMK1G-09P-5847	1 / 9	25	31.6	39.5	15.2	3 - 9.5	6.5	FKT1-2	42	±0.4	±0.15	±0.2
FMK2G-15P-5847	2 / 15	33.3	40	41	15.2	3 - 8.5	6.5	FKT1-2	43.5	39.1	33.3	25.2
FMK3G-25P-5847	3 / 25	47.04	53.7	45	15.2	3 - 8.5	8	FKT1-2A	47.5	53	47.04	38.9
FMK4G-37P-5847	4 / 37	63.5	70.2	48	18.2	3 - 12	9	FKT3-4	50.5	69.3	63.5	55.3

FMKYG-xxP-5847



e.g. FMK3G-25P-5847

*1) Y for hood size 1, 2, 3 or 4

*2) xx No. of contacts 09, 15, 25 or 37




No.	St.	Type Description / Material	Type	Plating
9	1	Rubber bushing	TPE	black
8	2	Knurled thumb screw	FRS1/5-K190 4-40 / Brass	nickel plated
7	0/2	Cable reduction plate	Zinc die-cast	nickel plated
6	1	Strain relief	ABS	nickel plated
5	1	Cable clamp	Steel	tin plated
4	4	Screw	Case hardened steel	zinc plated
3	2	Catch spring	PEI	black
2	1	Hood	FMKYG / Zinc die-cast	nickel plated
1	1	D-Sub Connector	FxxP0G1	Surface plating / Colour / Class




RoHS compliant

Packing unit on supplement AM0409

max. torque are 40 Ncm
Part-No. 9 not mounted
FMK1G-09P-5847 without Part-No. 7



TITLE Hood Connector Set	
SCALE 2:1	ORIGINAL/DWG NO. / REVISION / DATE / CH-NO. / DRAWN / CHECKED / DATE / NAME / DATE / ISO 2768-m
DRAWN / 10/02/2016 / BWH/tek	
CHECKED / 12/02/2016	
	
DWG. NO. FMKYG-xxP-5847	REV. 1
ORIGINAL/DWG NO. / REVISION / DATE / CH-NO. / DRAWN / CHECKED / DATE / NAME / DATE / ISO 2768-m	PAGES 1

COMMENT: IF ANY NEITHER BE PUBLISHED NOR MADE AVAILABLE TO A THIRD PARTY. AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.