

## Han F+B Hybrid Female



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 512 3101
Specification	Han F+B Hybrid Female
HARTING eCatalogue	<a href="https://b2b.harting.com/09155123101">https://b2b.harting.com/09155123101</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> F+B

### Version

Termination method	Crimp termination
Gender	Female
Number of contacts	4
Additional contacts	+ 4 additional signal contacts + 1 Data
PE contact	Yes
Details	Please order crimp contacts separately. 4x Han E <sup>®</sup> 4x Han D <sup>®</sup> 4x M12 for data element

### Technical characteristics

Conductor cross-section	0.14 ... 4 mm <sup>2</sup>
Rated current	20 A
Rated voltage	400 V
Rated impulse voltage	6 kV
Pollution degree	3
Rated current (signal)	10 A
Rated voltage (signal)	250 V
Rated impulse voltage (signal)	4 kV



Pushing Performance

## Technical characteristics

Pollution degree (signal)	3
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	$\geq 500$
Mating cycles with other HMC components	$\geq 3,000$
Transmission characteristics	Cat. 5 Class D up to 100 MHz

## Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

## Commercial data

Packaging size	1
Net weight	13 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors