ROHS COMPLIANT


## PRODUCT DATA DRAWING


REVISION HISTORY				
REV	DESCRIPTION	DATE	APPROVED	
-	NRN 44079	06/19	STW	

.375 9.53

-.250[6.35] **--**

2X 1/16" ALLEN KEY





ULTEM 1000 PER ASTM D5205 DETAIL A SCALE 12 : 1

FINISH:

**BEADS**:

**MATERIAL:** 

**COUPLING NUT:** 

**LOCK RING &** 

CONTACT:

**BODIES &** 

BODIES, INSERT, & COUPLING NUT:

PASSIVATED PER AMS-2700

STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1; OR ASTM A582 TYPE 303, COND. A

BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04

CONTACT: GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27, OVER NICKEL PER AMS 2404, CLASS 4, .00005" MIN.

**PERFORMANCE:** 

IMPEDANCE: 50 OHMS FREQ. RANGE: DC TO 65.0 GHz

VSWR: 1.60:1 MAX. DC TO 65.0 GHz

NOTES:

1. FOR RECOMMENDED FOOTPRINT FOR YOU PCB, CONTACT SV MICROWAVE SALES DEPARTMENT (sales@svmicro.com, 561-840-1800).

_				
	MATERIAL:	SEE NOTES		
	FINISH:	SEE NOTES		
	SURFACE AREA: N/A			
	PROPRIETARY			
	IS THE SOLE PI ANY REPRODU WITHOUT THE	TION CONTAINED IN THIS DE ROPERTY OF SV MICROWAY CTION IN PART OR AS A WE WRITTEN PERMISSION OF E, INC IS PROHIBITED.	VE, INC.	

DIMENSIONS ARE IN INCHES TOLERANCES:	UNLESS OTHERWISE SPECIFIED
FRACTIONAL: ±1/64 ANGULAR: X* ±1°0' X*X' ±15'  DECIMAL: .X ±.030	1) ALL DIMENSIONS ARE IN INICHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING 3) BREAK CORNERS & EDGES 005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA: S ON COMMON CENTERS TO BE CONCENTRIC WITHIN JOST J.R. 7) REMOVE ALL BURRS

THIRD ANGLE PROJECTION DRAWN: SRM 06/04/19

CHECKED: STW 06/04/19

APPROVED: STW 06/04/19



CONNECTOR WITH Ø.008 LAUNCH PIN

B 95077

SCALE: 6:1 SHEET 1 OF 1