




DIMENSIONS



DATE CODE PRINTING
YY-YEAR, XX-WEEK





PCB LAYOUT



GENERAL CHARACTERISTICS & RoHS INFO

REFER DRAWING C-8609-0000A

TERMINATION



ORDERING INFORMATION

SERIES	8609	3	96	7	1	13	7	4	5	ELF
ROWS FITTED WITH CONTACTS										
ROW a	b	c								96
ROW a	-	c								64
ROW -	b									32
NO. OF CONTACTS										
TYPE OF INSULATOR										
3 ROW MALE INSULATOR 7										
METHOD OF MOUNTING										
STANDARD MOUNTING - STYLE C 1										
TERMINATION										
ANGLED SPILL 13										
OPTIONS										
NO. OPTION 7										
WITH HARPOONS H										
PERFORMANCE CLASS										
DIN 41612 CLASS 3 4										
DIN 41612 CLASS 2 5										
DIN 41612 CLASS 1 6										
AS PER MIL C 55302 / JSS 50808 8										
PITCH PER ROW										
2.54 mm 5										
LEAD FREE VERSION ELF										

mat'l. code		surface		tolerance		projection		product family			
SEE DRAWING C-8609-0000A		ISO 1302		ISO 406 ISO 1101		title		8609			
itr	ecn no dr	date	tolerances unless otherwise specified		angles		linear		mm		
A	104-0063	MINI 2004-09-16	0.X ±0.1		0.XX ±0.1		scale 3:2		DIN STANDARD HEADER		
B	105-0042	MINI 2005-05-19	0.XXX ±0.1		2004-09-16		2004-09-16		DIN 41612 STYLE C		
C	106-0061	MINI 2006-05-31	0*±2*		2021-04-19		2021-04-19		dwg no sheet 1 of 1 size		
D	107-0100	KR 2007-08-20 dr	MINI K V		2021-04-19		2021-04-19		C-8609-2001 A3		
E	108-0146	KR 2008-10-21	engr RAKHEE G		appd M JACOB		SANJO		type Product Customer Drawing		
F	ELX-I-40686	MJA 2021-04-19	chr		revision F		sheet 1				
sheet index		revision sheet		1							