# Timers True Delay on Release Type DBB51





- Time range 1 to 600 s capacitor powered
- Knob-adjustable time setting
- . Automatic start after drop-out of power supply
- Repeatability:  $\leq$  0.2%
- Output: 5 A SPDT relay
- For mounting on DIN-rail in accordance with DIN/EN 50 022
- 17.5 mm DIN-rail housing (DIN 43880)
- Combined AC and DC power supply
- LED indication for relay status and power supply ON

### **Product Description**

Multi voltage (true) delay on release timer.

Time ranges from 1 to 600 s covered by 3 models.

Housing 17.5 mm wide suitable for DIN-rail mounting. Fits in M36 cover.

| Ordering key     | DBB      | 51 | CI  | <b>N24</b> | 10M |
|------------------|----------|----|-----|------------|-----|
| Housing —        | <u> </u> | Т  | Т   | Т          | Т   |
| Function —       |          |    | - 1 |            |     |
| Туре             |          |    | - 1 |            |     |
| Item number ———  |          |    | - 1 |            |     |
| Output —         |          |    |     |            |     |
| Power Supply ——— |          |    |     |            |     |
| Range ————       |          |    |     |            |     |

### **Type Selection**

| Mounting     | Output | Time range  | Supply: 24 VDC and 24 to 240 VAC |
|--------------|--------|-------------|----------------------------------|
| For DIN-rail | SPDT   | 1 to 10 s   | DBB 51 C M24 10S                 |
|              | SPDT   | 6 to 60 s   | DBB 51 C M24 1M                  |
|              | SPDT   | 60 to 600 s | DBB 51 C M24 10M                 |

## **Time Specifications**

| <u>-</u>  |   |
|---|---|
| Time ranges Type 10 S Type 1 M Type 10 M                            | 1 to 10 s<br>6 to 60 s<br>60 to 600 s                         |
| Repeatability   | ≤ 0.2%  |
| Time variation Within rated power supply Within ambient temperature | ≤ 0.05%<br>≤ 0.2%   |
| Reset DBB51CM2410S DBB51CM241M, DBB51CM2410M                        | Power supply applied for:<br>≥ 200 ms<br>≥ 200 ms<br>≥ 400 ms |

# **Supply Specifications**

| Power supply Rated operational voltage through terminals: A1, A2 | Overvoltage cat. III<br>(IEC 60664, IEC 60038)<br>24 VDC ± 15% and<br>24 to 240 VAC +10% -15%,<br>45 to 65 Hz |
|--|---|
| Voltage interruption   | ≤ 40 ms   |
| Rated operational power  AC supply:  DC supply:                  | 1.5 VA<br>0.06 W  |

### **Output Specifications**

| Output   | SPDT relay  |  |  |
|--|---|--|--|
| Rated insulation voltage   | 250 VAC (RMS)   |  |  |
|  | μ<br>5 A @ 250 VAC<br>5 A @ 24 VDC<br>2.5 A @ 250 VAC<br>2.5 A @ 24 VDC |  |  |
| Mechanical life  | ≥ 30 x 10 <sup>6</sup> operations                                       |  |  |
| Electrical life  | $\geq 10^{\circ}$ operations (at 5 A, 250 V, cos $\phi$ = 1)            |  |  |
| Operating frequency  | < 7200 operations / h   |  |  |
| Dielectric strength Dielectric voltage Rated impulse withstand voltage | 2 kVAC (RMS)<br>2.5 kV (1.2/50μs)                                       |  |  |



### **General Specifications**

| Power ON delay  | ≤ 200 ms   | Housing                                  |
|---|--|--|
| Power OFF delay   | ≤ 100 ms   | Dimensio                                 |
| Indication for Power supply ON  | LED, green   | Material Weight                          |
| Output relay ON   | LED, yellow (flashing when timing)   | Screw ter<br>Tightenin                   |
| Environment Degree of protection Pollution degree Operating temperature Storage temperature | (EN 60529)<br>IP 20<br>3 (IEC 60664)<br>-20 to 60 °C, R.H. < 95%<br>-30 to 80 °C, R.H. < 95% | CE Markin<br>EMC<br>Immunity<br>Emission |
|   |  | Timer Spe                                |

| Housing Dimensions                | 17.5 x 81 x 67.2 mm   |
|-----------------------------------|---|
| Material                          | PA66  |
| Weight                            | 70 g  |
| Screw terminals Tightening torque | Max 0.5 Nm according to IEC EN 60947  |
| CE Marking                        | Yes   |
| EMC<br>Immunity<br>Emission       | Electromagnetic Compatibility<br>According to EN 61000-6-2<br>According to EN 61000-6-3 |
| Timer Specifications              | According to EN 61812-1   |

### **Mode of Operation/Settings**

When the power supply is applied the relay operates. When the power supply is interrupted the time period starts and, at the end of the set time period, the relay releases.

If power supply is reapplied

before the relay releases the time is reset and the relay remains ON.

### Note:


DBB51 shoud not be operated by pulses shorter than 200 ms.

For these puroposes the relay DMB51, operated by external contact function, should be used.

### Time setting

Knob adjustable on absolute scale.

### **Operation Diagram**



## **Wiring Diagram**

# A1 16 18 A2 15 N(-)

### **Dimensions**

