



Nylon cable gland

Ex e nylon cable gland



Approvals / Characteristics



Features


- Suitable for potentially explosive gas atmospheres
- Increased safety "e" and intrinsic safety "i"

Certification and standards

Approved to: EN/IEC 60079-0, 60079-7, 60079-11, 60079-31
 EC TYPE Examination Certificate:
 IMQ 13 ATEX 016X, IECEx IMQ 13.0005X
 Ex e IIC Gb
 Ex tb IIIC Db
 IP test: IP66-IP68
 Temperature: -40°C to +80°C

Dimensions

Technical specifications



Type	Size	Min - Max	L	Dimensions			Torque (Nm)
				H min	CH	CH1	
EXCGM20S	20	6,0 - 12,0	10	40	24	24	5
EXCGM20SL	20	6,0 - 12,0	15	45	24	24	5
EXCGM20M	20	10,0 - 14,0	10	42	27	27	5.5
EXCGM20ML	20	10,0 - 14,0	15	50	27	27	5.5
EXCGM25S	25	13,0 - 18,0	10	47	33	33	7
EXCGM25SL	25	13,0 - 18,0	15	50	33	33	7
EXCGM25M	25	11,0 - 17,0	8	42.5	29	29	5
EXCGM32S	32	15,0 - 21,0	10	50	36	36	6
EXCGM32M	32	18,0 - 25,0	15	68	42	42	9
EXCGM40S	40	19,0 - 28,0	10	55	46	46	5
EXCGM40M	40	22,0 - 32,0	18	68	53	53	17
EXCGM50S	50	30,0 - 38,0	18	73	60	60	22
EXCGM63S	63	34,0 - 44,0	18	74	65	65	23

Type	Size (inch)	Min - Max	L	Dimensions			Torque (Nm)
				H min	CH	CH1	
EXCG050S	1/2"	6 - 12	15	45	24	24	5
EXCG050M	1/2"	10 - 14	15	47	27	27	5.5
EXCG075S	3/4"	13 - 18	15	50	33	33	7
EXCG100S	1"	18 - 25	18	58	42	42	9

For accessories see pages 134-35