

Heatsinks for D PAK and others

– **tape width:** 24 mm, **reel diameter:** 330 mm, **quantity:** FK 250 06 = 450, FK 250 08 = 450, FK 250 10 = 350
 – **tape width:** 24 mm, **reel diameter:** 330 mm, **quantity:** FK 251 06 = 450, FK 251 08 = 350, FK 251 10 = 250

art. no.			37 K/W	
FK 250 06 LF PAK ... weight: 1 g				
art. no.			34,8 K/W	
FK 250 08 LF PAK ... weight: 1.1 g				
art. no.			28,8 K/W	
FK 250 10 LF PAK ... weight: 1.2 g				
art. no.			32 K/W	
FK 251 06 LF PAK ... weight: 1.3 g				
art. no.			29,8 K/W	
FK 251 08 LF PAK ... weight: 1.4 g				
art. no.			24 K/W	
FK 251 10 LF PAK ... weight: 1.5 g				
please indicate:	... packing (option) TR=tape and reel			

surface treatment: solderable
material: copper (Cu)
material thickness: 0.6 mm

Heatsinks for transistors
 Heatsinks for TO 5 and TO 18
 Attachable heatsinks
 Finger-shaped heatsinks

→ C 4 – 9
 → C 15 – 16
 → C 10 – 14
 → C 2 – 3

High capacity heatsinks
 Designed parts out of aluminium
 Heatsink profile-overview
 Classification table

→ A 56 – 57
 → A 135
 → A 13 – 16
 → A 18 – 20

C 18

A

B

C

D

E

F

G

H

I

K

L

M

N