# 74AHCT17A Hex buffer Schmitt trigger Rev. 1 — 18 May 2017

**Product data sheet** 

## **General description**

The 74AHCT17A is a hex buffer with Schmitt-trigger inputs, capable of transforming slowly changing input signals into sharply defined, jitter-free output signals.

Designed to operate over a V<sub>CC</sub> range from 4.5 V to 5.5 V, the inputs are TTL compatible. This range allows the device to be used to translate from 3.3 V to 5 V.

This device is fully specified for partial Power-down applications using I<sub>OFF</sub>. The I<sub>OFF</sub> circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

#### **Features and benefits**

- · Direct interface with TTL levels
- Supply voltage range from 4.5 V to 5.5 V
- Typical t<sub>pd</sub> of 3.2 ns at 5 V
- Typical  $V_{OL(p)}$  < 0.8 V at  $V_{CC}$  = 5 V,  $T_{amb}$  = 25 °C
- Typical  $V_{OH(v)} > 2.3 \text{ V}$  at  $V_{CC} = 5 \text{ V}$ ,  $T_{amb} = 25 ^{\circ}\text{C}$
- Supports mixed-mode voltage operation on all ports
- I<sub>OFF</sub> circuitry provides partial Power-down mode operation
- Latch-up performance exceeds 250 mA per JESD 78 Class II
- ESD protection:
  - HBM ANSI/ESDA/JEDEC JS-001 Class 2 exceeds 3 kV
  - MM JESD22-A115-A exceeds 150 V
  - CDM JESD22-C101E exceeds 2 kV
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C


## **Ordering information**

#### **Table 1. Ordering information**

Type number	Package				
	Temperature range	Name	Description	Version	
74AHCT17APW	-40 °C to +125 °C	TSSOP14	plastic thin shrink small outline package; 14 leads; body width 4.4 mm	SOT402-1	




## 4 Functional diagram



## 5 Pinning information

### 5.1 Pinning



### 5.2 Pin description

Table 2. Pin description

Symbol	Pin	Description
1A, 2A, 3A, 4A, 5A, 6A	1, 3, 5, 9, 11, 13	data input
1Y, 2Y, 3Y, 4Y, 5Y, 6Y	2, 4, 6, 8, 10, 12	data output
GND	7	ground (0 V)
V <sub>CC</sub>	14	supply voltage

74AHCT17A

All information provided in this document is subject to legal disclaimers.

## 6 Functional description

### Table 3. Function table [1]

Input	Output
nA	nY
L	L
Н	Н

<sup>[1]</sup> H = HIGH voltage level;

## 7 Limiting values

#### **Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V <sub>CC</sub>	supply voltage			-0.5	+7.0	V
VI	input voltage		[1]	-0.5	+7.0	V
Vo	output voltage	output HIGH or LOW state	[2] [3]	-0.5	V <sub>CC</sub> + 0.5	V
		output power-down	[2]	-0.5	+7.0	V
I <sub>IK</sub>	input clamping current	V <sub>I</sub> < 0 V		-20	-	mA
I <sub>OK</sub>	output clamping current	V <sub>O</sub> < 0 V		-20	-	mA
Io	output current	$V_O = 0 V \text{ to } V_{CC}$		-	±25	mA
I <sub>CC</sub>	supply current			-	75	mA
I <sub>GND</sub>	ground current			-75	-	mA
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub>	total power dissipation	$T_{amb}$ = -40 °C to +125 °C	[4]	-	500	mW

<sup>[1]</sup> If the input current ratings are observed, the minimum input voltage ratings may be exceeded.

## 8 Recommended operating conditions

#### Table 5. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
$V_{CC}$	supply voltage		4.5	5.0	5.5	V
VI	input voltage		0	-	5.5	V
Vo	output voltage	output HIGH or LOW state	0	-	$V_{CC}$	V
		output power-down	0	-	5.5	V
T <sub>amb</sub>	ambient temperature		-40	+25	+125	°C
Δt/ΔV	input transition rise and fall rate	$V_{CC} = 5.0 \text{ V} \pm 0.5 \text{ V}$	-	-	1	ms/V

74AHCT17A

All information provided in this document is subject to legal disclaimers.

L = LOW voltage level.

<sup>[2]</sup> If the output current ratings are observed, the output voltage ratings may be exceeded.

<sup>[3]</sup> This value is limited to 7 V maximum.

<sup>[4]</sup> For TSSOP14 package: above 75 °C, the value of Ptot derates linearly at 7 mW/K.

## 9 Static characteristics


#### **Table 6. Static characteristics**


At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

Symbol	Parameter Conditions		25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit	
			Min	Тур	Max	Min	Max	Min	Max	
$V_{T+}$	positive-going	V <sub>CC</sub> = 4.5 V	-	-	1.9	-	1.9	-	1.9	V
	threshold voltage	V <sub>CC</sub> = 5.5 V	-	-	2.1	-	2.1	-	2.1	V
V <sub>T-</sub>	negative-going	V <sub>CC</sub> = 4.5 V	0.5	-	-	0.5	-	0.5	-	V
	threshold voltage	V <sub>CC</sub> = 5.5 V	0.6	-	-	0.6	-	0.6	-	V
$V_{H}$	hysteresis	V <sub>CC</sub> = 4.5 V	0.4	-	1.4	0.4	1.4	0.4	1.4	V
	voltage	V <sub>CC</sub> = 5.5 V	0.4	-	1.5	0.4	1.5	0.4	1.5	V
V <sub>OH</sub>	HIGH-level	$V_I = V_{IH}$ or $V_{IL}$ ; $V_{CC} = 4.5 \text{ V}$								
	output voltage	I <sub>O</sub> = -50 μA	4.4	-	-	4.4	-	4.4	-	V
		I <sub>O</sub> = -8 mA	3.94	-	-	3.8	-	3.7	-	V
V <sub>OL</sub>	LOW-level	$V_I = V_{IH}$ or $V_{IL}$ ; $V_{CC} = 4.5 \text{ V}$								
	output voltage	I <sub>O</sub> = 50 μA	-	-	0.1	-	0.1	-	0.1	V
		I <sub>O</sub> = 8 mA	-	-	0.36	-	0.44	-	0.55	V
l <sub>OFF</sub>	power-off leakage current	$V_I$ or $V_O$ = GND to 5.5 V; $V_{CC}$ = 0 V	-	-	0.5	-	5	-	5	μΑ
l <sub>l</sub>	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 0 \text{ V to } 5.5 \text{ V}$	-	-	±0.1	-	±1	-	±1	μA
I <sub>CC</sub>	supply current	$V_I = V_{CC}$ or GND; $I_O = 0$ A; $V_{CC} = 5.5 \text{ V}$	-	-	2	-	20	-	20	μA
ΔI <sub>CC</sub>	additional supply current	per input pin; $V_{CC}$ = 5.5 V; $V_{I}$ = 3.4 V; $I_{O}$ = 0 A; other pins at $V_{CC}$ or GND	-	-	1.35	-	1.5	-	1.5	mA

Downloaded from Arrow.com.

### 9.1 Transfer characteristics waveforms





## 10 Dynamic characteristics

#### **Table 7. Dynamic characteristics**

GND = 0 V. For test circuit, see Figure 9.

Symbol	Parameter	Conditions	25 °C		-40 °C to +85 °C		-40 °C to +125 °C		Unit	
			Min	Typ <sup>[1]</sup>	Max	Min	Max	Min	Max	
t <sub>pd</sub>	propagation	nA to nY; see Figure 8 [2]								
	delay	V <sub>CC</sub> = 4.5 V to 5.5 V								
		C <sub>L</sub> = 15 pF	-	3.2	8.3	1	9.9	1	10.6	ns
		C <sub>L</sub> = 50 pF	-	5.0	9.8	1	11.3	1	12.1	ns
Cı	input capacitance	$V_I = V_{CC}$ or GND; $V_{CC} = 5 V$	-	2	6	-	6	-	6	pF
Co	output capacitance	$V_O = V_{CC}$ or GND; $V_{CC} = 5 \text{ V}$	-	5	-	-	-	-	-	pF
C <sub>PD</sub>	power dissipation capacitance	per buffer; $C_L = 0$ pF; [3] f = 10 MHz; $V_I = GND$ to $V_{CC}$	-	9.8	-	-	-	-	-	pF

#### **Table 8. Noise characteristics**

GND = 0 V. For test circuit, see Figure 9.

Symbol Parameter		Conditions	T <sub>e</sub>	T <sub>amb</sub> = 25 °C			
			Min	Тур	Max		
V <sub>CC</sub> = 5 \	/; C <sub>L</sub> = 50 pF		'				
$V_{OL(p)}$	LOW-level output voltage (peak)		-	0.4	0.8	V	
$V_{OL(v)}$	LOW-level output voltage (valley)		-0.8	-0.2	-	V	
$V_{OH(v)}$	HIGH-level output voltage (valley)		-	4.5	-	V	
V <sub>IH(AC)</sub>	AC HIGH-level input voltage		2	-	-	V	
V <sub>IL(AC)</sub>	AC LOW-level input voltage		-	-	0.8	V	

Typical values are measured at  $T_{amb}$  = 25 °C and  $V_{CC}$  = 5 V.  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .  $C_{PD}$  is used to determine the dynamic power dissipation  $P_D$  (µW).

 $P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum (C_L \times V_{CC}^2 \times f_0)$  where:


f<sub>i</sub> = input frequency in MHz;

 $f_o$  = output frequency in MHz;

C<sub>L</sub> = output load capacitance in pF;

 $V_{CC}$  = supply voltage in Volts.


### 10.1 Waveforms and test circuit



**Table 9. Measurement points** 

Input	Output
$V_{M}$	$V_{M}$
1.5 V	0.5V <sub>CC</sub>

Downloaded from Arrow.com.



Test data is given in Table 10.

Definitions test circuit:

 $R_T$  = Termination resistance should be equal to output impedance  $Z_o$  of the pulse generator

 $C_L$  = Load capacitance including jig and probe capacitance

Figure 9. Test circuit for measuring switching times

Table 10. Test data

Input		Load	Test
VI	t <sub>r</sub> , t <sub>f</sub>	CL	
GND to 3 V	3.0 ns	15 pF, 50 pF	t <sub>PLH</sub> , t <sub>PHL</sub>

## 11 Package outline

## TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm SOT402-1 = v M A Q pin 1 index detail X ⊕ w M е scale **DIMENSIONS (mm are the original dimensions)** D (1) E (2) Z (1) UNIT ${\sf H}_{\sf E}$ θ У max. 0.75 0.15 0.95 0.30 0.2 5.1 4.5 6.6 0.72 1.1 mm 0.25 0.65 0.2 0.13 0.05 0.80 0.19

#### Notes

- Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- Plastic interlead protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFER	EUROPEAN	ISSUE DATE		
VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE
SOT402-1		MO-153				<del>-99-12-27</del> 03-02-18

Figure 10. Package outline SOT402-1 (TSSOP14)

All information provided in this document is subject to legal disclaimers

## 12 Abbreviations

#### **Table 11. Abbreviations**

Acronym	Description
CDM	Charge Device Model
DUT	Device Under Test
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model
TTL	Transistor-Transistor Logic

## 13 Revision history

#### Table 12. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
74AHCT17A v.1	20170518	Product data sheet	-	-

## 14 Legal information

#### 14.1 Data sheet status

Document status <sup>[1][2]</sup>	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- Please consult the most recently issued document before initiating or completing a design.
- The term 'short data sheet' is explained in section "Definitions". [2] [3]
- The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

#### 14.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### 14.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

All information provided in this document is subject to legal disclaimers.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer

design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### 14.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## **74AHCT17A**

Hex buffer Schmitt trigger

### **Contents**

1	General description	1
2	Features and benefits	1
3	Ordering information	1
4	Functional diagram	2
5	Pinning information	2
5.1	Pinning	
5.2	Pin description	
6	Functional description	
7	Limiting values	
8	Recommended operating conditions	3
9	Static characteristics	4
9.1	Transfer characteristics waveforms	5
10	Dynamic characteristics	E
10.1	Waveforms and test circuit	7
11	Package outline	9
12	Abbreviations	10
13	Revision history	
14	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2017.

All rights reserved.