

**Bourdon tube pressure gauges, liquid filled,  
Type 213.53.0XX  
Item no.: 48775768**

Description	
Design according	EN 837-1
Accuracy class	class 1.6
Scale range	0...400 bar
Constructional design	
Process connection	M10 x 1.0
Connector location	back mount
Pressure element	Copper alloy
Movement	Copper alloy
Case	Crimp ring case (version 53)
Nominal size	063 mm
Case filling fluid	glycerine
Pointer	plastic, black
Window	plastic, clear
Dial	plastic, white, with stop-pin
Options	
Mounting flange/bracket	front flange, stainless steel
Operating conditions	
Pressure limitation	Steady: 3/4 x full scale value Fluctuating: 2/3 x full scale value Short time: Full scale value
Permissible ambient temperature	-20 ... +60 °C
Permissible medium temperature	+60°C maximum
Temperature effect when the temperature deviates from the reference temperature (+20°C)	Max. ±0.4 %/10 K of the span
Ingress protection	IP 65

Image does not exist.