

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 2 of 8

Pictograms:

Hazard statements

H222	Extremely flammable aerosol.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.

Precautionary statements

P333+P313	If skin irritation or rash occurs: Get medical advice/attention.
P251	Do not pierce or burn, even after use.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P261	Avoid breathing dust/fume/gas/mist/vapours/spray.
P271	Use only outdoors or in a well-ventilated area.

SECTION 3: Composition/information on ingredients
3.2. Mixtures
Hazardous components

CAS No	Chemical name	Quantity
	EC No	Index No
	REACH No	
	GHS Classification	
	Hydrocarbons, C6, isoalkanes, <5% n-hexane	40-70 %
	931-254-9	01-2119484651-34
	Flam. Liq. 2, Skin Irrit. 2, STOT SE 3, Asp. Tox. 1, Aquatic Chronic 2; H225 H315 H336 H304 H411	
5989-27-5	(R)-p-mentha-1,8-diene; d-limonene	10-30%
	227-813-5	601-029-00-7
	Flam. Liq. 3, Skin Irrit. 2, Skin Sens. 1, Aquatic Acute 1, Aquatic Chronic 1; H226 H315 H317 H400 H410	
927-356-8	Hydrocarbons, C9-C11, n-alkane, isoalkane, cyclic, <2% aromatic	10-25%
		01-2119463258-33
	Flam. Liq. 3, STOT SE 3, Asp. Tox. 1; H226 H336 H304	
124-38-9	Carbondioxide	2,5-10 %
	204-696-9	
	Compressed gas; H280	
64-17-5	ethanol; ethyl alcohol	<1%
	200-578-6	603-002-00-5
	Flam. Liq. 2; H225	

Full text of H and EUH statements: see section 16.

SECTION 4: First aid measures
4.1. Description of first aid measures

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 3 of 8

General information

No data available

After inhalation

Provide fresh air.

After contact with skin

After contact with skin, wash immediately with: Water. Change contaminated clothing.

After contact with eyes

Rinse immediately carefully and thoroughly with eye-bath or water.

After ingestion

If swallowed, immediately drink: Water.

4.2. Most important symptoms and effects, both acute and delayed

No data available

4.3. Indication of any immediate medical attention and special treatment needed

No data available

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media**Carbon dioxide (CO₂). Foam. Extinguishing powder.**Unsuitable extinguishing media**

Water with tenside additive. Water.

5.2. Special hazards arising from the substance or mixture

Combustible. Vapours may form explosive mixtures with air. Heating causes rise in pressure with risk of bursting.

5.3. Advice for firefighters

In case of fire: Wear self-contained breathing apparatus.

Additional information

Use water spray jet to protect personnel and to cool endangered containers.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Remove all sources of ignition.

6.2. Environmental precautions

Do not allow to enter into surface water or drains. Explosion hazard.

6.3. Methods and material for containment and cleaning up

Ventilate affected area.

SECTION 7: Handling and storage**7.1. Precautions for safe handling****Advice on safe handling**

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Advice on protection against fire and explosion

Keep away from sources of ignition - No smoking.

7.2. Conditions for safe storage, including any incompatibilities**Requirements for storage rooms and vessels**

Keep container tightly closed. Keep in a cool, well-ventilated place. Keep away from sources of ignition - No smoking.

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 4 of 8

Hints on joint storage

Do not store together with: Material, rich in oxygen, oxidizing.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits (EH40)

CAS No	Substance	ppm	mg/m ³	fibres/ml	Category	Origin
124-38-9	Carbon dioxide	5000	9150		TWA (8 h)	WEL
		15000	27400		STEL (15 min)	WEL
64-17-5	Ethanol	1000	1920		TWA (8 h)	WEL

8.2. Exposure controls



Appropriate engineering controls

If handled uncovered, arrangements with local exhaust ventilation have to be used. Do not breathe gas/fumes/vapour/spray.

Protective and hygiene measures

Change contaminated clothing. Wash hands before breaks and after work. When using do not eat or drink.

Eye/face protection

Tightly sealed safety glasses.

Hand protection

DIN EN 374 Tested protective gloves are to be worn: NBR (Nitrile rubber) For special purposes, it is recommended to check the resistance to chemicals of the protective gloves mentioned above together with the supplier of these gloves. NBR (Nitrile rubber)

Skin protection

Protective clothing:

Respiratory protection

In case of inadequate ventilation wear respiratory protection.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state:	Aerosol
Colour:	colourless
Odour:	characteristic

Changes in the physical state

Initial boiling point and boiling range:	60 °C
Flash point:	< 0 °C
Lower explosion limits:	1,2 vol. %
Upper explosion limits:	7 vol. %
Ignition temperature:	300 °C
Vapour pressure: (at 20 °C)	227 hPa

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 5 of 8

 Vapour pressure: 719 hPa
 (at 50 °C)

 Density: 0,71 g/cm³

SECTION 10: Stability and reactivity

10.1. Reactivity

No data available

10.2. Chemical stability

No data available

10.3. Possibility of hazardous reactions

No data available

10.4. Conditions to avoid

Keep away from heat. Ignition hazard.

10.5. Incompatible materials

No data available

10.6. Hazardous decomposition products

No data available

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity

CAS No	Chemical name				
	Exposure route	Dose	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane				
	oral	LD50 >1000 mg/kg	Fisch 1		
5989-27-5	(R)-p-mentha-1,8-diene; d-limonene				
	oral	LD50 > 2000 mg/kg	Rat		
	dermal	LD50 > 2000 mg/kg	Rabbit	IUCLID	
64-17-5	ethanol; ethyl alcohol				
	oral	LD50 6200 mg/kg	Rat	IUCLID	
	inhalation (4 h) vapour	LC50 95,6 mg/l	Rat	RTECS	

SECTION 12: Ecological information

12.1. Toxicity

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 6 of 8

CAS No	Chemical name					
	Aquatic toxicity	Dose	[h] [d]	Species	Source	Method
	Hydrocarbons, C6, isoalkanes, <5% n-hexane					
	Acute algae toxicity	ErC50 mg/l	>1000	72 h	Alge	
	Acute crustacea toxicity	EC50 mg/l	>1000	48 h	Daphnia pulex (water flea)	
5989-27-5	(R)-p-mentha-1,8-diene; d-limonene					
	Acute fish toxicity	LC50	0,7 mg/l	96 h	Pimephales promelas	
	Acute crustacea toxicity	EC50 mg/l	0,42	48 h	Daphnia magna	
64-17-5	ethanol; ethyl alcohol					
	Acute crustacea toxicity	EC50	9268 - 14221 mg/l	48 h	Daphnia magna	IUCLID

12.3. Bioaccumulative potential
Partition coefficient n-octanol/water

CAS No	Chemical name	Log Pow
5989-27-5	(R)-p-mentha-1,8-diene; d-limonene	4,23
64-17-5	ethanol; ethyl alcohol	-0,31

Further information

Do not allow to enter into surface water or drains.

SECTION 13: Disposal considerations
13.1. Waste treatment methods
Advice on disposal

Dispose of waste according to applicable legislation.

Waste disposal number of waste from residues/unused products

160504 WASTES NOT OTHERWISE SPECIFIED IN THE LIST; gases in pressure containers and discarded chemicals; gases in pressure containers (including halons) containing hazardous substances; hazardous waste

Waste disposal number of contaminated packaging

150104 WASTE PACKAGING; ABSORBENTS, WIPING CLOTHS, FILTER MATERIALS AND PROTECTIVE CLOTHING NOT OTHERWISE SPECIFIED; packaging (including separately collected municipal packaging waste); metallic packaging

Contaminated packaging

Non-contaminated packages may be recycled. Handle contaminated packages in the same way as the substance itself.

SECTION 14: Transport information
Land transport (ADR/RID)

14.1. UN number:	UN1950
14.2. UN proper shipping name:	AEROSOLS
14.3. Transport hazard class(es):	2
Hazard label:	2.1

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 7 of 8



Classification code: 5F
Special Provisions: 190 327 625
Limited quantity: 1 L
Transport category: 2
Tunnel restriction code: D

Other applicable information (land transport)

E0

Inland waterways transport (ADN)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
Hazard label: 2.1



Classification code: 5F
Special Provisions: 190 327 344 625
Limited quantity: 1 L

Other applicable information (inland waterways transport)

E0

Marine transport (IMDG)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS
14.3. Transport hazard class(es): 2
14.4. Packing group: -
Hazard label: 2, see SP63

Special Provisions: 63, 190, 277, 327, 344, 959
Limited quantity: See SP277
EmS: F-D, S-U

Other applicable information (marine transport)

E0

Air transport (ICAO-TI/IATA-DGR)

14.1. UN number: UN1950
14.2. UN proper shipping name: AEROSOLS, flammable
14.3. Transport hazard class(es): 2.1
Hazard label: 2.1



Special Provisions: A145 A167
Limited quantity Passenger: 30 kg G

Safety Data Sheet

according to Regulation (EC) No 1907/2006

Label-Off

Revision date: 18.11.2019

Product code: 134

Page 8 of 8

IATA-packing instructions - Passenger:	203
IATA-max. quantity - Passenger:	75 kg
IATA-packing instructions - Cargo:	203
IATA-max. quantity - Cargo:	150 kg

Other applicable information (air transport)E0
: Y203**14.5. Environmental hazards**

ENVIRONMENTALLY HAZARDOUS: yes

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulatory information**

Restrictions on use (REACH, annex XVII):

Entry 28: Hydrocarbons, C6, isoalkanes, <5% n-hexane

2004/42/EC (VOC): 62,5 % (443,75 g/l)

National regulatory information

Water contaminating class (D): 2 - clearly water contaminating

SECTION 16: Other information**Relevant H and EUH statements (number and full text)**

H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H336	May cause drowsiness or dizziness.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.

(The data for the hazardous ingredients were taken respectively from the last version of the sub-contractor's safety data sheet.)