

3 V/5 V, Rail-to-Rail Quad, 8-Bit DAC

AD7304/AD7305

FEATURES

Four 8-bit DACs in one package +3 V, +5 V, and ±5 V operation Rail-to-rail REF input to voltage output swing 2.6 MHz reference multiplying bandwidth Internal power-on reset SPI serial interface-compatible—AD7304 Fast parallel interface—AD7305 40 µA power shutdown

APPLICATIONS

Automotive output span voltage Instrumentation, digitally controlled calibration Pin-compatible AD7226 replacement when V_{DD} < 5.5 V

GENERAL DESCRIPTION

The AD7304/AD7305¹ are quad, 8-bit DACs that operate from a single +3 V to +5 V supply, or \pm 5 V supplies. The AD7304 has a serial interface, while the AD7305 has a parallel interface. Internal precision buffers swing rail-to-rail. The reference input range includes both supply rails, allowing for positive or negative full-scale output voltages. Operation is guaranteed over the supply voltage range of 2.7 V to 5.5 V, consuming less than 9 mW from a 3 V supply.


The full-scale voltage output is determined by the external reference input voltage applied. The rail-to-rail V_{REF} input to DAC V_{OUT} allows for a full-scale voltage set equal to the positive supply, V_{DD} , the negative supply, V_{SS} , or any value in between.


The AD7304's doubled-buffered serial data interface offers high speed, 3-wire, SPI*-, and microcontroller-compatible inputs using data in (SDI), clock (CLK), and chip select $(\overline{\text{CS}})$ pins. Additionally, an internal power-on reset sets the output to zero scale.

The parallel input AD7305 uses a standard address decode along with the $\overline{\rm WR}$ control line to load data into the input registers.

The double-buffered architecture allows all four input registers to be preloaded with new values, followed by an LDAC control strobe that copies all the new data into the DAC registers, thereby updating the analog output values.

FUNCTIONAL BLOCK DIAGRAMS





When operating from less than 5.5 V, the AD7305 is pin-compatible with the popular industry-standard AD7226.

An internal power-on reset places both parts in the zero-scale state at turn-on. A 40 μ A power shutdown (SHDN) feature is activated on both parts by three-stating the SDI/SHDN pin on the AD7304 and three-stating the A0/SHDN address pin on the AD7305.

The AD7304/AD7305 are specified over the extended industrial -40°C to +85°C and the automotive -40°C to +125°C temperature ranges. AD7304s are available in a wide-body 16-lead SOIC (R-16) package. The parallel input AD7305 is available in the wide-body 20-lead SOIC (R-20) surface-mount package. For ultracompact applications, the thin 1.1 mm, 16-lead TSSOP (RU-16) package is available for the AD7304, while the 20-lead TSSOP (RU-20) houses the AD7305.

Rev. C Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

¹ Protected under Patent No. 5684481.

TABLE OF CONTENTS

Specifications
Timing Specifications
Absolute Maximum Ratings
ESD Caution
Pin Configurations and Function Descriptions
Typical Performance Characteristics10
Circuit Operation1
DAC Section1
AD7304 Serial Data Interface1
AD7304 Hardware Shutdown SHDN 1

Revision History

11/04—Data Sheet Changed from Rev. B to Rev. C

Update Format	Universal
Update Features	
Changes to Figure 35	
Add Power-Up Sequence	
Changes to Figure 36	
Change to Figure 37	
Updated Outline Dimensions	

2/04—Data Sheet Changed from Rev. A to Rev. B

Renumber TPCs and Figures	Universal
Deleted N-16 and N-20 packages	Universal
Changes to Absolute Maximum Ratings	
Changes to Ordering Guide	
Updated Outline Dimensions	14

3/98—Changed from Rev. 0 to Rev. A

2/98—Revision 0: Initial Version

AD7304/AD7305 Power-On Reset 15
Power up sequence15
AD7305 Parallel Data Interface10
AD7226 Pin Compatibility 10
AD7305 Hardware Shutdown SHDN 16
ESD Protection Circuits
Applications12
Outline Dimensions18
Ordering Guide 19

SPECIFICATIONS

@ $V_{DD} = 3 \text{ V or } 5 \text{ V}, \text{ V}_{SS} = 0 \text{ V}$; or $V_{DD} = +5 \text{ V}$ and $V_{SS} = -5 \text{ V}, \text{ V}_{SS} \le \text{V}_{REF} \le \text{V}_{DD}, -40^{\circ}\text{C} < \text{T}_{A} < +85^{\circ}\text{C}/+125^{\circ}\text{C}$, unless otherwise noted. Table 1.

Parameter	Symbol	Condition	3 V ± 10%	5 V ± 10%	±5 V ± 10%	Unit
STATIC PERFORMANCE						
Resolution ¹	Ν		8	8	8	Bits
Integral Nonlinearity ²	INL		±1	±1	±1	LSB max
Differential Nonlinearity	DNL	Monotonic, all codes 0 to 0xFF	±1	±1	±1	LSB max
Zero-Scale Error	V _{ZSE}	Data = 0x00	15	15	±15	mV max
Full-Scale Voltage Error	V _{FSE}	Data = 0xFF	±4	±4	±4	LSB max
Full-Scale Temperature	TCV _{FS}		5	5	5	ppm/°C typ ⁴
Coefficient ³						
REFERENCE INPUT						
V _{REFIN} Range	VREFIN		V _{SS} /V _{DD}	V _{SS} /V _{DD}	V _{SS} /V _{DD}	V min/max
Input Resistance (AD7304)	R _{REFIN}	Code = 0x55	28	28	28	kΩ typ
Input Resistance (AD7305)	R _{REFIN}	All DACs at code = $0x55$	7.5	7.5	7.5	kΩ typ
Input Capacitance ³	CREFIN		5	5	5	pF typ
ANALOG OUTPUTS						
Output Voltage Range	VOUT		V _{ss} /V _{DD}	V _{ss} /V _{DD}	Vss/Vdd	V min/max
Output Current Drive	lout	$Code = 0x80, \Delta V_{OUT} < 1 LSB$	±3	±3	±3	mA typ
Shutdown Resistance Rout DAC outputs placed in shutdown		DAC outputs placed in shutdown state	120	120	120	kΩ typ
Capacitive Load ³	C∟	No oscillation	200	200	200	pF typ
LOGIC INPUTS						
Logic Input Low Voltage	VIL		0.6	0.8	0.8	V min
Logic Input High Voltage	VIH		2.1	2.4	2.4	V max
Input Leakage Current ⁵	I _{IL}		±10	±10	±10	μA max
Input Capacitance ³	CIL		8	8	8	pF max
AC CHARACTERISTICS ³						
Output Slew Rate	SR	Code = 0x00 to 0xFF to 0x00	1/2.7	1/3.6	1.0/3.6	V/µs min/typ
Reference Multiplying	BW	Small signal, V _{ss} = -5 V			2.6	MHz typ
Total Harmonic Distortion	THD	$V_{REF} = 4 V p - p, V_{SS} = -5 V, f = 1 kHz$			0.025	%
Settling Time ⁶	ts	To $\pm 0.1\%$ of full scale	1.1/2	1.0/2	1.0/2	µs typ/max
Shutdown Recovery Time	t _{sDR}	To $\pm 0.1\%$ of full scale	2	2	2	µs max
Time to Shutdown	t _{SDN}		15	15	15	µs typ
DAC Glitch	Q		15	15	15	nVs typ
Digital Feedthrough	0		2	2	2	nVs typ
Feedthrough	VOUT/VREE	Code = $0x00$, $V_{REF} = 1 V p-p$, f = 100 kHz			-65	dB
SUPPLY CHARACTERISTICS						
Positive Supply Current	IDD	$V_{LOGIC} = 0 V \text{ or } V_{DD}$, no load	6	6	6	mA max
Negative Supply Current	Iss	$V_{SS} = -5 V$		-	6	mA max
Power Dissipation	P _{DISS}	$V_{\text{LOGIC}} = 0 \text{ V or } V_{\text{DD}}$, no load	15	30	60	mW max
Power Down	I _{DD_SD}	SDI/SHDN = floating	40	40	40	µA typ
Power Supply Sensitivity	PSS	$\Delta V_{DD} = \pm 10\%$	0.004	0.004	0.004	%/%

¹ One LSB = $V_{REF}/256$.

² The first three codes (0x00, 0x01, 0x10) are excluded from the integral nonlinearity error measurement in single-supply operation 3 V or 5 V.

³ These parameters are guaranteed by design and not subject to production testing.

⁴ Typical specifications represent average readings measured at 25°C.

 $^{^5}$ The SDI/SHDN and A0/SHDN pins have a 30 μA maximum $I_{\rm IL}$ input leakage current.

⁶ The settling time specification does not apply for negative going transitions within the last three LSBs of ground in single-supply operation.




Figure 3. Rail-to-Rail Reference Input to Output at 20 kHz

TIMING SPECIFICATIONS

 $@V_{\text{DD}} = 3 \text{ V or } 5 \text{ V}, \text{ } \text{V}_{\text{SS}} = 0 \text{ } \text{V}; \text{ or } \text{ } \text{V}_{\text{DD}} = +5 \text{ } \text{V} \text{ and } \text{ } \text{V}_{\text{SS}} = -5 \text{ } \text{V}, \text{ } \text{V}_{\text{SS}} \leq \text{ } \text{V}_{\text{REF}} \leq \text{ } \text{V}_{\text{DD}}, -40^{\circ}\text{C} < \text{T}_{\text{A}} < +85^{\circ}\text{C}/+125^{\circ}\text{C}, \text{ unless otherwise noted.}$

Parameter	Symbol	3 V ± 10%	5 V ± 10%	±5 V ± 10%	Unit	
INTERFACE TIMING SPECIFICATIONS ^{1, 2}						
AD7304 Only						
Clock Width High	t _{CH}	70	55	55	ns min	
Clock Width Low	tcl	70	55	55	ns min	
Data Setup	t _{DS}	50	40	40	ns min	
Data Hold	t _{DH}	30	20	20	ns min	
Load Pulse Width	t _{LDW}	70	60	60	ns min	
Load Setup	t _{LD1}	40	30	30	ns min	
Load Hold	t _{LD2}	40	30	30	ns min	
Clear Pulse Width	t _{CLWR}	60	60	60	ns min	
Select	tcss	30	20	20	ns min	
Deselect	t _{CSH}	60	40	40	ns min	
AD7305 Only						
Data Setup	t _{DS}	60	40	40	ns min	
Data Hold	t _{DH}	30	20	20	ns min	
Address Setup	t _{AS}	60	40	40	ns min	
Address Hold	t _{AH}	30	20	20	ns min	
Write Width	t _{WR}	60	50	50	ns min	
Load Pulse Width	t _{LDW}	60	50	50	ns min	
Load Setup	t _{LS}	60	40	40	ns min	
Load Hold	t _{LH}	30	20	20	ns min	

¹ These parameters are guaranteed by design and not subject to production testing. ² All input control signals are specified with $t_R = t_F = 2$ ns (10% to 90% of V_{DD}) and timed from a voltage level of 1.6 V.

ABSOLUTE MAXIMUM RATINGS

Table 3.

Parameter	Rating
V _{DD} to GND	–0.3 V, +8 V
V _{ss} to GND	+0.3 V, -8 V
V _{REFX} to GND	Vss, Vdd
Logic Inputs to GND	$-0.3 \text{ V}, \text{V}_{\text{DD}} + 0.3 \text{ V}$
Voutx to GND	$-0.3 \text{ V}, \text{V}_{\text{DD}} + 0.3 \text{ V}$
Iout Short-Circuit to GND	50 mA
Package Power Dissipation	(T _{J MAX} – T _A)/θ _{JA}
Thermal Resistance θ _{JA}	
16-Lead SOIC Package (R-16)	73°C/W
16-Lead TSSOP Package (RU-16)	180°C/W
20-Lead SOIC Package (R-20)	74°C/W
20-Lead TSSOP Package (RU-20)	155°C/W
Maximum Junction Temperature (T _{J MAX})	150°C
Operating Temperature Range	-40°C to +85°C
Storage Temperature Range	–65°C to +150°C
Lead Temperature	
R-16, R-20, RU-16, RU-20 (Vapor Phase, 60 sec)	235°C
R-16, R-20, RU-16, RU-20 (Infrared, 15 sec)	220°C

Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only; functional operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ESD CAUTION

ESD (electrostatic discharge) sensitive device. Electrostatic charges as high as 4000 V readily accumulate on the human body and test equipment and can discharge without detection. Although this product features proprietary ESD protection circuitry, permanent damage may occur on devices subjected to high energy electrostatic discharges. Therefore, proper ESD precautions are recommended to avoid performance degradation or loss of functionality.








Figure 5. AD7304 Timing Diagram Zoom In

Table 4.	AD7304	Control	Logic	Truth	Table
1 4010 11	110,001	Control	LUSIC		1 4010

CS ¹	CLK ¹	LDAC		Serial Shift Register Function	Input REG Function	DAC Register Function
Н	Х	Н	Н	No effect	No effect	No effect
L	↑+	Н	Н	Data advanced 1 bit	No effect	No effect
↑+	L	н	н	No effect	Updated with SR contents ²	No effect
Н	Х	L	н	No effect	Latched with SR contents ²	All input register contents transferred ³
Н	Х	н	$\downarrow -$	No effect	Loaded with 0x00	Loaded with 0x00
Н	Х	Н	↑+	No effect	Latched with 0x00	Latched with 0x00

 1 \uparrow + positive logic transition; \downarrow - negative logic transition; X Don't Care.

² One input register receives the data bits D7-D0 decoded from the SR address bits (A1, A0), where REG A = (0, 0), B = (0, 1), C = (1, 0), and D = (1, 1).

³ LDAC is a level-sensitive input.

Table 5. AD7304 Serial Int	ut Register Data Format, Data is Loaded in MSB-First Fo	ormat


	MSB B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1	LSB BO
AD7304	SAC	SDC	A1	A0	D7	D6	D5	D4	D3	D2	D1	D0


If B11 (SAC), *Shutdown All Channels*, is set to logic low, all DACs are placed in a power shutdown mode, and all output voltages become high resistance. If B10 (SDC), *Shutdown Decoded Channel*, is set to logic low, only the DAC decoded by Address Bits A1 and A0 is placed in shutdown mode.

WR 1	A1	A0	LDAC ²	Input Register Function	DAC Register Function
L	L	L	Н	Register A loaded with DB0 to DB7	Latched with previous contents, no change
↑ +	L	L	н	Register A latched with DB0 to DB7	Latched with previous contents, no change
L	L	Н	н	Register B loaded with DB0 to DB7	Latched with previous contents, no change
1+	L	Н	н	Register B latched with DB0 to DB7	Latched with previous contents, no change
L	Н	L	н	Register C loaded with DB0 to DB7	Latched with previous contents, no change
1+	Н	L	Н	Register C latched with DB0 to DB7	Latched with previous contents, no change
L	Н	Н	н	Register D loaded with DB0 to DB7	Latched with previous contents, no change
1+	Н	Н	н	Register D latched with DB0 to DB7	Latched with previous contents, no change
Н	Х	Х	L	No effect	All input register contents loaded, register transparent
L	Х	Х	L	Input register x transparent to DB0 to DB7	Register transparent
Н	Х	Х	↑+	No effect	All input register contents latched
Н	Х	Х	н	No effect, device not selected	No effect, device not selected

Table 6. AD7305 Control Logic Truth Table

 1 <u>+ positive logic transition;</u> $\downarrow-$ negative logic transition; X don't care. 2 LDAC is a level-sensitive input.








Figure 7. AD7305 Timing Diagram Zoom In

PIN CONFIGURATIONS AND FUNCTION DESCRIPTIONS




Figure 8. AD7304 Pin Configuration

Table 7. AD7304 Pin Function Descriptions

Pin No.	Mnemonic	Description
1	VoutB	Channel B Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to VREFB pin. Output is open circuit when SHDN is enabled.
2	V _{OUT} A	Channel A Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to V _{REF} A pin. Output is open circuit when SHDN is enabled.
3	Vss	Negative Power Supply Input. Specified range of operation is 0 V to –5.5 V.
4	VREFA	Channel A Reference Input. Establishes V_{OUT} A full-scale voltage. Specified range of operation is $V_{SS} < V_{REF}A < V_{DD}$.
5	V _{REF} B	Channel B Reference Input. Establishes $V_{OUT}B$ full-scale voltage. Specified range of operation is $V_{SS} < V_{REF}B < V_{DD}$.
6	GND	Common Analog and Digital Ground.
7	LDAC	Load DAC Register Strobe, Active Low. Simultaneously transfers data from all four input registers into the corresponding DAC registers. Asynchronous active low input. DAC register is transparent when $\overline{\text{LDAC}} = 0$. See Table 4 for operation.
8	CLR	Clears All Input and DAC Registers to the Zero Condition. Asynchronous active low input. The serial register is not effected.
9	<u>cs</u>	Chip Select, Active Low Input. Disables shift register loading when high. Transfers serial input register data to the decoded input register when CS returns high. Does not effect LDAC operation.
10	CLK	Clock Input, Positive Edge Clocks Data into Shift Register. Disabled by chip select \overline{CS} .
11	SDI/SHDN	Serial Data Input Loads Directly into the Shift Register, MSB First. Hardware shutdown (SHDN) control input, active when pin is left floating by a three-state logic driver. Does not effect DAC register contents as long as power is present on VDD.
12	VREFD	Channel D Reference Input. Establishes V_{OUT} D full-scale voltage. Specified range of operation is $V_{SS} < V_{REF}$ D $< V_{DD}$.
13	VREFC	Channel C Reference Input. Establishes VourC full-scale voltage. Specified range of operation is Vss VREFC < VDD.
14	V _{DD}	Positive Power Supply Input. Specified range of operation is 2.7 V to 5.5 V.
15	VoutD	Channel D Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to V _{REF} D pin. Output is open circuit when SHDN is enabled.
16	VoutC	Channel C Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to VREFC pin. Output is open circuit when SHDN is enabled.




Figure 9. AD7305 Pin Configuration

Pin No.	Mnemonic	Description	
1	VoutB	Channel B Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to V _{REF} B pin. Output is open circuit when SHDN is enabled.	
2	VoutA	Channel A Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to V _{REF} A pin. Output is open circuit when SHDN is enabled.	
3	Vss	Negative Power Supply Input. Specified range of operation is 0 V to –5.5 V.	
4	V _{REF}	Channel B Reference Input. Establishes V_{OUT} full-scale voltage. Specified range of operation is $V_{SS} < V_{REF} < V_{DD}$.	
5	GND	Common Analog and Digital Ground.	
6	LDAC	Load DAC Register Strobe, Active Low. Simultaneously transfers data from all four input registers into the corresponding DAC registers. Asynchronous active low input. DAC register is transparent when LDAC = 0. See Table 6 for operation.	
7	DB7	MSB Digital Input Data Bit.	
8	DB6	Data Bit 6.	
9	DB5	Data Bit 5.	
10	DB4	Data Bit 4.	
11	DB3	Data Bit 3.	
12	DB2	Data Bit 2.	
13	DB1	Data Bit 1.	
14	DB0	LSB Digital Input Data Bit.	
15	WR	Write Data into Input Register Control Line, Active Low. See Table 6 for operation.	
16	A1	Address Bit 1.	
17	A0/SHDN	Address Bit 0/Hardware Shutdown (SHDN) Control Input, Active When Pin Is Left Floating by a Three-State Logic Driver. Does not effect DAC register contents as long as power is present on V _{DD} .	
18	V _{DD}	Positive Power Supply Input. Specified range of operation is 2.7 V to 5.5 V.	
19	V _{OUT} D	Channel D Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to V _{REF} D pin. Output is open circuit when SHDN is enabled.	
20	VoutC	Channel C Rail-to-Rail Buffered DAC Voltage Output. Full-scale set by reference voltage applied to VREFC pin. Output is open circuit when SHDN is enabled.	

TYPICAL PERFORMANCE CHARACTERISTICS




Figure 10. I_{OUT} Sink vs. V_{OUT} Rail-to-Rail Performance




Figure 11. Iout SOURCE vs. Vout Rail-to-Rail Performance




Figure 12. INL vs. Code, All DAC Channels




Figure 13. INL vs. Reference Input Voltage

01114-013

01114-014




Figure 14. DNL vs. Code






Figure 15. Zero-Scale Voltage vs. Temperature








Figure 17. Multiplying Mode Step Response and Output Slew Rate




Figure 18. Multiplying Mode Gain vs. Frequency




Figure 19. Time to Shutdown




Figure 20. Shutdown Recovery Time (Wakeup)




Figure 21. THD vs. Reference Input Amplitude




Figure 22. THD vs. Frequency




Figure 23. Output Noise Voltage Density vs. Frequency




Figure 24. Digital Feedthrough






Figure 25. Midscale Transition Glitch







01114-027

Figure 27. Power-Supply Rejection vs. Frequency

01114-026

01114-025

01114-024

01114-032




Figure 28. Supply Current vs. Digital Input Voltage




Figure 29. Shutdown Supply Current vs. Digital Input Voltage (A0 Only)




Figure 30. Supply Current vs. Temperature




Figure 31. Shutdown Supply Current vs. Temperature




Figure 32. Normalized TUE Drift Accelerated by Burn-In Hours of Operation @ 150℃

CIRCUIT OPERATION

The AD7304/AD7305 are 4-channel, 8-bit, voltage output DACs, differing primarily in digital logic interface and number of reference inputs. Both parts share the same internal DAC design and true rail-to-rail output buffers. The AD7304 contains four independent multiplying reference inputs, while the AD7305 has one common reference input. The AD7304 uses a 3-wire SPI-compatible serial data interface, while the AD7305 offers an 8-bit parallel data interface.

DAC SECTION

Each part contains four voltage-switched R-2R ladder DACs. Figure 33 shows a typical equivalent DAC. These DACs are designed to operate both single-supply or dual-supply, depending on whether the user supplies a negative voltage on the V_{SS} pin. In a single-supply application, the V_{SS} is tied to ground. In either mode, the DAC output voltage is determined by the V_{REF} input voltage and the digital data (D) loaded into the corresponding DAC register according to Equation 1.

$$V_{OUT} = V_{REF} D/256 \tag{1}$$

Note that the output full-scale polarity is the same as the V_{REF} polarity for dc reference voltages.




Figure 33. Typical Equivalent DAC Channel

These DACs are also designed to accommodate ac reference input signals. As long as the ac signals are maintained between $V_{SS} < V_{REF} < V_{DD}$, the user can expect 50 kHz of full power, multiplying bandwidth performance. In order to use negative input reference voltages, the V_{SS} pin must be biased with a negative voltage of equal or greater magnitude than the reference voltage.

The reference inputs are code dependent, exhibiting worst-case minimum resistance values specified in the parametric specification table. The DAC outputs VoutA, VoutB, VoutC, and VoutD are each capable of driving 2 k Ω loads in parallel with up to 500 pF loads. Output sink current and source current are shown in Figure 10 and Figure 11, respectively. The output slew rate is nominally 3.6 V/ μ s while operating from ±5 V supplies. The low output impedance of the buffers minimizes crosstalk between analog input channels. At 100 kHz, 65 dB of channelto-channel isolation exists (Figure 26). Output voltage noise is plotted in Figure 23. In order to maintain good analog performance, power supply bypassing of 0.01 μ F in parallel with 1 μ F is recommended. The true rail-to-rail capability of the AD7304/AD7305 allows the user to connect the reference inputs directly to the same supply as the V_{DD} or V_{SS} pin (Figure 34). Under these conditions, clean power supply voltages (low ripple, avoid switching supplies) appropriate for the application should be used.




Figure 34. Equivalent DAC Amplifier Output Circuit

AD7304 SERIAL DATA INTERFACE

The AD7304 uses a 3-wire $(\overline{\text{CS}}, \text{SDI}, \text{CLK})$ SPI-compatible serial data interface. New serial data is clocked into the serial input register in a 12-bit data-word format. MSB bits are loaded first.

Table 5 defines the 12 data-word bits. Data is placed on the SDI/SHDN pin and clocked into the register on the positive clock edge of CLK subject to the data setup and data hold time requirements specified in the Timing Specifications section. Data can only be clocked in while the $\overline{\text{CS}}$ chip select pin is active low. Only the last 12-bits clocked into the serial register are interrogated when the $\overline{\text{CS}}$ pin returns to the logic high state, extra data bits are ignored. Since most microcontrollers output serial data in 8-bit bytes, two right-justified data bytes can be written to the AD7304. Keeping the $\overline{\text{CS}}$ line low between the first and second byte transfer results in a successful serial register update.

Once the data is properly aligned in the shift register, the positive edge of the CS initiates either the transfer of new data to the target DAC register, determined by the decoding of Address Bits A1 and A0, or the shutdown features is activated based on the SAC or SDC bits. When either SAC or SDC pins are set (Logic 0), the loading of new data determined by Bits B9 to B0 are still loaded, but the results do not appear on the buffer outputs until the device is brought out of the shutdown state. The selected DAC output voltages become high impedance with a nominal resistance of 120 k $\Omega\,$ to ground, see Figure 34. If both the SAC and SDC pins are set, all channels are still placed in shutdown mode. When the AD7304 has been programmed into the power shutdown state, the present DAC register data is maintained as long as V_{DD} remains greater than 2.7 V. The remaining characteristics of the software serial interface are defined by Table 4, Table 5, and Figure 5.

Two additional pins, $\overline{\text{CLR}}$ and $\overline{\text{LDAC}}$, on the AD7304 provide hardware control over the clear function and the DAC register loading. If these functions are not needed, the $\overline{\text{CLR}}$ pin can be tied to logic high, and the $\overline{\text{LDAC}}$ pin can be tied to logic low. The asynchronous input $\overline{\text{CLR}}$ pin forces all input and DAC registers to the zero-code state. The asynchronous $\overline{\text{LDAC}}$ pin can be strobed to active low when all DAC registers need to be updated simultaneously from their respective input registers.

The LDAC pin places the DAC register in a transparent mode while in the logic low state.




Figure 35. AD7304 Equivalent Logic Interface

AD7304 HARDWARE SHUTDOWN SHDN

If a three-state driver is used on the SDI/SHDN pin, the AD7304 can be placed into a power shutdown mode when the SDI/ SHDN pin is placed in a high impedance state. For proper operation, no other termination voltages should be present on this pin. An internal window comparator detects when the logic voltage on the SHDN pin is between 28% and 36% of V_{DD} . A high impedance internal bias generator provides this voltage on the SHDN pin. The four DAC output voltages become high impedance with a nominal resistance of 120 k Ω to ground (see Figure 34 for an equivalent circuit).

AD7304/AD7305 POWER-ON RESET

When the V_{DD} power supply is turned on, an internal reset strobe forces all the input and DAC registers to the zero-code state. The V_{DD} power supply should have a monotonically increasing ramp in order to have consistent results, especially in the region of $V_{DD} = 1.5$ V to 2.3 V. The V_{SS} supply has no effect on the power-on reset performance. The DAC register data stays at zero until a valid serial register software load takes place. In the case of the double-buffered AD7305, the output DAC register can only be changed once the LDAC strobe is initiated.

POWER-UP SEQUENCE

It is recommended to power V_{DD}/V_{SS} first before applying any voltage to the reference terminals to avoid potential latch up. The ideal power-up sequence is in the following order: GND, V_{DD} , V_{SS} , Digital Inputs, and V_{REFx} . The order of powering digital inputs and reference inputs is not important as long as they are powered after V_{DD}/V_{SS} .

AD7305 PARALLEL DATA INTERFACE

The AD7305 has an 8-bit parallel interface DB7 = MSB, DB0 = LSB. Two address bits, A1 and A0, are decoded when an active low write strobe is placed on the \overline{WR} pin, see Table 6. The \overline{WR} is a level-sensitive input pin, therefore, the data setup and data hold times defined in the Timing Specifications section need to be adhered to.




Figure 36. AD7305 Equivalent Logic Interface

The $\overline{\text{LDAC}}$ pin provides the capability of simultaneously updating all DAC registers with new data from the input registers at the same time. This results in the analog outputs all changing to their new values at the same time. The $\overline{\text{LDAC}}$ pin is a level-sensitive input. If the simultaneous update feature is not required, the $\overline{\text{LDAC}}$ pin can be tied to logic low. When the LDAC is tied to Logic Low, the DAC registers become transparent and the input register data determines the DAC output voltage (see Figure 36 for an equivalent interface logic diagram).

AD7226 PIN COMPATIBILITY

By tying the $\overline{\text{LDAC}}$ pin to ground, the AD7305 has the same pin configuration and functionality as the AD7226, with the exception of a lower power supply operating voltage.

AD7305 HARDWARE SHUTDOWN SHDN

If a three-state driver is used on the A0/SHDN pin, the AD7305 can be placed into a power shutdown mode when the A0/SHDN pin is placed in a high impedance state. For proper operation, no other termination voltages should be present on this pin. An internal window comparator detects when the logic voltage on the SHDN pin is between 28% and 36% of V_{DD}. A high impedance, internal-bias generator provides this voltage on the SHDN pin. The four DAC output voltages become high impedance with a nominal resistance of 120 k Ω to ground.

ESD PROTECTION CIRCUITS

All logic input pins contain back-biased ESD protection Zeners connected to ground (GND). The V_{REF} pins also contain a back-biased ESD protection Zener connected to V_{DD} (see Figure 37).




Figure 37. Equivalent ESD Protection Circuits

APPLICATIONS

The AD7304/AD7305 are inherently 2-quadrant multiplying DACs. That is, they can easily be set up for unipolar output operation. The full-scale output polarity is the same as the reference input voltage polarity.

In some applications, it may be necessary to generate the full 4-quadrant multiplying capability or a bipolar output swing. This is easily accomplished using an external true rail-to-rail op amp, such as the OP295. Connecting the external amplifier with two equal value resistors, as shown in Figure 38, results in a full 4-quadrant multiplying circuit. In this circuit, the amplifier provides a gain of two, which increases the output span magnitude to 10 V. The transfer equation of this circuit shows that both negative and positive output voltages are created as the input data (D) is incremented from code zero ($V_{OUT} = -5 \text{ V}$) to midscale ($V_{OUT} = 0 \text{ V}$) to full scale ($V_{OUT} = +5 \text{ V}$).

$$V_{OUT} = \frac{D}{128 - 1} \times V_{REF} \tag{2}$$




Figure 38. 4-Quadrant Multiplying Application Circuit

OUTLINE DIMENSIONS




Figure 40. 20-Lead Standard Small Outline Package [SOIC] Wide Body (R-20) Dimensions shown in millimeters and (inches)




Figure 41. 16-Lead Thin Shrink Small Outline Package [TSSOP] (RU-16) Dimensions shown in millimeters




Figure 42. 20-Lead Thin Shrink Small Outline Package [TSSOP] (RU-20) Dimensions shown in millimeters

ORDERING GUIDE

Model	Temperature Range	Package Description	Package Options
AD7304BR	-40°C to +85°C	16-Lead SOIC	R-16
AD7304BR-REEL	-40°C to +85°C	16-Lead SOIC	R-16
AD7304BRZ ¹	-40°C to +85°C	16-Lead SOIC	R-16
AD7304BRZ-REEL ¹	-40°C to +85°C	16-Lead SOIC	R-16
AD7304YR	-40°C to +125°C	16-Lead SOIC	R-16
AD7304YRZ ¹	-40°C to +125°C	16-Lead SOIC	R-16
AD7304BRU	-40°C to +85°C	16-Lead TSSOP	RU-16
AD7304BRU-REEL7	-40°C to +85°C	16-Lead TSSOP	RU-16
AD7305BR	-40°C to +85°C	20-Lead SOIC	R-20
AD7305BR-REEL	-40°C to +85°C	20-Lead SOIC	R-20
AD7305YR	-40°C to +125°C	20-Lead SOIC	R-20
AD7305YR-REEL	–40°C to +125°C	20-Lead SOIC	R-20
AD7305BRU	-40°C to +85°C	20-Lead TSSOP	RU-20
AD7305BRU-REEL7	-40°C to +85°C	20-Lead TSSOP	RU-20
AD7305BRUZ ¹	-40°C to +85°C	20-Lead TSSOP	RU-20
AD7305BRUZ-REEL71	–40°C to +85°C	20-Lead TSSOP	RU-20

 1 Z = Pb-free part.

NOTES

© 2004 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective companies. Printed in the U.S.A. C01114-0-11/04(C)



www.analog.com

Rev. C | Page 20 of 20