# 8-Kb and 16-Kb SPI Serial CMOS EEPROM

#### **Description**

The CAT25080/25160 are 8–Kb/16–Kb Serial CMOS EEPROM devices internally organized as 1024x8/2048x8 bits. They feature a 32–byte page write buffer and support the Serial Peripheral Interface (SPI) protocol. The device is enabled through a Chip Select ( $\overline{\text{CS}}$ ) input. In addition, the required bus signals are a clock input (SCK), data input (SI) and data output (SO) lines. The  $\overline{\text{HOLD}}$  input may be used to pause any serial communication with the CAT25080/25160 device. These devices feature software and hardware write protection, including partial as well as full array protection.

#### **Features**

- 20 MHz SPI (5 V) Compatible
- 1.8 V to 5.5 V Supply Voltage Range
- SPI Modes (0,0) & (1,1)
- 32-byte Page Write Buffer
- Self-timed Write Cycle
- Hardware and Software Protection
- Block Write Protection
  - Protect 1/4, 1/2 or Entire EEPROM Array
- Low Power CMOS Technology
- 1,000,000 Program/Erase Cycles
- 100 Year Data Retention
- Industrial and Extended Temperature Range
- 8-lead PDIP, SOIC, TSSOP and 8-pad TDFN, UDFN Packages
- These Devices are Pb-Free, Halogen Free/BFR Free, and RoHS Compliant




Figure 1. Functional Symbol



## ON Semiconductor®

http://onsemi.com







SOIC-8 V SUFFIX CASE 751BD UDFN-8 HU2 SUFFIX CASE 517AW TDFN-8\* VP2 SUFFIX CASE 511AK








PDIP-8 L SUFFIX CASE 646AA TSSOP-8 Y SUFFIX CASE 948AL UDFN-8 HU4 SUFFIX CASE 517AZ

#### **PIN CONFIGURATION**



PDIP (L), SOIC (V), TSSOP (Y), TDFN\* (VP2), UDFN (HU2, HU4)

## PIN FUNCTION

Pin Name <sup>†</sup>	Function			
CS	Chip Select			
so	Serial Data Output			
WP	Write Protect			
V <sub>SS</sub>	Ground			
SI	Serial Data Input			
SCK	Serial Clock			
HOLD	Hold Transmission Input			
V <sub>CC</sub>	Power Supply			

<sup>†</sup>The exposed pad for the TDFN/UDFN packages can be left floating or connected to Ground.

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 18 of this data sheet.

1

<sup>\*</sup> Not recommended for new designs

#### **Table 1. ABSOLUTE MAXIMUM RATINGS**

Parameters	Ratings	Units
Operating Temperature	-45 to +130	°C
Storage Temperature	-65 to +150	°C
Voltage on any Pin with Respect to Ground (Note 1)	-0.5 to V <sub>CC</sub> + 0.5	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

#### Table 2. RELIABILITY CHARACTERISTICS (Note 2)

Symbol	Parameter	Min	Units
N <sub>END</sub> (Note 3)	Endurance	1,000,000	Program / Erase Cycles
T <sub>DR</sub>	Data Retention	100	Years

<sup>2.</sup> These parameters are tested initially and after a design or process change that affects the parameter according to appropriate AEC-Q100 and JEDEC test methods.

#### **Table 3. D.C. OPERATING CHARACTERISTICS**

 $(V_{CC} = 1.8 \text{ V to } 5.5 \text{ V}, T_A = -40^{\circ}\text{C to } +85^{\circ}\text{C} \text{ and } V_{CC} = 2.5 \text{ V to } 5.5 \text{ V}, T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C} \text{ unless otherwise specified.})$ 

Symbol	Parameter	Test Cond	ditions	Min	Max	Units
Icc	Supply Current	Read, Write, V <sub>CC</sub> = 5.0 V,	10 MHz / -40°C to +85°C		2	mA
		SO open	5 MHz / -40°C to +125°C		2	mA
I <sub>SB1</sub>	Standby Current	$V_{IN} = GND \text{ or } V_{CC}, \overline{CS} = V_{CC}, \overline{WP} = V_{CC}, V_{CC} = 5.0 \text{ V}$			2	μΑ
I <sub>SB2</sub>	Standby Current	$V_{IN} = GND \text{ or } V_{CC}, \overline{CS} = V_{CC},$	$T_A = -40^{\circ}\text{C to } +85^{\circ}\text{C}$		4	μΑ
		$\overline{\text{WP}} = \text{GND}, V_{\text{CC}} = 5.0 \text{ V}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$		5	μΑ
ΙL	Input Leakage Current	V <sub>IN</sub> = GND or V <sub>CC</sub>		-2	2	μΑ
I <sub>LO</sub>	Output Leakage	CS = V <sub>CC</sub> ,	$T_A = -40^{\circ}\text{C to } +85^{\circ}\text{C}$	-1	1	μΑ
	Current	$V_{OUT} = GND \text{ or } V_{CC}$	$T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C}$	-1	2	μΑ
V <sub>IL</sub>	Input Low Voltage			-0.5	0.3 V <sub>CC</sub>	V
V <sub>IH</sub>	Input High Voltage			0.7 V <sub>CC</sub>	V <sub>CC</sub> + 0.5	V
V <sub>OL1</sub>	Output Low Voltage	V <sub>CC</sub> > 2.5 V, I <sub>OL</sub> = 3.0 mA			0.4	V
V <sub>OH1</sub>	Output High Voltage	$V_{CC} > 2.5 \text{ V}, I_{OH} = -1.6 \text{ mA}$		V <sub>CC</sub> – 0.8 V		V
V <sub>OL2</sub>	Output Low Voltage	$V_{CC} > 1.8 \text{ V}, I_{OL} = 150 \mu\text{A}$			0.2	V
V <sub>OH2</sub>	Output High Voltage	$V_{CC} > 1.8 \text{ V}, I_{OH} = -100 \mu\text{A}$		V <sub>CC</sub> – 0.2 V		V

## Table 4. PIN CAPACITANCE (Note 2) ( $T_A = 25^{\circ}C$ , f = 1.0 MHz, $V_{CC} = +5.0$ V)

Symbol	Test	Conditions	Min	Тур	Max	Units
C <sub>OUT</sub>	Output Capacitance (SO)	V <sub>OUT</sub> = 0 V			8	pF
C <sub>IN</sub>	Input Capacitance (CS, SCK, SI, WP, HOLD)	V <sub>IN</sub> = 0 V			8	pF

<sup>1.</sup> The DC input voltage on any pin should not be lower than -0.5 V or higher than  $V_{CC} + 0.5$  V. During transitions, the voltage on any pin may undershoot to no less than -1.5 V or overshoot to no more than  $V_{CC} + 1.5$  V, for periods of less than 20 ns.

<sup>3.</sup> Page Mode,  $V_{CC} = 5 \text{ V}$ ,  $25^{\circ}\text{C}$ .

#### Table 5. A.C. CHARACTERISTICS - Mature Product

 $(T_A = -40^{\circ}C \text{ to } +85^{\circ}C \text{ (Industrial)} \text{ and } T_A = -40^{\circ}C \text{ to } +125^{\circ}C \text{ (Extended))}$  (Notes 4, 7)

			V – 5.5 V		5 V – 5.5 V C to +85°C	
Symbol	Parameter	Min	Max	Min	Max	Units
f <sub>SCK</sub>	Clock Frequency	DC	5	DC	10	MHz
t <sub>SU</sub>	Data Setup Time	40		20		ns
t <sub>H</sub>	Data Hold Time	40		20		ns
t <sub>WH</sub>	SCK High Time	75		40		ns
t <sub>WL</sub>	SCK Low Time	75		40		ns
t <sub>LZ</sub>	HOLD to Output Low Z		50		25	ns
t <sub>RI</sub> (Note 5)	Input Rise Time		2		2	μs
t <sub>FI</sub> (Note 5)	Input Fall Time		2		2	μs
t <sub>HD</sub>	HOLD Setup Time	0		0		ns
t <sub>CD</sub>	HOLD Hold Time	10		10		ns
t <sub>V</sub>	Output Valid from Clock Low		75		40	ns
t <sub>HO</sub>	Output Hold Time	0		0		ns
t <sub>DIS</sub>	Output Disable Time		50		20	ns
t <sub>HZ</sub>	HOLD to Output High Z		100		25	ns
t <sub>CS</sub>	CS High Time	50		20		ns
t <sub>CSS</sub>	CS Setup Time	20		15		ns
t <sub>CSH</sub>	CS Hold Time	30		20		ns
t <sub>CNS</sub>	CS Inactive Setup Time	20		15		ns
t <sub>CNH</sub>	CS Inactive Hold Time	20		15		ns
t <sub>WPS</sub>	WP Setup Time	10		10		ns
t <sub>WPH</sub>	WP Hold Time	100		60		ns
t <sub>WC</sub> (Note 6)	Write Cycle Time		5		5	ms

4. AC Test Conditions:

Input Pulse Voltages: 0.3  $V_{CC}$  to 0.7  $V_{CC}$ 

Input rise and fall times: ≤ 10 ns

Input and output reference voltages: 0.5  $V_{CC}$ Output load: current source  $I_{OL\ max}/I_{OH\ max}$ ;  $C_L = 50\ pF$ 

- 5. This parameter is tested initially and after a design or process change that affects the parameter.
- 6. t<sub>WC</sub> is the time from the rising edge of CS after a valid write sequence to the end of the internal write cycle.
- 7. All Chip Select (CS) timing parameters are defined relative to the positive clock edge (Figure 2). tcsH timing specification is valid for die revision C and higher. The die revision C is identified by letter "C" or a dedicated marking code on top of the package. For previous product revision (Rev. B) the t<sub>CSH</sub> is defined relative to the negative clock edge.

Table 6. POWER-UP TIMING (Notes 5, 8)

Symbol	Parameter	Max	Units
t <sub>PUR</sub>	Power-up to Read Operation	1	ms
t <sub>PUW</sub>	Power-up to Write Operation	1	ms

8. t<sub>PUR</sub> and t<sub>PUW</sub> are the delays required from the time V<sub>CC</sub> is stable until the specified operation can be initiated.

#### Table 7. A.C. CHARACTERISTICS – New Product (Rev D)

 $(T_A = -40^{\circ}\text{C to } +85^{\circ}\text{C (Industrial)} \text{ and } T_A = -40^{\circ}\text{C to } +125^{\circ}\text{C (Extended)}, \text{ unless otherwise specified.)}$  (Note 9)

		V <sub>CC</sub> = 1.8 -40°C t	V <sub>CC</sub> = 1.8 V - 5.5 V -40°C to +85°C		V <sub>CC</sub> = 2.5 V - 5.5 V -40°C to +125°C		V <sub>CC</sub> = 4.5 V - 5.5 V -40°C to +85°C	
Symbol	Parameter	Min	Max	Min	Max	Min	Max	Units
f <sub>SCK</sub>	Clock Frequency	DC	5	DC	10	DC	20	MHz
t <sub>SU</sub>	Data Setup Time	20		10		5		ns
t <sub>H</sub>	Data Hold Time	20		10		5		ns
t <sub>WH</sub>	SCK High Time	75		40		20		ns
$t_WL$	SCK Low Time	75		40		20		ns
$t_LZ$	HOLD to Output Low Z		50		25		25	ns
t <sub>RI</sub> (Note 10)	Input Rise Time		2		2		2	μs
t <sub>FI</sub> (Note 10)	Input Fall Time		2		2		2	μs
t <sub>HD</sub>	HOLD Setup Time	0		0		0		ns
t <sub>CD</sub>	HOLD Hold Time	10		10		5		ns
$t_V$	Output Valid from Clock Low		70		35		20	ns
t <sub>HO</sub>	Output Hold Time	0		0		0		ns
t <sub>DIS</sub>	Output Disable Time		50		20		20	ns
t <sub>HZ</sub>	HOLD to Output High Z		100		25		25	ns
t <sub>CS</sub>	CS High Time	80		40		20		ns
t <sub>CSS</sub>	CS Setup Time	30		30		15		ns
t <sub>CSH</sub>	CS Hold Time	30		30		20		ns
t <sub>CNS</sub>	CS Inactive Setup Time	20		20		15		ns
t <sub>CNH</sub>	CS Inactive Hold Time	20		20		15		ns
t <sub>WPS</sub>	WP Setup Time	10		10		10		ns
t <sub>WPH</sub>	WP Hold Time	10		10		10		ns
t <sub>WC</sub> (Note 12)	Write Cycle Time		5		5		5	ms

#### Table 8. POWER-UP TIMING (Notes 10, 11)

Symbol	Parameter		Max	Units
t <sub>PUR</sub>	Power-up to Read Operation		1	ms
t <sub>PUW</sub>	Power-up to Write Operation		1	ms

#### 9. AC Test Conditions:

Input Pulse Voltages: 0.3  $V_{CC}$  to 0.7  $V_{CC}$ 

Input rise and fall times: ≤ 10 ns

Input and output reference voltages: 0.5 V<sub>CC</sub>
Output load: current source I<sub>OL max</sub>/I<sub>OH max</sub>; C<sub>L</sub> = 30 pF

- 10. This parameter is tested initially and after a design or process change that affects the parameter.
- 11. t<sub>PUR</sub> and t<sub>PUW</sub> are the delays required from the time V<sub>CC</sub> is stable at the operating voltage until the specified operation can be initiated.
- $12.t_{WC}$  is the time from the rising edge of  $\overline{CS}$  after a valid write sequence to the end of the internal write cycle.

#### **Pin Description**

SI: The serial data input pin accepts op-codes, addresses and data. In SPI modes (0,0) and (1,1) input data is latched on the rising edge of the SCK clock input.

**SO:** The serial data output pin is used to transfer data out of the device. In SPI modes (0,0) and (1,1) data is shifted out on the falling edge of the SCK clock.

**SCK:** The serial clock input pin accepts the clock provided by the host and used for synchronizing communication between host and CAT25080/160.

 $\overline{\text{CS}}$ : The chip select input pin is used to enable/disable the CAT25080/160. When  $\overline{\text{CS}}$  is high, the SO output is tri-stated (high impedance) and the device is in Standby Mode (unless an internal write operation is in progress). Every communication session between host and CAT25080/160 must be preceded by a high to low transition and concluded with a low to high transition of the  $\overline{\text{CS}}$  input.

 $\overline{\text{WP}}$ : The write protect input pin will allow all write operations to the device when held high. When  $\overline{\text{WP}}$  pin is tied low and the WPEN bit in the Status Register (refer to Status Register description, later in this Data Sheet) is set to "1", writing to the Status Register is disabled.

HOLD: The HOLD input pin is used to pause transmission between host and CAT25080/160, without having to retransmit the entire sequence at a later time. To pause, HOLD must be taken low and to resume it must be taken back high, with the SCK input low during both transitions.

When not used for pausing, the  $\overline{HOLD}$  input should be tied to  $V_{CC}$ , either directly or through a resistor.

#### **Functional Description**

The CAT25080/160 devices support the Serial Peripheral Interface (SPI) bus protocol, modes (0,0) and (1,1). The device contains an 8-bit instruction register. The instruction set and associated op-codes are listed in Table 9.

Reading data stored in the CAT25080/160 is accomplished by simply providing the READ command and an address. Writing to the CAT25080/160, in addition to a WRITE command, address and data, also requires enabling the device for writing by first setting certain bits in a Status Register, as will be explained later.

After a high to low transition on the  $\overline{\text{CS}}$  input pin, the CAT25080/160 will accept any one of the six instruction op-codes listed in Table 9 and will ignore all other possible 8-bit combinations. The communication protocol follows the timing from Figure 2.

**Table 9. INSTRUCTION SET** 

Instruction	Opcode	Operation
WREN	0000 0110	Enable Write Operations
WRDI	0000 0100	Disable Write Operations
RDSR	0000 0101	Read Status Register
WRSR	0000 0001	Write Status Register
READ	0000 0011	Read Data from Memory
WRITE	0000 0010	Write Data to Memory




Figure 2. Synchronous Data Timing

#### **Status Register**

The Status Register, as shown in Table 10, contains a number of status and control bits.

The  $\overline{RDY}$  (Ready) bit indicates whether the device is busy with a write operation. This bit is automatically set to 1 during an internal write cycle, and reset to 0 when the device is ready to accept commands. For the host, this bit is read only.

The WEL (Write Enable Latch) bit is set/reset by the WREN/WRDI commands. When set to 1, the device is in a

Write Enable state and when set to 0, the device is in a Write Disable state.

The BP0 and BP1 (Block Protect) bits determine which blocks are currently write protected. They are set by the user with the WRSR command and are non-volatile. The user is allowed to protect a quarter, one half or the entire memory, by setting these bits according to Table 11. The protected blocks then become read-only.

#### **Table 10. STATUS REGISTER**

7	6	5	4	3	2	1	0
WPEN	0	0	0	BP1	BP0	WEL	RDY

## **Table 11. BLOCK PROTECTION BITS**

Status Re	gister Bits			
BP1	BP0	Array Address Protected	Protection	
0	0	None	No Protection	
0	1	25080: 0300-03FF 25160: 0600-07FF	Quarter Array Protection	
1	0	25080: 0200-03FF 25160: 0400-07FF	Half Array Protection	
1	1	25080: 0000-03FF 25160: 0000-07FF	Full Array Protection	

## **Table 12. WRITE PROTECT CONDITIONS**

WPEN	WP	WEL	Protected Blocks	Unprotected Blocks	Status Register
0	Х	0	Protected	Protected	Protected
0	Х	1	Protected	Writable	Writable
1	Low	0	Protected	Protected	Protected
1	Low	1	Protected	Writable	Protected
Х	High	0	Protected	Protected	Protected
Х	High	1	Protected	Writable	Writable

#### WRITE OPERATIONS


The CAT25080/160 device powers up into a write disable state. The device contains a Write Enable Latch (WEL) which must be set before attempting to write to the memory array or to the status register. In addition, the address of the memory location(s) to be written must be outside the protected area, as defined by BP0 and BP1 bits from the status register.

#### Write Enable and Write Disable

The internal Write Enable Latch and the corresponding Status Register WEL bit are set by sending the WREN

instruction to the CAT25080/160. Care must be taken to take the  $\overline{\text{CS}}$  input high after the WREN instruction, as otherwise the Write Enable Latch will not be properly set. WREN timing is illustrated in Figure 3. The WREN instruction must be sent prior to any WRITE or WRSR instruction.

The internal write enable latch is reset by sending the WRDI instruction as shown in Figure 4. Disabling write operations by resetting the WEL bit, will protect the device against inadvertent writes.



#### **Byte Write**

Once the WEL bit is set, the user may execute a write sequence, by sending a WRITE instruction, a 16-bit address and data as shown in Figure 5. Only 10 significant address bits are used by the CAT25080 and 11 by the CAT25160. The rest are don't care bits, as shown in Table 13. Internal programming will start after the low to high  $\overline{\text{CS}}$  transition. During an internal write cycle, all commands, except for RDSR (Read Status Register) will be ignored. The  $\overline{\text{RDY}}$  bit will indicate if the internal write cycle is in progress  $\overline{\text{RDY}}$  high), or the device is ready to accept commands  $\overline{\text{RDY}}$  low).

#### **Page Write**

After sending the first data byte to the CAT25080/160, the host may continue sending data, up to a total of 32 bytes, according to timing shown in Figure 6. After each data byte, the lower order address bits are automatically incremented, while the higher order address bits (page address) remain unchanged. If during this process the end of page is exceeded, then loading will "roll over" to the first byte in the page, thus possibly overwriting previously loaded data. Following completion of the write cycle, the CAT25080/160 is automatically returned to the write disable state.

**Table 13. BYTE ADDRESS** 

Device	Address Significant Bits	Address Don't Care Bits	# Address Clock Pulse	
CAT25080	A9 – A0	A15 – A10	16	
CAT25160	A10 – A0	A15 – A11	16	




Figure 6. Page WRITE Timing

#### Write Status Register

The Status Register is written by sending a WRSR instruction according to timing shown in Figure 7. Only bits 2, 3 and 7 can be written using the WRSR command.

#### **Write Protection**

The Write Protect  $(\overline{WP})$  pin can be used to protect the Block Protect bits BP0 and BP1 against being inadvertently altered. When  $\overline{WP}$  is low and the WPEN bit is set to "1", write operations to the Status Register are inhibited.  $\overline{WP}$  going low while  $\overline{CS}$  is still low will interrupt a write to the status register. If the internal write cycle has already been initiated,  $\overline{WP}$  going low will have no effect on any write operation to the Status Register. The  $\overline{WP}$  pin function is blocked when the WPEN bit is set to "0". The  $\overline{WP}$  input timing is shown in Figure 8.




Figure 7. WRSR Timing




Figure 8. WP Timing

#### **READ OPERATIONS**

#### **Read from Memory Array**

To read from memory, the host sends a READ instruction followed by a 16-bit address (see Table 13 for the number of significant address bits).

After receiving the last address bit, the CAT25080/160 will respond by shifting out data on the SO pin (as shown in Figure 9). Sequentially stored data can be read out by simply continuing to run the clock. The internal address pointer is automatically incremented to the next higher address as data is shifted out. After reaching the highest memory address, the address counter "rolls over" to the lowest memory address, and the read cycle can be continued indefinitely. The read operation is terminated by taking  $\overline{\text{CS}}$  high.

#### **Read Status Register**

To read the status register, the host simply sends a RDSR command. After receiving the last bit of the command, the CAT25080/160 will shift out the contents of the status register on the SO pin (Figure 10). The status register may be read at any time, including during an internal write cycle.

While the internal write cycle is in progress, the RDSR command will output the full content of the status register (New product, Rev. D) or the RDY (Ready) bit only (i.e., data out = FFh) for previous product revision C (Mature product). For easy detection of the internal write cycle completion, both during writing to the memory array and to the status register, we recommend sampling the RDY bit only through the polling routine. After detecting the RDY bit "0", the next RDSR instruction will always output the expected content of the status register.




Figure 9. READ Timing




Figure 10. RDSR Timing

#### **Hold Operation**

The HOLD input can be used to pause communication between host and CAT25080/160. To pause, HOLD must be taken low while SCK is low (Figure 11). During the hold condition the device must remain selected (CS low). During the pause, the data output pin (SO) is tri-stated (high impedance) and SI transitions are ignored. To resume communication, HOLD must be taken high while SCK is low.

#### **Design Considerations**

The CAT25080/160 devices incorporate Power–On Reset (POR) circuitry which protects the internal logic against powering up in the wrong state. The device will power up into Standby mode after  $V_{\rm CC}$  exceeds the POR trigger level and will power down into Reset mode when  $V_{\rm CC}$  drops

below the POR trigger level. This bi-directional POR behavior protects the device against 'brown-out' failure following a temporary loss of power.

The CAT25080/160 device powers up in a write disable state and in a low power standby mode. A WREN instruction must be issued prior to any writes to the device.

After power up, the  $\overline{\text{CS}}$  pin must be brought low to enter a ready state and receive an instruction. After a successful byte/page write or status register write, the device goes into a write disable mode. The  $\overline{\text{CS}}$  input must be set high after the proper number of clock cycles to start the internal write cycle. Access to the memory array during an internal write cycle is ignored and programming is continued. Any invalid op–code will be ignored and the serial output pin (SO) will remain in the high impedance state.





Figure 11. HOLD Timing


## **PACKAGE DIMENSIONS**


PDIP-8, 300 mils CASE 646AA-01 ISSUE A



SYMBOL	MIN	NOM	MAX
Α			5.33
A1	0.38		
A2	2.92	3.30	4.95
b	0.36	0.46	0.56
b2	1.14	1.52	1.78
С	0.20	0.25	0.36
D	9.02	9.27	10.16
Е	7.62	7.87	8.25
E1	6.10	6.35	7.11
е	2.54 BSC		
eB	7.87		10.92
L	2.92	3.30	3.80

## **TOP VIEW**






SIDE VIEW END VIEW

- (1) All dimensions are in millimeters.
- (2) Complies with JEDEC MS-001.


## **PACKAGE DIMENSIONS**

SOIC 8, 150 mils CASE 751BD-01 ISSUE O




SYMBOL	MIN	NOM	MAX
Α	1.35		1.75
A1	0.10		0.25
b	0.33		0.51
С	0.19		0.25
D	4.80		5.00
E	5.80		6.20
E1	3.80		4.00
е	1.27 BSC		
h	0.25		0.50
L	0.40		1.27
θ	0°		8°

**TOP VIEW** 



SIDE VIEW




**END VIEW** 

- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Complies with JEDEC MS-012.


## **PACKAGE DIMENSIONS**

## TSSOP8, 4.4x3 CASE 948AL-01 ISSUE O




SYMBOL	MIN	NOM	MAX
Α			1.20
A1	0.05		0.15
A2	0.80	0.90	1.05
b	0.19		0.30
С	0.09		0.20
D	2.90	3.00	3.10
Е	6.30	6.40	6.50
E1	4.30	4.40	4.50
е	0.65 BSC		
L	1.00 REF		
L1	0.50	0.60	0.75
θ	0°		8°

## **TOP VIEW**




SIDE VIEW



- (1) All dimensions are in millimeters. Angles in degrees.(2) Complies with JEDEC MO-153.


# PACKAGE DIMENSIONS

TDFN8, 2x3 CASE 511AK-01 ISSUE A



TOP VIEW	SIDE VIEW	BOTTOM VIEW

SYMBOL	MIN	NOM	MAX
Α	0.70	0.75	0.80
A1	0.00	0.02	0.05
A2	0.45	0.55	0.65
АЗ	0.20 REF		
b	0.20	0.25	0.30
D	1.90	2.00	2.10
D2	1.30	1.40	1.50
E	2.90	3.00	3.10
E2	1.20	1.30	1.40
е	0.50 TYP		
L	0.20	0.30	0.40





FRONT VIEW


- (1) All dimensions are in millimeters.
- (2) Complies with JEDEC MO-229.

# PACKAGE DIMENSIONS

UDFN8, 2x2 CASE 517AW-01 ISSUE O








**TOP VIEW** 

SIDE VIEW

**BOTTOM VIEW** 

SYMBOL	MIN	NOM	MAX
Α	0.45	0.50	0.55
A1	0.00	0.02	0.05
b	0.18	0.25	0.30
D	1.90	2.00	2.10
D2	1.50	1.60	1.70
Е	1.90	2.00	2.10
E2	0.80	0.90	1.00
е	0.50 BSC		
L	0.20	0.30	0.45




**DETAIL A** 


- (1) All dimensions are in millimeters.
- (2) Complies with JEDEC MO-229.


#### **PACKAGE DIMENSIONS**

## **UDFN8, 2x3 EXTENDED PAD**

CASE 517AZ-01 ISSUE O








**TOP VIEW** 

SIDE VIEW


**BOTTOM VIEW** 

SYMBOL	MIN	NOM	MAX
Α	0.45	0.50	0.55
A1	0.00	0.02	0.05
А3	0.127 REF		
b	0.20	0.25	0.30
D	1.95	2.00	2.05
D2	1.35	1.40	1.45
Е	2.95	3.00	3.05
E2	1.25	1.30	1.35
е	0.50 REF		
L	0.25	0.30	0.35

- (1) All dimensions are in millimeters.
- (2) Refer JEDEC MO-236/MO-252.



**FRONT VIEW** 



**DETAIL A** 

#### ORDERING INFORMATION (Notes 13 - 16)

Device Order Number	Specific Device Marking*	Package Type	Temperature Range	Lead Finish	Shipping (Note 18)
CAT25080HU2I-GT3	S3	UDFN8	I = Industrial (-40°C to +85°C)	NiPdAu	
CAT25080HU2E-GT3	S3	UDFN8	E = Extended (-40°C to +125°C)	NiPdAu	Tape & Reel,
CAT25080HU4I-GT3	S3U	UDFN8-EP	I = Industrial (-40°C to +85°C)	NiPdAu	3,000 Units / Reel
CAT25080HU4E-GT3	S3U	UDFN8-EP	E = Extended (-40°C to +125°C)	NiPdAu	
CAT25080LI-G	25080D	PDIP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tuba 50 Unita / Tuba
CAT25080LE-G	25080D	PDIP-8	E = Extended (-40°C to +125°C)	NiPdAu	Tube, 50 Units / Tube
CAT25080VI-GT3	25080D	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	
CAT25080VE-GT3	25080D	SOIC-8, JEDEC	E = Extended (-40°C to +125°C)	NiPdAu	
CAT25080VP2I-GT3 (Note 17)	S3T	TDFN-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel,
CAT25080VP2E-GT3 (Note 17)	S3T	TDFN-8	E = Extended (-40°C to +125°C)	NiPdAu	3,000 Units / Reel
CAT25080YI-GT3	S08D	TSSOP-8	I = Industrial (-40°C to +85°C)	NiPdAu	
CAT25080YE-GT3	S08D	TSSOP-8	E = Extended (-40°C to +125°C)	NiPdAu	
				•	
CAT25160HU2I-GT3	S4	UDFN8	I = Industrial (-40°C to +85°C)	NiPdAu	
CAT25160HU2E-GT3	S4	UDFN8	E = Extended (-40°C to +125°C)	NiPdAu	Tape & Reel,
CAT25160HU4I-GT3	S4U	UDFN8-EP	I = Industrial (-40°C to +85°C)	NiPdAu	3,000 Units / Reel
CAT25160HU4E-GT3	S4U	UDFN8-EP	E = Extended (-40°C to +125°C)	NiPdAu	
CAT25160LI-G	25160D	PDIP-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tuba 50 Unita / Tuba
CAT25160LE-G	25160D	PDIP-8	E = Extended (-40°C to +125°C)	NiPdAu	Tube, 50 Units / Tube
CAT25160VI-GT3	25160D	SOIC-8, JEDEC	I = Industrial (-40°C to +85°C)	NiPdAu	
CAT25160VE-GT3	25160D	SOIC-8, JEDEC	E = Extended (-40°C to +125°C)	NiPdAu	
CAT25160VP2I-GT3 (Note 17)	S4T	TDFN-8	I = Industrial (-40°C to +85°C)	NiPdAu	Tape & Reel,
CAT25160VP2E-GT3 (Note 17)	S4T	TDFN-8	E = Extended (-40°C to +125°C)	NiPdAu	3,000 Units / Reel
CAT25160YI-GT3	S16D	TSSOP-8	I = Industrial (-40°C to +85°C)	NiPdAu	
CAT25160YE-GT3	S16D	TSSOP-8	E = Extended (-40°C to +125°C)	NiPdAu	

<sup>13.</sup> All packages are RoHS-compliant (Lead-free, Halogen-free).

<sup>14.</sup> The standard lead finish is NiPdAu.

<sup>15.</sup> For detailed information and a breakdown of device nomenclature and numbering systems, please see the ON Semiconductor Device Nomenclature document, TND310/D, available at <a href="https://www.onsemi.com">www.onsemi.com</a>

<sup>16.</sup> For additional package and temperature options, please contact your nearest ON Semiconductor Sales office.

<sup>17.</sup> Not recommended for new design

<sup>18.</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

<sup>\*</sup> Marking for New Product (Rev D)

ON Semiconductor and was registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any licenses under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportuni

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Europe, Middle East and Africa Technical Support Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

CAT25080/D