

200 mW LL-34 Hermetically Sealed Glass Fast Switching Schottky Barrier Diode



Absolute Maximum Ratings T_A = 25°C unless otherwise noted

Symbol	Parameter	Value	Units
P _D	Power Dissipation	200	mW
T _{STG}	Storage Temperature Range	-65 to +125	°C
TJ	Operating Junction Temperature	+125	°C
V _{RRM}	Repetitive Peak Reverse Voltage	30	V
V _R	Maximum DC Blocking Voltage	30	V
I _{F(AV)}	Average Forward Rectified Current	200	mA
I _{FSM}	Peak Forward Surge Current	4	Α

DEVICE MARKING DIAGRAM



Cathode Band Color: Black

These ratings are limiting values above which the serviceability of the diode may be impaired.

Specification Features:

- Low Forward Voltage Drop
- LL-34 Package (JEDEC)
- Through-Hole Device Type Mounting
- Hermetically Sealed Glass
- Compression Bonded Construction
- All External Surfaces Are Corrosion Resistant And Leads Are Readily Solderable
- RoHS Compliant
- Solder Hot Dip Tin (Sn) Lead Finish

Cathode Anode

ELECTRICAL SYMBOL

Electrical Characteristics $T_A = 25$ °C unless otherwise noted

Symbol	Parameter	Test Condition	Limits			Unit
			Min	Тур	Max	Onit
B _V	Breakdown Voltage	I _R =10μA	30			Volts
I _R	Reverse Leakage Current	V _R =25V			2	uA
V _F	Forward Voltage	I _F =0.1mA			0.24	
		I _F =1mA			0.32	
		I _F =10mA			0.40	Volts
		I _F =30mA			0.50	
		I _F =100mA			0.80	
T _{RR}	Reverse Recovery Time	I _F =I _R =10mA				
		R _L =100Ω		5		nS
		I _{RR} =1mA				
С	Capacitance	V _R =1V, f=1M _{HZ}		7	10	pF

Number: DB-095 Jan, 2011 / B





Package Outline

Package		Case Outline				
	← B →			LL	-34	
		DIM	Millimeters		Inches	
LL34	A		Min	Max	Min	Max
LLOT		Α	3.30	3.60	0.130	0.142
	→	В	1.40	1.50	0.055	0.059
	<u> </u>	С	0.35	0.50	0.014	0.020

Notes:

- All dimensions are within DO213AC JEDEC standard.
 LL-34 polarity denoted by cathode band.





NOTICE

The information presented in this document is for reference only. Tak Cheong reserves the right to make changes without notice for the specification of the products displayed herein.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Tak Cheong Semiconductor Co., Ltd., or anyone on its behalf, assumes no responsibility or liability for any damagers resulting from such improper use of sale.

This publication supersedes & replaces all information reviously supplied. For additional information, please visit our website http://www.takcheong.com, or consult your nearest Tak Cheong's sales office for further assistance.

Number: DB-100 April 14, 2008 / A