

Power Cord, Locking C19 to CEE/7 Schuko, 3.0m

AP8755

Call for More Information 0800 2799254



- Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Output	
Nominal Output Voltage	240V
Cord Length	3.1meters
Maximum Total Current Draw	16
Output Connections	(1) IEC 60320 C19

Input	
Input Connections	Schuko CEE 7/7P
Cord Length	3meters
Number of Power Cords	1
Maximum Input Current	16A
Maximum Line Current	16A

Physical	
Maximum Height	230MM, 23.0CM
Maximum Width	230MM, 23.0CM
Maximum Depth	45MM, 4.5CM
Net Weight	0.42KG
Shipping weight	0.42KG
Shipping Height	230MM, 23.0CM
Shipping Width	230MM, 23.0CM
Shipping Depth	45MM, 4.5CM
Color	Black

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Power Cord, Locking C19 to CEE/7 Schuko, 3.0m | AP8755 | Downloaded on 02/25/2022 (EST)

Physical	
Units per Pallet	600.0

Environmental	
Operating Temperature	0 - 70 °C
Operating Relative Humidity	20 - 80 %
Operating Elevation	0 - 3048meters
Storage Temperature	-20 - 70 °C
Storage Relative Humidity	20 - 80 %
Storage Elevation	0 - 15240meters

Conformance	
Approvals	VDE
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.