

TWN4 PALON COMPACT PANEL LIGHT

RFID READER/WRITER SUPPORTING LF, HF AND NFC FOR PANEL MOUNT



(exemplary illustration)

TWN4 Palon Compact Panel Light is a versatile panel mount reader for integration into third-party products and devices. It supports enhanced interfaces, especially RS-485, and inherits all advantages and integrated tool support of the ELATEC TWN4 family. The IP65 protected housing is easy to install.

TWN4 Palon Compact Panel Light is a multi-technology reader/writer family supporting almost all 125 kHz and 13.56 MHz contactless technologies, including NFC. On-board antennas for HF and LF allow excellent contactless performance.

Special features:

- + Optimized housing design for easy, fast and secure installation
- + Integrated LF and HF antennas
- One on-board SAM socket (Secure Access Module)
- + Interfaces: RS-485, Wiegand or Clock/Data. OSDP protocol optionally, USB
- + Supports quick (re)configuration over network and over wireless interface with TWN4 CONFIG Card
- Direct chip-commands support
- + Firmware update in the field possible
- Powerful SDK for writing apps which are executed directly on the reader
- + On-board 18 kB flash storage, e.g. for storing user accessible non-volatile data
- + TWN4 Upgrade Card for P and PI options available on request
- + 3D construction data (STEP) available on request





































TECHNICAL DATA


405 H.L. /LEV / 40 FC MIL. /LIEV
125 kHz (LF) / 13.56 MHz (HF)
Integrated
Transparent Polycarbonate (PC) housing, black PC outer mounting ring. TWN4 Palon
Compact M Light reader module pre-installed. ABS locknut M63 x 1.5, black or grey, pre-
installed design inlay (customizable). For mounting hole diameter 63.2 mm with anti-twist
protection
82 mm x 82 mm x 34.2 mm / 3.23 inch x 3.23 inch x 1.35 inch
9.0 V - 30 V via connector X1; 4.3 V - 5.5 V via micro USB
Limited power source according to the safety norms listed in the respective declaration of
conformity, short-circuit current < 8 A
Operating: typ. 160 mA @12 V; Idle: typ. 50 mA @12 V; Peak typ. 250 mA @12 V
Operating: -25 °C up to +80 °C (-13 °F up to +176 °F)
Storage: -40 °C up to +85 °C (-40 °F up to +185 °F)
IP65 protected housing (frontside, when mounted)
5% to 95% non-condensing (inner electronic components)
Up to 100 mm / 4 inch, depending on OEM environment and transponder
USB keyboard emulation – USB virtual COM port – CCID / PC/SC 2.01
·
500,000 hours (electronic components)
Approx. 77 g / 2.72 oz
Infrared tamper detector, front facing
PCB terminal block, 8 positions, push-in spring connection for wires 0.2 to 0.5 mm ² / AWG
24 to 20, tool-free cable wiring
8 position DIP switch for RS-485: addressing, speed settings, line termination
Center RGB LED; acoustic loudspeaker
ISO14443A: LEGIC Advant ¹⁾ , MIFARE Classic EV1 ²⁾ , MIFARE Classic, MIFARE Mini, MIFARE DESFire EV1, MIFARE DESFire EV2 ³⁾ , MIFARE DESFire Light ⁴⁾ , MIFARE Plus S, X, MIFARE Pro X ⁵⁾ , MIFARE Smart MX ⁵⁾ , MIFARE Ultralight, MIFARE Ultralight C, MIFARE Ultralight EV1 ²⁾ , NTAG2xx, SLE44R35 ⁵⁾ , SLE66Rxx (my-d move) ⁵⁾ , Topaz ISO18092 ECMA-340: NFC Forum Tag 1-5, NFC Peer-to-Peer, Sony FeliCa ⁶⁾ , NFC Active and passive communication mode ISO14443B: Calypso ⁵⁾ , Calypso Innovatron protocol ⁵⁾ , CEPAS ⁵⁾ , HID iCLASS ¹⁾ , Moneo ⁵⁾ , Pico Pass ⁷⁾ , SRI4K, SRIX4K, SRI512, SRT512 ISO15693: EM4x33 ⁵⁾ , EM4x35 ⁵⁾ , HID iCLASS ¹⁾ , HID iCLASS SE/SR ¹⁾ , ICODE SLI, LEGIC Advant ¹⁾ , M24LR16/64, MB89R118/119, SRF55Vxx (my-d vicinity) ⁵⁾ , Tag-it, PicoPass ⁷⁾
AWID, Cardax, CASI-RUSCO, Deister ⁹), EM4100, 4102, 4200 ¹⁰), EM4050, 4150, 4450, 4550, EM4305 ¹¹), FDX-B ¹²), EM4105 ¹²), UltraProx ¹²), HITAG 1 ¹³), HITAG 2 ¹³), HITAG S ¹³), ICT ⁴), IDTECK, Isonas, Keri, Miro, Nedap ⁹), PAC ⁴), Pyramid, Q5, T5557, T5567, T5577, TIRIS/HDX ¹²), TITAN (EM4050), UNIQUE, ZODIAC
All Standard Transponders, Cotag, G-Prox ⁹ , HID DuoProx II, HID ISO Prox II, HID Micro
Prox, HID ProxKey III, HID Prox, HID Prox II, Indala, ioProx, Nexwatch
Requires TWN4 SIO Card, All Standard Transponders, All Option P Transponders, HID
iCLASS, HID iCLASS SE/SR/Elite, HID iCLASS SEOS (Facility Code/PAC) ¹⁴⁾
Windows Embedded CE ⁴⁾ , 7 (32-/64-bit), 8, 8.1, 10, Linux, Android ⁴⁾ , iOS ⁴⁾ , MAC OS X ⁴⁾
USB, RS-485, OSDP4), Output 5V: Wiegand (D0/D1), or Clock/Data
HF Air: up to 848 kbit/s, USB Full speed (12 Mbit/s). RS-485: up to 38.400 baud
HF Air: up to 848 kbit/s, USB Full speed (12 Mbit/s), RS-485: up to 38,400 baud One SAM socket for ID-000 cards or modules
One SAM socket for ID-000 cards or modules



		act M Light reader module in transparent housing, black outer mounting seal, standard inlay, installation instruction, cardboard box	
ORDER CODE(S)	T4PK-F02TR6 T4PK-F02TR6-P T4PK-F02TR6-PI	TWN4 Palon Compact Panel Light kit, as described same, option P same, option PI	
	Bulk Packaging: TWN4 Palon Compact M Light reader module in transparent housing, black outer mounting ring, locknut, O ring seal, standard inlay, packed in bulk plastic bag		
	T4PK-F04TR6 T4PK-F04TR6-P T4PK-F04TR6-PI	TWN4 Palon Compact Panel Light kit, as described same, option P same, option PI	
ACCESSORIES	HOPL-YR01TR MECH-LNB01 MECH-ORB01 CAB-B9	Palon Panel transparent housing with black design frame Locknut O-ring seal USB A / USB micro cable	

¹¹UID only ²¹r/w enhanced security features on request ³¹EV2/EV3 supported as part of the EV1 downward compatibility ⁴¹On request ⁵¹r/w in direct chip command mode ⁵¹UID + r/w public area ¹¹UID only, read/write on request ⁵¹125 kHz technology requires a Russian local test and import license from the ministry of Trade and Industry (MINPROMTORC). This license has to be in place before Elatec can accept any order to be shipped to Russia ⁵¹Hash value only ¹¹¹Only emulation of 4100, 4102 ¹¹¹From FW V4.05 ¹²¹134.2 kHz only ¹³³Without encryption ¹⁴¹UID + PAC (Facility Code), r/w on request






(All measures in mm)

DIP	ASSIGNMENT
1	RS-485 address 0 LSB
2	RS-485 address 1
3	RS-485 address 2
4	RS-485 address 3 MSB
5	RS-485 BIAS on/off
6	RS-485 speed 0
7	RS-485 speed 1
8	RS-485 termination 120 Ohm on/off

PIN	ASSIGNMENT
1	(unused)
2	(unused)
3	RS-485 A
4	RS-485 B
5	TTL Wiegand D0 or DATA
6	TTL Wiegand D1 or CLOCK
7	VIN 9 – 30 Volt
8	GND



Drawing / rear view PCB

Firmware may change the assignment of the DIP switch. Please refer to the TWN4 Palon manual. For Wiegand, Clock/Data the DIP switch is not used.

ELATEC GmbH	ELATEC Systems GmbH	ELATEC Inc.	ELATEC Technology (Shenzhen) LLC
Zeppelinstr. 1	Schwieberdinger Str. 44	1995 SW Martin Hwy	918, Main Building, Tian An Cyber Times
82178 Puchheim	71636 Ludwigsburg	Palm City • FL 34990	Tower, No. 6, Tairan Fourth Road, Tian 'an
Germany	Germany	USA	Community, Shatou Neighborhood
P +49 89 552 9961 0	P +49 7141 309736 0	P +1 772 210 2263	Futian District • Shenzhen • China
F +49 89 552 9961 129		F +1 772 382 3749	P/F +86 755 2394 6014
E-Mail: info-rfid@elatec.com	E-Mail: info-rfid@elatec.com	E-Mail: americas-info@elatec.com	E-Mail: apac-info@elatec.com
Website: elatec.com	Website: elatec.com	Website: elatec.com	Website: elatec.com

ELATEC reserves the right to change any information or data in this document without prior notice. ELATEC declines all responsibility for the use of this product with any other specification but the one mentioned above. Any additional requirement for a specific customer application has to be validated by the customer himself at his own responsibility. Where application information is given, it is only advisory and does not form part of the specification. Disclaimer: All names used in this document are registered trademarks of their respective owners.