


PCB TERMINAL BLOCKS

5mm Pitch Standard Profile 90° Screw Terminal Blocks

- 2-12 pole solid block
- End stackable
- Guided pin alignment
- Moulded in grey UL94-V0 flame retardant PC
- Wire protector terminals
- 0.5-4.0mm² (30-14AWG) solid cable
- 0.5-2.5mm² (30-14AWG) stranded cable
- Anti solder wicking terminals
-  approved


CTB1050



TYPE NO.	POLES	LENGTH
CTB1050/2	2	10mm
CTB1050/3	3	15mm
CTB1050/4	4	20mm
CTB1050/5	5	25mm
CTB1050/6	6	30mm
CTB1050/7	7	35mm
CTB1050/8	8	40mm
CTB1050/9	9	45mm
CTB1050/10	10	50mm
CTB1050/11	11	55mm
CTB1050/12	12	60mm

SPECIFICATION

Rating	24A/250V UL=16A/300V, VDE&IMQ=24A/450V
Dielectric strength	≥2.5kV
Impulse withstand voltage	4kV
Working temperature	85°C
Moulding	UL94-V0 flame retardant PC
Pin/terminal	Tinned, nickel plated brass
Wire Protector	Tinned, plated phosphor bronze
Screw/torque	M3 steel zinc plated, 0.5Nm
Recommended PCB hole size	ø1.1mm



For other dimensions see CTB1000

PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDs &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

DIN RAIL
ENCLOSURES

BATTERIES

SOLAR
PANELS

TRANS-
FORMERS