


Technical Parameters:

- Weight:** 20g
- Display color:** Red/Blue/Green/Yellow
- Display mode:** Five 0.36" LED digital tube
- update rate:** >3 s/time
- Physical size:** 48 x 29 x 26 mm (L*W* H)
- Opening size:** 45 x 26 mm (L*W)
- Supplyvoltage:** 3.5-30V
- Lead wire length:** 14 cm(4 lines)
- Measurement range:** DC 0.0000-3.0000A
- Operation temperature:** -10 degrees~65 degrees
- Measurement accuracy:** ± (0.5%+ 2 words){Mean that in the worst condition the maximum error is below 1.7mA and the normal error is below 0.5mA}




Note:(please follow the instructions carefully wiring, or burn out)

The power supply end of the ammeter and measuring the ground USES a total design, that is to say, the power supply ground wire and test the ground wire is mutually, so only string ammeter test end after the electric appliances (both devices being measured between the cathode and tested equipment power of cathode)

Advice header power supply to use isolated power supply separately

Instruction of wiring

Ammeter with isolated power supply



Ammeter in the measurement system for power

