

RS PRO

Manual, mechanical and air pilot operated 3/2 poppet valves

- > Port size: G1/8
- Long established and well-proven valves
- > Compact size
- Normally closed and normally open models
- May also be used as 2/2 valves









Technical features

Medium:

Compressed air, filtered, lubricated and non-lubricated or hydraulic fluid

Operation:

Poppet valves, directly actuated **Mounting:**

Through-holes in valve body

Operating pressure:

2 ... 10 bar (29 ... 145 psi)

Port size:

G1/8

Ambient/Media temperature:

-20 ... +80°C max. (-4 ... +176 °F) Air supply must be dry enough to avoid ice formation at temperatures below +2°C (+35°F).

Flow:

I/min Cv 174 0,20 156 0,18

Others:

For use as a 2/2 valve the main supply must be connected to port '1' and the exhaust port 3' should be plugged.

Materials:

Body: Diecast zinc alloy Piston: aluminium Seals: NBR

Technical data 3/2 mechanical valves

| 5/2 mechanical valves | | | | | | | | | | |
|-----------------------|-----------|----------|---------------------|--------------------------|--------------------------------------|----------------|---------------|------------------|---------|--|
| Symbol | Port size | Function | Operator/ Return | Operating pressure (bar) | Operating force or torque at 6,3 bar | Weight (kg) | Spares Kit | Dimension No. | Model | |
| = 1 3 W | G1/8 | NC | Plunger/Spring | 210 | 35 N | 0,20 | QS/666/1/00 | 1 | 3146238 | |
| | | | | | | | | | | |
| ,2 | G1/8 | NO | Plunger/Spring | 210 | 72 N | 0,20 | QS/667/1/00 | 1 | | |
| | | | | | | | | | | |
| © 1 3 | G1/8 | NC | Roller/Spring | 210 | 20 N | 0,30 | QS/666/1/00 | 2 | | |
| | | | | | | | | | | |
| @ | G1/8 | NO | Roller/Spring | 210 | 40 N | 0,30 | QS/667/1/00 | 2 | | |
| | | | . , , | | | · | | | | |
| @ | G1/8 | NC | Roller/Spring | 210 | 0,25 Nm | 0,30 | QS/666/1/00 | 3 | 3146266 | |
| | | | 3 | | | ., | | | | |
| | | | | | | | | | | |
| | G1/8 | NC | Rod/Spring | 210 | 0,25 Nm | 0,30 | QS/666/1/00 | 4 | 3146288 | |
| | | | | | | | | | | |
| | G1/8 | NC | Antenna/Spring | 210 | 0,25 Nm | 0,30 | QS/666/1/00 | 5 | 3146294 | |
| | | | | | | | | | | |
| | | | | | | | | | | |



3/2 manual valves

| Symbol | Port size | Function | Knob colour | Operator/ Return | Operating pressure (bar) | Operating force or torque at 6,3 bar | Weight (kg) | Spares Kit | Dimension No. | Model |
|-----------|--------------|----------|----------------|--|--------------------------|--------------------------------------|----------------|-------------|---------------|-----------|
| (1) 1 3 W | G1/8 | NC | Silver | Knob/spring | 2 10 | 35 N | 0,20 | QS/666/1/00 | 7 | 2204098 |
| | G1/8 | NC | Black | Knob/spring | 2 10 | 35 N | 0,20 | QS/666/1/00 | 7 | PS/666/1N |
| | G1/8 | NC | Red | Knob/spring | 2 10 | 35 N | 0,20 | QS/666/1/00 | 7 | PS/666/1R |
| | G1/8 | NC | Green | Knob/spring | 2 10 | 35 N | 0,20 | QS/666/1/00 | 7 | PS/666/1G |
| 2 0 | G1/8 | NC | _ | Lever/lever (Panel mounting) | 2 10 | 14 N | 0,30 | QS/666/1/00 | 8 | 2180301 |
| | | | | | | | | | | |
| | G1/8 | NC | - | Lever (long)/lever (Panel mounting) | 2 10 | 10 N | 0,30 | QS/666/1/00 | 6 | 2204099 |
| | | | | | | | | | | |

3/2 pilot operated valves


| Symbol | Port size | Function | Operator/ Return | Operating pressure (bar) | Pilot pressure (bar) at 7 bar supply pressure | Weight (kg) | Spares Kit | Dimension No. | Model |
|-------------------------|--------------|----------|---------------------|--------------------------|--|----------------|--------------|------------------|---------|
| 12 -⊳ | G1/8 | NC | Pressure/spring | 210 | 2,8 | 0,20 | QS/666/40/00 | 9 | 3146216 |
| 10 2 -D-1 W10 3⊙1 | G1/8 | NO | Pressure/spring | 2 10 | 5,3 *1) | 0,20 | QS/667/40/00 | 9 | 3146222 |

^{*1) 4,6} bar at 3,5 bar supply, 6,0 bar at 10 bar supply




Dimensions





Pre-travel: 0,8 mm closed top seat Operating Travel: 0,8 mm open bottom seat Over-travel: 1,5 mm Model number S/667/14 type 3/2 normally open numbers are shown in brackets.

2




Dimensions in mm


 \bigcirc

Projection/First angle

Pre-travel: 1,4 mm closed top seat Operating Travel: 1,4 mm open bottom seat Over-travel: 2,2 mm Model number S/667/8 type 3/2 normally open numbers are shown in brackets.







30° max. 30° max. 25° min. 3,5 37,5 28,5 75 ₩ ₩ 22,5 51 19 19 33,5 5


Mechanism may be operated either side of centre line. When the valve is mounted horizontally, the roller is recommended to be positioned on the upper face of the arm. *Alternative position

Mechanism may be operated either side of centre line.

*Recommended









6

Dimensions in mm Projection/First angle \bigcirc











*Rotation at Point of Application: 40° minimum @ 80 mm50° minimum @ 120 mm 55° minimum @ 160 mm Mechanism may be operated either side of centre line.


Panel hole: ø 16 mm Panel thickness: 4 mm maximum











Panel hole: ø 16 mm Panel thickness: 4 mm maximum





Dimensions in mm Projection/First angle





