


Features

- Low forward voltage
- Reverse voltage $V_R \leq 100$ V
- Low capacitance
- High-speed switching
- Very small and flat lead SMD plastic package



Absolute Maximum Ratings $T_a = 25^\circ\text{C}$

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_{RM}	100	V
Forward Current	I_F	250	mA
Non-Repetitive Peak Forward Current	I_{FSM}	2.5	A
Power Dissipation (Note.1) (Note.2)	P_d	400	mW
		715	
Thermal Resistance Junction to Ambient (Note.1) (Note.2)	$R_{\theta JA}$	310	°C/W
		175	
Thermal Resistance Junction to Solder Point	$R_{\theta JSP}$	35	
Junction Temperature	T_J	150	°C
Storage Temperature range	T_{stg}	-65 to 150	

Note.1:Device mounted on an FR4 Printed-Circuit Board (PCB), single-sided copper, tin-plated and standard footprint.

Note.2:Device mounted on an FR4 PCB, single-sided copper, tin-plated, mounting pad for cathode 1 cm³.

■ Electrical Characteristics $T_a = 25^\circ\text{C}$

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Reverse breakdown voltage	V_R	$I_R = 100 \mu\text{A}$	100			V
Forward voltage	V_F	$I_F = 0.1 \text{ mA}$			200	mV
		$I_F = 10 \text{ mA}$			350	
		$I_F = 10 \text{ mA}, T_J = -40^\circ\text{C}$			470	
		$I_F = 50 \text{ mA}$			475	
		$I_F = 50 \text{ mA}, T_J = -40^\circ\text{C}$			560	
		$I_F = 250 \text{ mA}$			850	
Reverse voltage leakage current	I_R	$V_R = 1.5 \text{ V}$			0.5	uA
		$V_R = 1.5 \text{ V}, T_J = 60^\circ\text{C}$			12	
		$V_R = 10 \text{ V}$			0.8	
		$V_R = 10 \text{ V}, T_J = 60^\circ\text{C}$			20	
		$V_R = 50 \text{ V}$			2	
		$V_R = 50 \text{ V}, T_J = 60^\circ\text{C}$			44	
		$V_R = 75 \text{ V}$			4	
		$V_R = 75 \text{ V}, T_J = 60^\circ\text{C}$			80	
		$V_R = 100 \text{ V}$			9	
		$V_R = 100 \text{ V}, T_J = 60^\circ\text{C}$			120	
Junction capacitance	C_J	$V_R = 0 \text{ V}, f = 1 \text{ MHz}$			39	pF
		$V_R = 1 \text{ V}, f = 1 \text{ MHz}$			21	
Reverse recovery time	t_{rr}	$I_F = I_R = 10 \text{ mA}, I_{rr} = 0.1 \times I_R, R_L = 100\Omega$			5.9	ns

PROTECTION PRODUCTS
 Typical characteristics


www.sot23.com.tw


Fig 1. Transient thermal impedance from junction to ambient as a function of pulse duration; typical values






Fig 2. Transient thermal impedance from junction to ambient as a function of pulse duration; typical values



- (1) $T_{amb} = 150^\circ C$
- (2) $T_{amb} = 125^\circ C$
- (3) $T_{amb} = 85^\circ C$
- (4) $T_{amb} = 25^\circ C$
- (5) $T_{amb} = -40^\circ C$


Fig 3. Forward current as a function of forward voltage; typical values



- (1) $T_{amb} = 125^\circ C$
- (2) $T_{amb} = 85^\circ C$
- (3) $T_{amb} = 60^\circ C$
- (4) $T_{amb} = 25^\circ C$
- (5) $T_{amb} = -40^\circ C$

Fig 4. Reverse current as a function of reverse voltage; typical values

■ Typical Characteristics



f = 1 MHz; T_{amb} = 25 °C

Fig 5. Diode capacitance as a function of reverse voltage; typical values




Fig 6. Average reverse power dissipation as a function of reverse voltage; typical values




Fig 7. Average forward current as a function of ambient temperature; typical values




Fig 8. Average forward current as a function of ambient temperature; typical values





Fig 9. Average forward current as a function of solder point temperature; typical values



(1) $I_R = 1 \text{ mA}$

Input signal: reverse pulse rise time $t_r = 0.6 \text{ ns}$; reverse voltage pulse duration $t_p = 100 \text{ ns}$; duty cycle $\delta = 0.05$

Oscilloscope: rise time $t_r = 0.35 \text{ ns}$

Fig 10. Reverse recovery time test circuit and waveforms





Fig 11. Duty cycle definition

The current ratings for the typical waveforms as shown in Figure 7, 8 and 9 are calculated according to the equations: $I_{FAV} = I_M \times \delta$ with I_M defined as peak current, $I_{RMS} = I_{F(AV)}$ at DC, and $I_{RMS} = I_M \times \sqrt{\delta}$ with I_{RMS} defined as RMS current.

Outline Drawing - SOD-323



Dim	Millimeters		Inches	
	Min	Max	Min	Max
A	1.60	1.80	0.063	0.071
B	1.2	1.40	0.047	0.055
C	0.80	0.90	0.031	0.035
D	0.25	0.35	0.010	0.014
E	0.15REF		0.006REF	
H	0	0.10	0	0.004
J	0.08	0.15	0.003	0.006
K	2.50	2.70	0.098	0.106

Land Pattern - SOD-323

