

Sample &

Buy





Reference

Design

SNVS311D-MAY 2005-REVISED FEBRUARY 2015

## LP3878-ADJ Micropower 800-mA Low-Noise "Ceramic Stable" Adjustable Voltage Regulator for 1-V to 5-V Applications

Technical

Documents

## 1 Features

- Input Supply Voltage: 2.5 V to 16V
- Output Voltage Range: 1 V to 5.5 V
- Designed for Use With Low-ESR Ceramic Capacitors
- Very Low Output Noise
- 8-Lead SO PowerPAD<sup>™</sup> and WSON Surface-Mount Packages
- < 10-µA Quiescent Current in Shutdown</li>
- Low Ground Pin Current at all Loads
- Overtemperature and Overcurrent Protection
- –40°C to 125°C Operating Junction Temperature Range

## 2 Applications

- ASIC Power Supplies In:
  - Desktops, Notebooks, and Graphic CardsSet Top Boxes, Printers, and Copiers
  - Set Top Boxes, Finiters, and Copier
- DSP and FPGA Power Supplies
- SMPS Post-Regulator
- Medical Instrumentation

## 3 Description

Tools &

Software

The LP3878-ADJ is an 800-mA, adjustable output, voltage regulator designed to provide high performance and low noise in applications requiring output voltages as low as 1 V.

Support &

Community

2.2

Using an optimized VIP (Vertically Integrated PNP) process, the LP3878-ADJ delivers superior performance:


- Ground Pin Current: Typically 5.5 mA at 800-mA load, and 180 μA at 100-μA load.
- Low Power Shutdown: The LP3878-ADJ draws less than 10-µA quiescent current when the SHUTDOWN pin is pulled low.
- Precision Output: Ensured output voltage accuracy is 1% at room temperature.
- Low Noise: Broadband output noise is only 18 μV (typical) with a 10-nF bypass capacitor.

#### Device Information<sup>(1)</sup>

PART NUMBER	PACKAGE	BODY SIZE (NOM)
	SO PowerPAD (8)	4.89 mm × 3.90 mm
LP3878-ADJ	WSON (8)	4.00 mm × 4.00 mm

(1) For all available packages, see the orderable addendum at the end of the data sheet.

### **Basic Application Circuit**



\*Capacitor values shown are minimum required to assure stability. A larger output capacitor provides improved dynamic response. Output capacitor must meet ESR requirements (see *Application Information*). \*\*The SHUTDOWN (or S/D) pin must be actively terminated (see *Device Functional Modes*). Tie to IN (pin 4) if not used.

2 Submit Documentation Feedback

## Table of Contents

Feat	ures 1
Арр	lications 1
Des	cription 1
Revi	ision History 2
Pin	Configuration and Functions 3
Spe	cifications 4
6.1	Absolute Maximum Ratings 4
6.2	ESD Ratings 4
6.3	Recommended Operating Conditions 4
6.4	Thermal Information 4
6.5	Electrical Characteristics5
6.6	Typical Characteristics 6
Deta	ailed Description 11
7.1	Overview 11
	Functional Block Diagram 11
7.3	Feature Description 11
	App Des Rev Pin 6.1 6.2 6.3 6.4 6.5 6.6 Deta 7.1 7.2

	7.4	Device Functional Modes	. 12
8	Арр	lication and Implementation	13
	8.1	Application Information	13
	8.2	Typical Application	13
9	Pow	er Supply Recommendations	17
10	Lay	out	17
	10.1	Layout Guidelines	. 17
	10.2	Layout Example	. 17
	10.3	Power Dissipation	. 17
11	Dev	ice and Documentation Support	18
	11.1	Documentation Support	. 18
	11.2	Trademarks	18
	11.3	Electrostatic Discharge Caution	. 18
	11.4	Glossary	. 18
12		hanical, Packaging, and Orderable	
	Info	rmation	18

## 4 Revision History

NOTE: Page numbers for previous revisions may differ from page numbers in the current version.

Cł	hanges from Revision C (December 2014) to Revision D
•	Deleted trademark symbol from VIP - no longer trademark: add reference design icon to Ton Navigators

	Deleted trademark symbol norm vir - no longer trademark, add reference design tor top havigators	
•	Deleted soldering info - now in POA	4
	Changed wording of footnote 5 to Ab Max Ratings	
	Changed I <sub>OUT</sub> to I <sub>OUT</sub> throughout document	
•	Changed wording of Reverse Input-Output Voltage	11
•	Changed outpin pin to OUT pin	15
	Added new paragraph to Noise Bypass Capacitor subsection	

#### Changes from Revision B (April 2013) to Revision C

•	Added Pin Configuration and Functions section, ESD Ratings table, Feature Description section, Device Functional
	Modes, Application and Implementation section, Power Supply Recommendations section, Layout section, Device
	and Documentation Support section, and Mechanical, Packaging, and Orderable Information section; update
	thermal values
-	

#### Changes from Revision A (April 2013) to Revision B



www.ti.com

Page

Page


Copyright © 2005–2015, Texas Instruments Incorporated

Page

1



## 5 Pin Configuration and Functions



#### **Pin Functions**

PIN		1/0	DESCRIPTION		
NAME	NUMBER	1/0	DESCRIPTION		
ADJ	6	I	Provides feedback to error amplifier from the resistive divider that sets the output voltage.		
BYPASS	1	—	The capacitor connected between BYPASS and GROUND lowers output noise voltage level and is required for loop stability.		
GROUND	3	—	e ground.		
IN	4	I	ut source voltage.		
N/C	2		PO NOT CONNECT. Device pin 2 is reserved for post packaging test and calibration of the P3878-ADJ V <sub>ADJ</sub> accuracy. This pin must be left floating. Do not connect to any potential. No not connect to ground. Any attempt to do pin continuity testing on device pin 2 is iscouraged. Continuity test results will be variable depending on the actions of the factory alibration. Aggressive pin continuity testing (high voltage, or high current) on device pin 2 hay activate the trim circuitry forcing V <sub>ADJ</sub> to move out of tolerance.		
N/C	7		No internal connection.		
OUT	5	0	Regulated output voltage.		
SHUTDOWN	8	I	Output is enabled above turnon threshold voltage. Pull down to turn off regulator output.		
Thermal Pad	_	_	The exposed thermal pad on the bottom of the package should be connected to a copper thermal pad on the PCB under the package. The use of thermal vias to remove heat from the package into the PCB is recommended. Connect the thermal pad to ground potential or leave floating. Do not connect the thermal pad to any potential other than the same ground potential seen at device pin 3. For additional information on using TI's Non Pull Back WSON package, see Application Note <i>AN-1187</i> , SNOA401.		

## 6 Specifications

## 6.1 Absolute Maximum Ratings

over operating free-air temperature range (unless otherwise noted)<sup>(1)(2)</sup>

	MIN	MAX	UNIT
SHUTDOWN pin		1	kV
Power dissipation <sup>(3)</sup>	Internal	y Limited	
Input supply voltage (survival), V <sub>IN</sub>	-0.3	16	V
ADJ pin	-0.3	6	V
Output voltage (survival), V <sub>OUT</sub> <sup>(4)</sup>	-0.3	6	V
I <sub>OUT</sub> (survival)	Short-Circu	uit Protected	
Input – output voltage (survival), V <sub>IN</sub> – V <sub>OUT</sub> <sup>(5)</sup>	-0.3	16	V
Storage temperature, T <sub>stg</sub>	-65	150	°C

(1) Stresses beyond those listed under Absolute Maximum Ratings may cause permanent damage to the device. These are stress ratings only, which do not imply functional operation of the device at these or any other conditions beyond those indicated under Recommended Operating Conditions. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

(2) If Military- or Aerospace-specified devices are required, please contact the TI Sales Office/Distributors for availability and specifications.

(3) The maximum allowable power dissipation is a function of the maximum junction temperature, T<sub>J</sub>(MAX), the junction-to-ambient thermal resistance, R<sub>0JA</sub>, and the ambient temperature, T<sub>A</sub>. The maximum allowable power dissipation at any ambient temperature is calculated using: P<sub>(MAX)</sub> = (T<sub>J</sub>(MAX) - T<sub>A</sub>) / R<sub>0JA</sub>. The value of R<sub>0JA</sub> for the WSON (NGT) and SO PowerPAD (DDA) packages are specifically dependent on PCB trace area, trace material, and the number of layers and thermal vias. For improved thermal resistance and power dissipation for the WSON package, see Application Note AN-1187, SNOA401. Exceeding the maximum allowable power dissipation will cause excessive die temperature, and the regulator will go into thermal shutdown.

(4) If used in a dual-supply system where the regulator load is returned to a negative supply, the LP3878-ADJ output must be diodeclamped to ground.

(5) The PNP pass element contains a parasitic diode between the IN pin and the OUT pin that is normally reverse-biased. Forcing the OUT pin voltage above the IN pin voltage will turn on this diode and may induce a latch-up mode which can damage the part (see Application and Implementation).

### 6.2 ESD Ratings

			VALUE	UNIT
V <sub>(ESD)</sub>	Electrostatic discharge	Human body model (HBM), per ANSI/ESDA/JEDEC JS-001, all pins <sup>(1)</sup>	±2000	V

(1) JEDEC document JEP155 states that 500-V HBM allows safe manufacturing with a standard ESD control process.

## 6.3 Recommended Operating Conditions

over operating free-air temperature range (unless otherwise noted)

		MIN	MAX	UNIT
V <sub>IN</sub>	Supply input voltage	2.5	16	V
V <sub>SD</sub>	SHUTDOWN input voltage		V <sub>IN</sub>	V
I <sub>OUT</sub>	Output current		800	mA
TJ	Operating junction temperature	-40	125	°C

### 6.4 Thermal Information

		LP387	'8-ADJ	
	Junction-to-case (top) thermal resistance   Junction-to-board thermal resistance   Junction-to-board thermal resistance   JT Junction-to-top characterization parameter   JB Junction-to-board characterization parameter	DDA	NGT	UNIT
		8 PINS		
$R_{\thetaJA}$	Junction-to-ambient thermal resistance	42.5	38.1	
R <sub>0JC(top)</sub>	Junction-to-case (top) thermal resistance	54.0	27.9	
$R_{\theta JB}$	Junction-to-board thermal resistance	26.5	15.2	°C/W
ΨJT	Junction-to-top characterization parameter	8.0	0.2	°C/VV
Ψ <sub>JB</sub>	Junction-to-board characterization parameter	26.4	15.3	
R <sub>0JC(bot)</sub>	Junction-to-case (bottom) thermal resistance	3.6	4.5	

(1) For more information about traditional and new thermal metrics, see the IC Package Thermal Metrics application report, SPRA953.



### 6.5 Electrical Characteristics

Limits are specified through design, testing, or correlation. The limits are used to calculate TI's Average Outgoing Quality Level (AOQL). Unless otherwise specified:  $T_J = 25^{\circ}C$ ,  $V_{IN} = 3$  V,  $V_{OUT} = 1$  V,  $I_{OUT} = 1$  mA,  $C_{OUT} = 10$  µF,  $C_{IN} = 4.7$  µF,  $V_{\overline{SD}} = 2$  VV $_{\overline{SD}}$ ,  $C_{BYPASS} = 10$  nF.

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
			0.99	1.00	1.01	
V <sub>ADJ</sub>	Adjust pin voltage	1 mA $\leq$ I <sub>OUT</sub> $\leq$ 800 mA, 3 V $\leq$ V <sub>IN</sub> $\leq$ 6 V	0.98	1.00	1.02	V
♥ ADJ	Aujust pin voltage	1 mA ≤ I <sub>OUT</sub> ≤ 800 mA, 3 V ≤ V <sub>IN</sub> ≤ 6 V -40°C ≤ T <sub>J</sub> ≤ 125°C	0.97		1.03	v
		$3 \text{ V} \le \text{V}_{\text{IN}} \le 16 \text{ V}$		0.007	0.014	
ΔV <sub>OUT</sub> /ΔV <sub>IN</sub>	Output voltage line regulation	$3 \text{ V} \le \text{V}_{\text{IN}} \le 16 \text{ V}, -40^{\circ}\text{C} \le \text{T}_{\text{J}} \le 125^{\circ}\text{C}$			0.032	%/V
		$I_{OUT} = 800 \text{ mA}, V_{OUT} \ge V_{OUT(NOM)} - 1\%$		2.5		
		$I_{OUT} = 800 \text{ mA}, V_{OUT} \ge V_{OUT(NOM)} - 1\%$ -40°C ≤ T <sub>J</sub> ≤ 125°C			3.1	
、 <i>r</i>	Minimum input voltage	$I_{OUT} = 800 \text{ mA}, V_{OUT} \ge V_{OUT(NOM)} - 1\%$ $0 \le T_J \le 125^{\circ}C$		2.5		
V <sub>IN(MIN)</sub>	required to maintain output regulation	$\begin{split} I_{OUT} &= 800 \text{ mA}, \ V_{OUT} \geq V_{OUT(NOM)} - 1\% \\ 0 \leq T_J \leq 125^\circ\text{C}, \ -40^\circ\text{C} \leq T_J \leq 125^\circ\text{C} \end{split}$			2.8	V
		$I_{OUT} = 750 \text{ mA}, V_{OUT} \ge V_{OUT(NOM)} - 1\%$		2.5		
		$I_{OUT} = 750 \text{ mA}, V_{OUT} \ge V_{OUT(NOM)} - 1\%$ -40°C ≤ T <sub>J</sub> ≤ 125°C			3.0	
		I <sub>OUT</sub> = 100 μA		1	2	
		$I_{OUT} = 100 \ \mu A, -40^{\circ}C \le T_{J} \le 125^{\circ}C$			3	
	Dropout voltage <sup>(1)</sup>	I <sub>OUT</sub> = 200 mA		150	200	
V <sub>DOUT</sub>	$V_{OUT} = 3.8 V$	$I_{OUT} = 200 \text{ mA}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$			300	mV
		I <sub>OUT</sub> = 800 mA		475	600	
		$I_{OUT} = 800 \text{ mA}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$			1100	
		I <sub>OUT</sub> = 100 μA		180	200	
		I <sub>OUT</sub> = 100 μA, −40°C ≤ T <sub>J</sub> ≤ 125°C			225	μA
		I <sub>OUT</sub> = 200 mA		1.5	2	
IGND	Ground pin current	$I_{OUT} = 200 \text{ mA}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$			3.5	0
		I <sub>OUT</sub> = 800 mA		5.5	8.5	mA
		$I_{OUT} = 800 \text{ mA}, -40^{\circ}\text{C} \le T_{J} \le 125^{\circ}\text{C}$			15	
I <sub>OUT(PK)</sub>	Peak output current	$V_{OUT} \ge V_{OUT(NOM)} - 5\%$		1200		
I <sub>OUT(MAX)</sub>	Short-circuit current	$R_L = 0 \Omega$ (steady state)		1300		mA
e <sub>n</sub>	Output noise voltage (RMS)	Bandwidth = 100 Hz to 100 kHz, $C_{BYPASS} = 10$ nF		18		μV <sub>(RMS)</sub>
ΔV <sub>OUT</sub> /ΔV <sub>IN</sub>	Ripple rejection	f = 1 kHz		60		dB
I <sub>ADJ</sub>	ADJ pin bias current (sourcing)	I <sub>OUT</sub> = 800 mA		200		nA
SHUTDOWN I	nput					
		V <sub>H</sub> = Output ON		1.4		
		$V_{H} = Output ON, -40^{\circ}C \le T_{J} \le 125^{\circ}C$			1.6	
V <sub>SD</sub>	SHUTDOWN input voltage	$V_L$ = Output OFF, $I_{IN} \le 10 \ \mu A$		0.20		V
	ee.e.e	$V_L$ = Output OFF, $I_{IN} \le 10 \ \mu A$ -40°C $\le T_J \le 125$ °C	0.04			
		$V_{OUT} \le 10 \text{ mV}, I_{IN} \le 50 \mu\text{A}$		0.6		
		$V_{\overline{SD}} = 0 V$		0.02		
<b>—</b>		$V_{\overline{SD}} = 0 \text{ V}, -40^{\circ}\text{C} \le \text{T}_{\text{J}} \le 125^{\circ}\text{C}$			-1	
ISD	SHUTDOWN input current	$V_{SD} = 5 V$		5		μA
		$V_{SD} = 5 \text{ V}, -40^{\circ}\text{C} \le \text{T}_{\text{J}} \le 125^{\circ}\text{C}$			15	

(1) Dropout voltage specification applies only if  $V_{IN}$  is sufficient so that it does not limit regulator operation.

LP3878-ADJ


SNVS311D-MAY 2005-REVISED FEBRUARY 2015



www.ti.com

## 6.6 Typical Characteristics


Unless otherwise specified:  $V_{IN} = 3.3 \text{ V}$ ,  $V_{OUT} = 1 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 4.7 \text{ }\mu\text{F}$ ,  $C_{OUT} = 10 \text{ }\mu\text{F}$ ,  $V_{\overline{SD}} = 2 \text{ V}$ ,  $C_{BYP} = 10 \text{ }n\text{F}$ ,  $T_{J} = 25^{\circ}\text{C}$ .





### **Typical Characteristics (continued)**

Unless otherwise specified:  $V_{IN}$  = 3.3 V,  $V_{OUT}$  = 1 V,  $I_{OUT}$  = 1 mA,  $C_{IN}$  = 4.7  $\mu$ F,  $C_{OUT}$  = 10  $\mu$ F,  $V_{SD}$  = 2 V,  $C_{BYP}$  = 10 nF,  $T_{J}$  = 25°C.




LP3878-ADJ SNVS311D-MAY 2005-REVISED FEBRUARY 2015



www.ti.com

## **Typical Characteristics (continued)**


Unless otherwise specified:  $V_{IN} = 3.3 \text{ V}$ ,  $V_{OUT} = 1 \text{ V}$ ,  $I_{OUT} = 1 \text{ mA}$ ,  $C_{IN} = 4.7 \text{ }\mu\text{F}$ ,  $C_{OUT} = 10 \text{ }\mu\text{F}$ ,  $V_{\overline{SD}} = 2 \text{ V}$ ,  $C_{BYP} = 10 \text{ }n\text{F}$ ,  $T_{J} = 25^{\circ}\text{C}$ .





#### **Typical Characteristics (continued)**

Unless otherwise specified:  $V_{IN}$  = 3.3 V,  $V_{OUT}$  = 1 V,  $I_{OUT}$  = 1 mA,  $C_{IN}$  = 4.7 µF,  $C_{OUT}$  = 10 µF,  $V_{SD}$  = 2 V,  $C_{BYP}$  = 10 nF,  $T_J$  = 25°C.




LP3878-ADJ SNVS311D-MAY 2005-REVISED FEBRUARY 2015



www.ti.com

## **Typical Characteristics (continued)**

Unless otherwise specified:  $V_{IN}$  = 3.3 V,  $V_{OUT}$  = 1 V,  $I_{OUT}$  = 1 mA,  $C_{IN}$  = 4.7  $\mu$ F,  $C_{OUT}$  = 10  $\mu$ F,  $V_{\overline{SD}}$  = 2 V,  $C_{BYP}$  = 10 nF,  $T_{J}$  = 25°C.





## 7 Detailed Description


## 7.1 Overview

The LP3878-ADJ is an adjustable regulator; the output voltage can be set from 1 V to 5.5 V. The device can deliver 800-mA continuous load current. Standard regulator features, such as overcurrent and overtemperature protection, are also included.

The LP3878-ADJ contains other features:

- Low power shutdown current and low ground pin current
- Very low output noise
- 8-lead SO PowerPAD or WSON surface-mount packages to allow for increased power dissipation.

## 7.2 Functional Block Diagram



## 7.3 Feature Description

### 7.3.1 Shutdown Input Operation

The LP3878-ADJ is shut off by pulling the  $\overline{SHUTDOWN}$  input low, and turned on by pulling it high. If this feature is not to be used, the  $\overline{SHUTDOWN}$  input should be tied to  $V_{IN}$  to keep the regulator output on at all times.

To assure proper operation, the signal source used to drive the SHUTDOWN input must be able to swing above and below the specified turnon or turnoff voltage thresholds listed in the *Electrical Characteristics* under V<sub>ON/OFF</sub>.

#### 7.3.2 Reverse Input-Output Voltage

The PNP power transistor used as the pass element in the LP3878-ADJ contains a parasitic diode between the IN pin and the OUT pin. During normal operation (where the IN pin voltage is higher than the OUT pin voltage) this parasitic diode is reverse-biased. However, if the OUT pin voltage is pulled above the IN pin voltage this diode will turn ON, and current will flow into the LP3878-ADJ OUT pin.

In such cases, a parasitic SCR between the IN pin and the GND pin can latch ON which will allow a high current to flow from the VIN supply, into the IN pin to ground, which can damage the part. In any application where the OUT pin voltage may be higher than the IN pin voltage, even momentarily, an external Schottky diode must be connected from the IN pin to the OUT pin (cathode to IN pin, anode to OUT pin), to limit the reverse voltage across the LP3878-ADJ to 0.3 V (see *Absolute Maximum Ratings*).

### 7.3.3 Low Output Noise

With a 10-nF capacitor on the BYPASS pin, the output noise is only 18  $\mu$ V.

Copyright © 2005–2015, Texas Instruments Incorporated



### 7.4 Device Functional Modes

#### 7.4.1 Operation With $V_{OUT(TARGET)} + 2 V \le V_{IN} \le 16 V$

The device operates if the input voltage is equal to, or exceeds  $V_{OUT(TARGET)}$  + 2 V. At input voltages below the minimum  $V_{IN}$  requirement, the device does not operate correctly and output voltage may not reach target value.

## 7.4.2 Operation With SHUTDOWN Pin Control

LP3878-ADJ is turned off by pulling the  $\overline{SHUTDOWN}$  pin low, and turned on by pulling it high. If this feature is not used, the  $\overline{SHUTDOWN}$  pin should be tied to  $V_{IN}$  to keep the regulator output on at all times. To assure proper operation, the signal source used to drive the  $\overline{SHUTDOWN}$  input must be able to swing above and below the specified turnon and turnoff voltage thresholds listed in the *Electrical Characteristics* under  $V_L$  and  $V_H$ .



## 8 Application and Implementation


#### NOTE

Information in the following applications sections is not part of the TI component specification, and TI does not warrant its accuracy or completeness. TI's customers are responsible for determining suitability of components for their purposes. Customers should validate and test their design implementation to confirm system functionality.

#### 8.1 Application Information

The LP3878-ADJ can provide 800-mA output current with 2.5-V to 6-V output voltage. A minim<u>um 10- $\mu$ F output</u> capacitor is required for loop stability. An input capacitor of at least 4.7- $\mu$ F is required also. The SHUTDOWN pin must be tied to input if not used. A 10-nF bypass capacitor is required to improve loop stability, it also can reduce noise on the regulator output significantly. A capacitor, C<sub>FF</sub>, is required to increase phase margin and assure loop stability. Output voltage can be set by two resistors R1 and R2 (see Figure 27), and R2 must be less than 5 k $\Omega$  to ensure loop stability.

#### 8.2 Typical Application



dynamic response. Output capacitor must meet ESR requirements (see *Application Information*). \*\*The SHUTDOWN (or S/D) pin must be actively terminated (see *Device Functional Modes*). Tie to IN (pin 4) if not used.

#### 8.2.1 Design Requirements

DESIGN PARAMETER	VALUE
Input voltage	3.8 V ±10%
Output voltage	1.8 V ±3%
Output current	800 mA (maximum)
Input capacitor	4.7 μF (minimum)
Output capacitor	10 µF (minimum)
Bypass capacitor	10 nF
External resistor R2	1 kΩ (less than 5 kΩ)



#### 8.2.2 Detailed Design Procedure

#### 8.2.2.1 External Capacitors

Like any low-dropout regulator, the LP3878-ADJ requires external capacitors for regulator stability. These capacitors must be correctly selected for good performance.

#### 8.2.2.1.1 Input Capacitor

A capacitor whose value is at least 4.7  $\mu$ F (±20%) is required between the LP3878-ADJ input and ground. A good quality X5R or X7R ceramic capacitor should be used.

Capacitor tolerance and temperature variation must be considered when selecting a capacitor (see *Capacitor Characteristics*) to assure the minimum requirement of input capacitance is met over all operating conditions.

The input capacitor must be located not more than 0.5 inches from the input pin and returned to a clean analog ground. Any good quality ceramic or tantalum capacitor may be used, assuming the minimum input capacitance requirement is met.

#### 8.2.2.1.2 Output Capacitor

The LP3878-ADJ requires a ceramic output capacitor whose size is at least 10  $\mu$ F (±20%). A good quality X5R or X7R ceramic capacitor should be used. Capacitance tolerance and temperature characteristics must be considered when selecting an output capacitor.

The LP3878-ADJ is designed specifically to work with ceramic output capacitors, utilizing circuitry which allows the regulator to be stable across the entire range of output current with an ultra-low equivalent series resistance (ESR) output capacitor.

The output capacitor selected must meet the requirement for minimum amount of capacitance and also have an ESR value which is within the stable range. A curve is provided which shows the stable ESR range as a function of load current (see Figure 28).




Figure 28. Stable Region for Output Capacitor ESR

Copyright © 2005–2015, Texas Instruments Incorporated



#### NOTE

**Important:** The output capacitor must maintain its ESR within the stable region over the full operating temperature range of the application to assure stability.

The output capacitor ESR forms a zero which is required to add phase lead near the loop gain crossover frequency, typically in the range of 50 kHz to 200 kHz. The ESR at lower frequencies is of no importance. Some capacitor manufacturers list ESR at low frequencies only, and some give a formula for Dissipation Factor (DF) which can be used to calculate a value for a term referred to as ESR. However, because the DF formula is usually at a much lower frequency than the range listed above, it will give an unrealistically high value. If good quality X5R or X7R ceramic capacitors are used, the actual ESR in the 50-kHz to 200-kHz range will not exceed 25 m $\Omega$ . If these are used as output capacitors for the LP3878-ADJ, the regulator stability requirements are satisfied.

It is important to remember that capacitor tolerance and variation with temperature must be taken into consideration when selecting an output capacitor so that the minimum required amount of output capacitance is provided over the full operating temperature range (see *Capacitor Characteristics*).

The output capacitor must be located not more than 0.5 inches from the OUT pin and returned to a clean analog ground.

#### 8.2.2.1.3 Noise Bypass Capacitor

The 10-nF capacitor on the BYPASS pin significantly reduces noise on the regulator output and is required for loop stability. However, the capacitor is connected directly to a high-impedance circuit in the bandgap reference.

Because this circuit has only a few µA flowing in it, any significant loading on this node will cause a change in the regulated output voltage. For this reason, dc leakage current through the noise bypass capacitor must never exceed 100 nA, and should be kept as low as possible for best output voltage accuracy.

The types of capacitors best suited for the noise bypass capacitor are ceramic and film. High-quality ceramic capacitors with either NPO or COG dielectric typically have very low leakage. 10-nF polypropylene and polycarbonate film capacitors are available in small surface-mount packages and typically have extremely low leakage current.

While the capacitor value on the BYPASS will affect start-up time, this is not intended to be used as a soft-start circuit. There is no dedicated discharge circuitry for this capacitor, and it can be pre-biased if the IN pin, or the SHUTDOWN pin are not at 0 V at start-up.

#### 8.2.2.2 Feedforward Capacitor

The feedforward capacitor designated  $C_{FF}$  in Figure 27 is required to increase phase margin and assure loop stability. Improved phase margin also gives better transient response to changes in load or input voltage, and faster settling time on the output voltage when transients occur.  $C_{FF}$  forms both a pole and zero in the loop gain, the zero providing beneficial phase lead (which increases phase margin) and the pole adding undesirable phase lag (which should be minimized). The zero frequency is determined both by the value of  $C_{FF}$  and R1:

$$f_{Z} = 1 / (2\pi C_{FF} \times R1)$$

(1)

The pole frequency resulting from  $C_{FF}$  is determined by the value of  $C_{FF}$  and the parallel combination of R1 and R2:

$$f_{P} = 1 / (2\pi C_{FF} \times (R1 // R2))$$

(2)

At higher output voltages where R1 is much greater than R2, the value of R2 primarily determines the value of the parallel combination of R1 // R2. This puts the pole at a much higher frequency than the zero. As the regulated output voltage is reduced (and the value of R1 decreases), the parallel effect of R2 diminishes and the two equations become equal (at which point the pole and zero cancel out). Because the pole frequency gets closer to the zero at lower output voltages, the beneficial effects of C<sub>FF</sub> are increased if the frequency range of the zero is shifted slightly higher for applications with low V<sub>OUT</sub> (because then the pole adds less phase lag at the loop crossover frequency).

 $C_{FF}$  should be selected to place the pole-zero pair at a frequency where the net phase lead added to the loop at the crossover frequency is maximized. The following design guidelines were obtained from bench testing to optimize phase margin, transient response, and settling time:

For V<sub>OUT</sub> ≤ 2.5 V: C<sub>FF</sub> should be selected to set the zero frequency in the range of about 50 kHz to 200 kHz.



(3)

For V<sub>OUT</sub> > 2.5 V: C<sub>FF</sub> should be selected to set the zero frequency in the range of about 20 kHz to 100 kHz.

#### 8.2.2.3 Capacitor Characteristics

#### 8.2.2.3.1 Ceramic

The LP3878-ADJ was designed to work with ceramic capacitors on the output to take advantage of the benefits they offer: for capacitance values in the 10- $\mu$ F range, ceramics are the least expensive and also have the lowest ESR values (which makes them best for eliminating high-frequency noise). The ESR of a typical 10- $\mu$ F ceramic capacitor is in the range of 5 m $\Omega$  to 10 m $\Omega$ , which meets the ESR limits required for stability by the LP3878-ADJ.

One disadvantage of ceramic capacitors is that their capacitance can vary with temperature. Many large value ceramic capacitors ( $\geq 2.2 \ \mu$ F) are manufactured with the Z5U or Y5V temperature characteristic, which results in the capacitance dropping by more than 50% as the temperature goes from 25°C to 85°C.

Another significant problem with Z5U and Y5V dielectric devices is that the capacitance drops severely with applied voltage. A typical Z5U or Y5V capacitor can lose 60% of its rated capacitance with half of the rated voltage applied to it.

For these reasons, X7R and X5R type ceramic capacitors must be used on the input and output of the LP3878-ADJ.

#### 8.2.2.4 Setting the Output Voltage


The output voltage is set using resistors R1 and R2 (see Figure 27).

The formula for output voltage is:

$$V_{OUT} = V_{ADJ} \times (1 + (R1 / R2))$$

R2 must be less than 5 k $\Omega$  to ensure loop stability.

To prevent voltage errors, R1 and R2 must be located near the LP3878-ADJ and connected via traces with no other currents flowing in them (Kelvin connect). The bottom of the R1/R2 divider must be connected directly to the LP3878-ADJ ground pin.



#### 8.2.3 Application Curves



## 9 Power Supply Recommendations

The LP3878-ADJ is designed to operate from an input voltage supply range between 2.5 V and 16 V. The input voltage range provides adequate headroom in order for the device to have a regulated output. This input supply must be well regulated. An input capacitor of at least 4.7 µF is required.

## 10 Layout

#### 10.1 Layout Guidelines


Good PC layout practices must be used or instability can be induced because of ground loops and voltage drops. The input and output capacitors must be directly connected to the input, output, and ground pins of the regulator using traces which do not have other currents flowing in them (Kelvin connect).

The best way to do this is to lay out  $C_{IN}$  and  $C_{OUT}$  near the device with short traces to the IN, OUT, and ground pins. The regulator ground pin should be connected to the external circuit ground so that the regulator and its capacitors have a single point ground.

It should be noted that stability problems have been seen in applications where vias to an internal ground plane were used at the ground points of the IC and the input and output capacitors. This was caused by varying ground potentials at these nodes resulting from current flowing through the ground plane. Using a single-point ground technique for the regulator and its capacitors fixed the problem.

Because high current flows through the traces going into IN and coming from OUT, Kelvin connect the capacitor leads to these pins so there is no voltage drop in series with the input and output capacitors.

### 10.2 Layout Example



### 10.3 Power Dissipation

The LP3878-ADJ is offered in the 8-lead SO PowerPAD or WSON surface-mount packages to allow for increased power dissipation compared to the SO-8 and Mini SO-8. For details on thermal performance as well as mounting and soldering specifications, refer to Application Note *AN-1187*, SNOA401.

## **11** Device and Documentation Support

#### **11.1 Documentation Support**

#### 11.1.1 Related Documentation

For related documentation see the following:

Application Note AN-1187, SNOA401

#### 11.2 Trademarks

PowerPAD is a trademark of Texas Instruments.

### **11.3 Electrostatic Discharge Caution**



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

### 11.4 Glossary

#### SLYZ022 — TI Glossary.

This glossary lists and explains terms, acronyms, and definitions.

## 12 Mechanical, Packaging, and Orderable Information

The following pages include mechanical, packaging, and orderable information. This information is the most current data available for the designated devices. This data is subject to change without notice and revision of this document. For browser-based versions of this data sheet, refer to the left-hand navigation.



## **PACKAGING INFORMATION**

Orderable Device	Status (1)	Package Type	Package Drawing	Pins	Package Qty	Eco Plan (2)	Lead/Ball Finish (6)	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
LP3878MR-ADJ	NRND	SO PowerPAD	DDA	8	95	TBD	Call TI	Call TI	-40 to 125	3878 MRADJ	
LP3878MR-ADJ/NOPB	ACTIVE	SO PowerPAD	DDA	8	95	Green (RoHS & no Sb/Br)	CU SN	Level-3-260C-168 HR	-40 to 125	3878 MRADJ	Samples
LP3878MRX-ADJ/NOPB	ACTIVE	SO PowerPAD	DDA	8	2500	Green (RoHS & no Sb/Br)	CU SN	Level-3-260C-168 HR	-40 to 125	3878 MRADJ	Samples
LP3878SD-ADJ/NOPB	ACTIVE	WSON	NGT	8	1000	Green (RoHS & no Sb/Br)	CU NIPDAU   CU SN	Level-1-260C-UNLIM	-40 to 125	3878ADJ	Samples
LP3878SDX-ADJ/NOPB	ACTIVE	WSON	NGT	8	4500	Green (RoHS & no Sb/Br)	CU NIPDAU   CU SN	Level-1-260C-UNLIM	-40 to 125	3878ADJ	Samples

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW**: Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

(2) Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check http://www.ti.com/productcontent for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

Green (RoHS & no Sb/Br): TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

(5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.



## PACKAGE OPTION ADDENDUM

15-Dec-2016

<sup>(6)</sup> Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:**The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


## PACKAGE MATERIALS INFORMATION

www.ti.com


Texas Instruments

## TAPE AND REEL INFORMATION





## QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal												
Device	Package Type	Package Drawing		SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
LP3878MRX-ADJ/NOPB	SO Power PAD	DDA	8	2500	330.0	12.4	6.5	5.4	2.0	8.0	12.0	Q1
LP3878SD-ADJ/NOPB	WSON	NGT	8	1000	180.0	12.4	4.3	4.3	1.1	8.0	12.0	Q1
LP3878SDX-ADJ/NOPB	WSON	NGT	8	4500	330.0	12.4	4.3	4.3	1.1	8.0	12.0	Q1

TEXAS INSTRUMENTS

www.ti.com

## PACKAGE MATERIALS INFORMATION

3-Aug-2017



\*All dimensions are nominal

Device	Package Type	Package Drawing	Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
LP3878MRX-ADJ/NOPB	SO PowerPAD	DDA	8	2500	367.0	367.0	35.0
LP3878SD-ADJ/NOPB	WSON	NGT	8	1000	203.0	203.0	35.0
LP3878SDX-ADJ/NOPB	WSON	NGT	8	4500	346.0	346.0	35.0


## **DDA0008B**



## **PACKAGE OUTLINE**

## PowerPAD<sup>™</sup> SOIC - 1.7 mm max height

PLASTIC SMALL OUTLINE



#### NOTES:

PowerPAD is a trademark of Texas Instruments.

- 1. All linear dimensions are in millimeters. Any dimensions in parenthesis are for reference only. Dimensioning and tolerancing per ASME Y14.5M. 2. This drawing is subject to change without notice.
- 3. This dimension does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.15 mm per side.
- 4. This dimension does not include interlead flash. Interlead flash shall not exceed 0.25 mm per side.
- 5. Reference JEDEC registration MS-012.




## DDA0008B

## **EXAMPLE BOARD LAYOUT**

## PowerPAD<sup>™</sup> SOIC - 1.7 mm max height

PLASTIC SMALL OUTLINE



NOTES: (continued)

- 6. Publication IPC-7351 may have alternate designs.
- 7. Solder mask tolerances between and around signal pads can vary based on board fabrication site.
- This package is designed to be soldered to a thermal pad on the board. For more information, see Texas Instruments literature numbers SLMA002 (www.ti.com/lit/slma002) and SLMA004 (www.ti.com/lit/slma004).
- 9. Size of metal pad may vary due to creepage requirement.
- 10. Vias are optional depending on application, refer to device data sheet. If any vias are implemented, refer to their locations shown on this view. It is recommended that vias under paste be filled, plugged or tented.




## DDA0008B

## **EXAMPLE STENCIL DESIGN**

## PowerPAD<sup>™</sup> SOIC - 1.7 mm max height

PLASTIC SMALL OUTLINE




NOTES: (continued)

- 11. Laser cutting apertures with trapezoidal walls and rounded corners may offer better paste release. IPC-7525 may have alternate design recommendations.
- 12. Board assembly site may have different recommendations for stencil design.



## **MECHANICAL DATA**

# NGT0008A



#### IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

TI's products are provided subject to TI's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such TI products. TI's provision of these resources does not expand or otherwise alter TI's applicable warranties or warranty disclaimers for TI products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2019, Texas Instruments Incorporated