## INDUCTORS

## **公TDK**

### Inductors for power circuits Wound ferrite **VLCF** series







#### **FEATURES**

O Magnetic shield type wound inductor for power circuits.

O Low-profile product.

O Magnetic shield construction with ferrite core.

○ Operating temperature range: -40 to +105°C (including self-temperature rise)

#### APPLICATION

O Power source inductor for mobile devices such as HDDs, DVCs, and DSCs ○ LCDs, other DC to DC converters

#### PART NUMBER CONSTRUCTION

VLCF	4020	T  -	1R8	Ν	1R9	- 2	
Series name	L×W×H dimensions 4.0×4.0×2.0 mm	Packaging style	Inductance (µH)	Inductance tolerance	Rated current (A)	Internal co	ode

#### CHARACTERISTICS SPECIFICATION TABLE

L		Measuring DC resistance frequency		Rated curre	nt*	Part No.	
					Isat	Itemp	
(µH)	Tolerance	(kHz)	<b>(</b> Ω <b>)max.</b>	<b>(</b> Ω <b>)typ.</b>	(A)max.	(A)typ.	
1.8	±30%	100	0.051	0.046	1.97	2.37	VLCF4020T-1R8N1R9
2.2	±30%	100	0.059	0.054	1.72	2.19	VLCF4020T-2R2N1R7
3.3	±30%	100	0.078	0.071	1.52	1.94	VLCF4020T-3R3N1R5
4.7	±30%	100	0.098	0.089	1.24	1.71	VLCF4020T-4R7N1R2
6.8	±30%	100	0.131	0.119	1.05	1.47	VLCF4020T-6R8N1R0
10	±20%	100	0.185	0.168	0.85	1.22	VLCF4020T-100MR85
15	±20%	100	0.303	0.275	0.68	1.0	VLCF4020T-150MR68
22	±20%	100	0.431	0.391	0.56	0.8	VLCF4020T-220MR56
27	±20%	100	0.496	0.451	0.48	0.8	VLCF4020T-270MR48
33	±20%	100	0.628	0.571	0.47	0.69	VLCF4020T-330MR47
47	±20%	100	0.934	0.849	0.39	0.56	VLCF4020T-470MR39
100	±20%	100	1.4	1.308	0.26	0.45	VLCF4020T-101MR26

\* Rated current: smaller value of either Isat or Itemp.

Isat: When based on the inductance change rate (30% below the initial value)

Itemp: When based on the temperature increase (temperature increase of 40°C by self heating)

#### Measurement equipment

Measurement item	Product No.	Manufacturer
L	4194A	Keysight Technologies
DC resistance	VP-2941A	Panasonic
Rated current Isat	4285A+42841A+42842C	Keysight Technologies

\* Equivalent measurement equipment may be used.




A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (1/5)

20180831

# VLCF4020 type

## L FREQUENCY CHARACTERISTICS



4294A Keysight Technologies


\* Equivalent measurement equipment may be used.

Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
 (2/5)
 Please note that the contents may change without any prior notice due to reasons such as upgrading.
 20180831

# VLCF4020 type

#### ■ INDUCTANCE VS. DC BIAS CHARACTERISTICS


\* Equivalent measurement equipment may be used.




A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (3/5) 20180831

# VLCF4020 type


#### SHAPE & DIMENSIONS






Dimensions in mm

#### PACKAGING STYLE



Dimensions in mm

#### TAPE DIMENSIONS



Туре	A	В	К
VLCF4020	4.2	4.2	2.2

#### PACKAGE QUANTITY


Package quantity	1000 pcs/reel
i ackage quantity	1000 pc3/reer

#### TEMPERATURE RANGE, INDIVIDUAL WEIGHT

	Operating temperature range*	Storage temperature range**	Individual weight
-40 to 105 °C -40 to 105 °C		–40 to 105 °C	112 mg
*	Operating temperature range includes self-temperature rise.		


\*\* The storage temperature range is for after the assembly.





Dimensions in mm

### RECOMMENDED REFLOW PROFILE



Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use.
(4/5)
Please note that the contents may change without any prior notice due to reasons such as upgrading.
20180831

# **REMINDERS FOR USING THESE PRODUCTS**

Before using these products, be sure to request the delivery specifications.

# SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

<ul> <li>The storage period is less than 6 months. Be sure to follow the sto less).</li> <li>If the storage period elapses, the soldering of the terminal electroc</li> </ul>				
O Do not use or store in locations where there are conditions such as	•			
Before soldering, be sure to preheat components.				
	e difference between the solder temperature and chip temperature			
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.				
O When embedding a printed circuit board where a chip is mounted the overall distortion of the printed circuit board and partial distortion				
<ul> <li>Self heating (temperature increase) occurs when the power is tu design.</li> </ul>	rned ON, so the tolerance should be sufficient for the set thermal			
Carefully lay out the coil for the circuit board design of the non-mag A malfunction may occur due to magnetic interference.	gnetic shield type.			
$\bigcirc$ Use a wrist band to discharge static electricity in your body through	n the grounding wire.			
$\bigcirc$ Do not expose the products to magnets or magnetic fields.				
$\bigcirc$ Do not use for a purpose outside of the contents regulated in the d	elivery specifications.			
ment, industrial robots) under a normal operation and use conditio The products are not designed or warranted to meet the requirement ity require a more stringent level of safety or reliability, or whose far person or property.	ment, personal equipment, office equipment, measurement equip-			
<ul> <li>(1) Aerospace/aviation equipment</li> <li>(2) Transportation equipment (cars, electric trains, ships, etc.)</li> <li>(3) Medical equipment</li> <li>(4) Power-generation control equipment</li> <li>(5) Atomic energy-related equipment</li> <li>(6) Seabed equipment</li> <li>(7) Transportation control equipment</li> <li>When designing your equipment even for general-purpose application tection circuit/device or providing backup circuits in your equipment.</li> </ul>	<ul> <li>(8) Public information-processing equipment</li> <li>(9) Military equipment</li> <li>(10) Electric heating apparatus, burning equipment</li> <li>(11) Disaster prevention/crime prevention equipment</li> <li>(12) Safety equipment</li> <li>(13) Other applications that are not considered general-purpose applications</li> </ul>			

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading. (5/5)