



## DCF921H2T-GB

### DEWALT 18V XR Brushless 1/2" Hog Ring Compact Impact Wrench – 2 x 5.0Ah Powerstack

The DCF921 18V XR Impact Wrench with Hog Ring Anvil was designed to easily handle various fastening projects. Get up to 406Nm of fastening torque and 610Nm of max breakaway torque in a 125mm long body with this compact power tool that offers easy manoeuvrability without sacrificing power. Choose between 4 modes to allow for reliable high-level performance, operability, and versatility. Dark work areas are no problem with this Cordless Impact Wrench, which comes with an LED work light for visibility in dimly lit spaces.

- 406Nm of Fastening Torque
- 610Nm of Breakaway Torque
- Compact 125mm Head Length
- Brushless Motor
- 4 Mode Switch for Accurate Application Control
- Scaffold Mode offers excellent application control for Scaffolders
- 1/2" Anvil with Hog Ring

#### Standard Equipment

- DCF921 Impact Wrench
- 2 x 5.0Ah Powerstack Batteries (DCBP518-XJ)
- Multi-Voltage Charger
- T-Stak Kitbox

BATTERY VOLTAGE	18 V
BATTERY CAPACITY (SUPPLIED)	5.0Ah POWERSTACK
MAX BREAKAWAY TORQUE	609Nm
MAX FASTENING TORQUE	406Nm
DRIVE SIZE	1/2" SQUARE DRIVE
NO LOAD SPEED	0-2500 RPM
IMPACTS PER MINUTE	0-3500 IPM
VIBRATION LEVEL	13m/s <sup>2</sup>
SOUND LEVEL PRESSURE	97dB
SOUND POWER LEVEL	108dB
WEIGHT	1.0Kg

1 YEAR LIMITED WARRANTY, 3 YEAR LIMITED WARRANTY WHEN REGISTERED

We're confident of the quality of our products and we'll repair, without charge, any defects due to faulty materials or workmanship within the specified warranty.