



Taoglas Reach Series - PCS.68.A

Description:

Reach Low Profile Wideband 5G/4G PCB SMD Antenna

Features:

Patent Pending Innovative Low Profile Desigr

High Efficiency Wideband Antenna, Covering 600 to 6000 MHz

Supporting 5G FR1 Bands

600 MHz 5G/4G Band 71 Support

Surface Mount Distribution (SMD) - Supplied on Tape & Reel

Manufactured in an IATF16949 Certified Facility

Dimensions: 42 x 10 x 1.5 mm

RoHS & REACH Compliant



1.	Introduction	3
2.	Specifications	5
3.	Antenna Characteristics	7
4.	Radiation Patterns	11
5.	Mechanical Drawing	16
6.	Matching Circuit	18
7.	Packaging	19
	Changelog	20

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.













1. Introduction



The Taoglas Reach Series PCS.68.A is a revolutionary 5G/4G, low profile, small footprint, patent pending, SMD mount PCB wide-band antenna. The PCS.68.A has been designed to cover all 5G and 4G bands, including all sub-6GHz deployments across the 600MHz to 6000MHz spectrum in a very small footprint of just 42 x 10mm. It also covers 3G/2G bands to allow for fall-back when 5G/4G is not available. The low profile size of just 1.5mm in height allows for installation where height is at a premium.

Typical applications include

- Autonomous/UAVs
- Smart Metering
- Connected Health

- Wearable Technologies
- Payment Terminals

The patent pending design uses printed circuit board material and innovative design techniques to deliver the highest efficiencies at all bands when mounted on the device's main PCB. The PCS.68.A is suitable for lower cost 5G/4G applications, especially IoT projects requiring wide bandwidth and comes supplied on tape and reel to allow it to be mounted via 'pick & place' onto the PCB.

If tuning is required, it can also be tuned specifically depending on device environment. Contact your local Taoglas customer support team for advice on integrating the PCS.68.A into your device.



1.1 Key Advantages

1. Highest efficiency in small footprint

A comparative antenna to the Reach, for example, metal/ceramic/FPC, would have much-reduced efficiency in this configuration due to their high substrate loss at high frequencies. Very high efficiency antennas are critical to 5G/4G devices ability to deliver the stated data-speed rates of systems such as 5G/4G.

2. Low profile

Many applications require a large mechanical size to work efficiently, which occupys the usable PCB space. The size of PCS.68 is only 42mm X 10mm (420mm²), and if accounting for the 4mm keep out area, the total area consumed on the PCB is only 42mmX14mm = 588mm². The solution allows board designers to maximize their PCB space.

3. Adaptable

The high radiation efficiency of the Reach over its entire operating bandwidth means that the total efficiency is only limited by the impedance mismatch loss. As a result, this antenna has been optimized via a matching network to 600 MHz - 960 MHz and 1710 MHz - 6000 MHz with the minimum efficiencies of 30% and 50% respectively. The performance of direct feeding the antenna without a matching circuit is good from 730 MHz - 960 MHz and 1710 MHz - 6000 MHz.

4. More resistant to detuning compared to other antenna integrations

If tuning is required it can be tuned for the device environment using a matching circuit, or other techniques on the main PCB itself. There is no need for new tooling, thereby saving money if customization is required.

5. Surface Mount Device (SMD)

Direct mount, 'on-board' antennas save on labor, cable and connector costs, lead to higher integration yield rates and reduce losses in transmission.

6. Minimum Transmission and Reception Losses

These are kept to an absolute minimum resulting in much improved OTA (over the air), i.e. TRP (Total Radiated Power) / TIS (Total Isotropic Radiation), device performance compared to similar efficiency cable and connector antenna solutions. This means it is an ideal antenna to be used for devices that This means it is an ideal antenna to be used for devices that need to pass for example USA carrier network approvals.



2. Specifications

			Electr	ical				
Band	Frequency (MHz)	Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	VSWR	Impedance	Polarization	Radiation Pattern
5GNR/4G Band 5,8,12,13,14,17,18,20, 26,27,28, 29,71	617~960	45	-3.3	-1				
5GNR/4G Band 21,32,74,75,76	1427~1518	25	-7	-2				
4G/3G Band 1,2,3,4,9,23,25,35,39,66	1710~2200	77	-1.2	3.8				
Wi-Fi 2400	2400~2500	53	-2.7	2	<3.5:1	50 Ω	Linear	Omni
4G/3G Band 7,38,41	2490~2690	62	-2.2	4				
5GNR/4G Band 22,42,43,48,77,78,79	3300~5000	67	-2	4.5				
LTE5200/ Wi-Fi 5800	5150~5925	77	-1	4				

The PCS.86.A antenna performance was measured on a 130 x 42 ground plane

Mechanical			
Dimensions	42mm x 10mm x 1.5mm		
Weight	2g		
Material	PCB		
Termination	Solder Pad		
EVB Connector	SMA-Female		

Environmental			
Operation Temperature	-40°C to 85°C		
Storage Temperature	-40°C to 105°C		
Relative Humidity	Non-condensing 65°C 95% RH		
RoHs & REACH Compliant	Yes		




		5G/4G Bands	
Band Number	5GNR / FR1 / L	TE / LTE-Advanced / WCDMA / HSPA / HSF	PA+ / TD-SCDMA
	Uplink	Downlink	Covered
1	UL: 1920 to 1980	DL: 2110 to 2170	✓
2	UL: 1850 to 1910	DL: 1930 to 1990	✓
3	UL: 1710 to 1785	DL: 1805 to 1880	✓
4	UL: 1710 to 1755	DL: 2110 to 2155	✓
5	UL: 824 to 849	DL: 869 to 894	✓
7	UL: 2500 to 2570	DL:2620 to 2690	✓
8	UL: 880 to 915	DL: 925 to 960	✓
9	UL: 1749.9 to 1784.9	DL: 1844.9 to 1879.9	✓
11	UL: 1427.9 to 1447.9	DL: 1475.9 to 1495.9	✓
12	UL: 699 to 716	DL: 729 to 746	✓
13	UL: 777 to 787	DL: 746 to 756	✓
14	UL: 788 to 798	DL: 758 to 768	✓
17	UL: 704 to 716	DL: 734 to 746	✓
18	UL: 815 to 830	DL: 860 to 875	✓
19	UL: 830 to 845	DL: 875 to 890	✓
20	UL: 832 to 862	DL: 791 to 821	✓
21	UL: 1447.9 to 1462.9	DL: 1495.9 to 1510.9	✓
22	UL: 3410 to 3490	DL: 3510 to 3590	✓
23	UL:2000 to 2020	DL: 2180 to 2200	✓
24	UL:1625.5 to 1660.5	DL: 1525 to 1559	✓
25	UL: 1850 to 1915	DL: 1930 to 1995	✓
26	UL: 814 to 849	DL: 859 to 894	✓
27	UL: 807 to 824	DL: 852 to 869	✓
28	UL: 703 to 748	DL: 758 to 803	✓
29	UL: -	DL: 717 to 728	✓
30	UL: 2305 to 2315	DL: 2350 to 2360	✓
31	UL: 452.5 to 457.5	DL: 462.5 to 467.5	×
32	UL: -	DL: 1452 – 1496	✓
35		✓	
38	2570 to 2620		
39	1880 to 1920 ✓		
40	2300 to 2400		
41	2496 to 2690		✓
42		✓	
43		3600 to 3800	✓
48		3550 to 3700	✓
66	UL: 1710-1780	DL: 2110-2200	✓
71		617 to 698	✓
74/75/76		1427 to 1518	✓
77		3300 to 4200	✓
78		3300 to 3800	✓
79		4400 to 5000	✓




3. Antenna Characteristics

3.1 Test Setup




On Evaluation Board

3.2 Return Loss



Analysis of the effect of reducing ground plane length


3.3 VSWR



Analysis of the effect of reducing ground plane length




3.4 Efficiency



Analysis of the effect of reducing ground plane length


3.5 Peak Gain



Analysis of the effect of reducing ground plane length



3.6 Average Gain





Analysis of the effect of reducing ground plane length



4. Radiation Patterns (Measured on 130 X 42mm EVB)


4.1 800MHz 3D and 2D Radiation Patterns









4.2 1470MHz 3D and 2D Radiation Patterns









4.3 1910MHz 3D and 2D Radiation Patterns









4.4 2550MHz 3D and 2D Radiation Patterns









4.5 4500MHz 3D and 2D Radiation Patterns








5. Mechanical Drawing (Units: mm)






5.2 Evaluation Board Drawing





6. Matching Circuit





Circuit Symbol	Size	Description
L1	0402	12nH inductor (TDK MLK1005S12NJ)
C1	0402	3.3pF Capacitor (CRM0335C1E3R3CD01)



330mm

19

330mm

350mm

7. Packaging

800 pcs PCS.68.A per Tape & Reel Dimensions: 330*330*60mm Weight: 2.5Kg

1 reel in small inner box Dimensions: 350*350*70mm Weight: 2.6Kg


2400 pcs in one carton Dimensions: 370*360*275mm

Weight: 8Kg

275mm 360mm 370mm

70mm

Pallet Dimensions: 1200*1320*1000mm 24 Cartons Per Pallet 6 Cartons Per Layer 4 Layers





Changelog for the datashee

SPE-19-8-129 - PCS.68.A

Revision: D (Current	: Version)
Date:	2020-03-06
Notes:	Updated drawing and pictures
Author:	Jack Conroy

Previous Revisions



www.taoglas.com

