



(air),

±8kV



# DESCRIPTION

The KSM Series is designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.

KSM Series has beens pecifically designed protect sensitive components which are connected to power data and transmission lines from overvoltage caused by ESD(electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

# MACHANICAL DATA

unidirectional lines

♦Low clamping voltage

♦Low leakage current

♦SOT-23 package

FEATURES

♦IEC61000-4-2

(contact)

♦ Flammability Rating: UL 94V-0

♦Working voltages: 3.3V to 36V

- ♦ Packaging: Tape and Reel
- $\diamond$  High temperature soldering guaranted:260  $^{\circ}$ C /10s

(ESD)

♦350 Watts Peak Pulse Power per (tp=8/20µs)

♦IEC61000-4-4 (EFT) 40A (5/50ns)

♦ Protects one bidirectional line or two

±15kV

- ♦Reel size: 7 inch
- ♦MSL 1

## ORDERING INFORMATION

♦ Package: SOT-23

♦ Material: Halogen free


♦ Packing: Tape & Reel

♦ Quantity per reel: 3,000pcs

# **APPLICATIONS**

- ♦ Cell Phone Handsets and Accessories
- ♦ Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- ♦ Notebooks, Desktops, and Servers
- ♦ Portable Instrumentation
- ♦ Networking and Telecom
- ♦ Serial and Parallel Ports.
- ♦ Peripherals

## PIN CONFIGURATION



# PACKAGE OUTLINE





ABSOLUTE MAXIMUM RATING									
Symbol	Parameter	Value	Units						
V <sub>ESD</sub>	ESD per IEC 61000-4-2 (Air)	±15	kV						
	ESD per IEC 61000-4-2 (Contact)	±8	·						
P <sub>PP</sub>	Peak Pulse Power (8/20μs)	350	W						
T <sub>OPT</sub>	Operating Temperature	-55/+150	°C						
T <sub>STG</sub>	Storage Temperature	-55/+150	°C						
T <sub>L</sub>	Lead Soldering Temperature	260 (10 sec.)	°C						

ELECTRICAL CHARACTERISTICS (Tamb=25°C)												
PART NUMBER	DEVICE MARKING	V <sub>RWM</sub> (V) (max.)	V <sub>B</sub> (V) (min.)	I <sub>T</sub> (mA)	V <sub>C</sub> @1A (V) (max.)	V <sub>C</sub> (V) (max.) (@A)		I <sub>R</sub> (μΑ) (max.)	C <sub>J</sub> (pF) (max.)			
KSM03	M03	3.3	4	1	7.0	14	20	40	450			
KSM05	M05	5	6	1	9.8	18	17	10	300			
KSM08	M08	8	8.5	1	13.4	24	15	2	240			
KSM12	M12	12	13.3	1	19	32	11	1	130			
KSM15	M15	15	16.7	1	24	38	10	1	120			
KSM18	M18	18	20	1	29	45	9	1	100			
KSM20	M20	20	22.3	1	35	50	8	1	90			
KSM24	M24	24	26.7	1	43	52	7	1	80			
KSM36	M36	36	40	1	60	75	5	1	60			



