

GRT188R61A106KE13#

“#” indicates a package specification code.



< List of part numbers with package codes >

GRT188R61A106KE13D GRT188R61A106KE13J

Appearance & Shape



References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|------------------|---------------------------|
| D | 180mm Paper Tape | 4000 |
| J | 330mm Paper Tape | 10000 |

| Mass (typ.) | |
|-------------|-------|
| 1 piece | 8.1mg |
| φ180mm Reel | 154g |

Notices

Derating1

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT188R61A106KE13#

“#” indicates a package specification code.

Specifications

| | |
|--|---------------|
| Length | 1.6±0.15mm |
| Width | 0.8±0.15mm |
| Thickness | 0.8±0.15mm |
| Capacitance | 10µF ±10% |
| Distance between external terminals g | 0.6mm min. |
| External terminal size e | 0.2 to 0.55mm |
| Operating Temperature Range | -55°C to 85°C |
| Rated Voltage | 10Vdc |
| Size code in inch(mm) | 0603 (1608M) |
| Capacitance change rate | ±15.0% |
| Temperature characteristics (complied standard) | X5R(EIA) |
| Temperature range of temperature characteristics | -55°C to 85°C |

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


GRT188R61A106KE13#

"#" indicates a package specification code.




Characteristic Data


The charts below may show another part number which shares its characteristics.




GRT188R61A106KE13 |Z| DCOV, 25degC



GRT188R61A106KE13 R DCOV, 25degC



GRT188R61A106KE13 C-DC bias capchange, 25.0degC, AC0.




GRT188R61A106KE13 C-AC Voltage capchange, DCOV, 25.0d

Attention


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GRT188R61A106KE13#

"#" indicates a package specification code.



GRT188R61A106KE13 C-Temp. capchange, DCO. 0V, ACO. 5Vrm



GRT188R61A106KE13 Temp. rise ■ 80kHz ■ 400kHz ■ 800kHz

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.