



## TECHNICAL DATA SHEET

### RS 764-3023 White Gloss Paint

RS 764-3023 is from a range of quick drying, high quality, universal spray paints based on alkyd resins. It exhibits excellent coverage and hardness characteristics and is ideally suited for use in manufacturing, repair and for home and workshop use.

- Excellent coverage & flow; easy to apply
- Fast drying with high opacity; various colours available
- Excellent hardness and very good adhesion to bare metal
- Very good resistance to water and other and chemicals; ideal for a variety of applications

<b>Typical Properties:</b>	Gloss	Gloss 90 angle of 60°
	Satin	25 angle of 60°
	Coverage @ ~20µm	1.0-1.5 m <sup>2</sup> (depends on colour)
	Drying time @ 20°C	15 minutes (surface)
		3 hours (touch dry)
		24 hours (full cure)
	Maximum Temperature (°C)	110

<b><u>Description</u></b>	<b><u>Packaging</u></b>	<b><u>Order Code</u></b>
White Gloss	400ml Aerosol	RS 764-3023

#### **Directions for Use**

- Ensure that surface is dry, smooth and free from dust and grease.
- To test, paint a sample panel in advance. Check synthetic and plastic substrates for adhesion and compatibility. For plastics such as PP and EPDM, a primer coat should be applied first.
- Shake the spray-can well for at least 2 minutes and at intervals during use.
- Spray, (holding the aerosol vertically), at a distance of 25-30 cm from the object to be painted. Best results are obtained by applying several thin coats rather than one single thick coat. Wait a few minutes, with a maximum of 30 minutes, between the applications of each layer.
- After use, clear the valve by spraying with the can inverted
- If repainting is necessary, this should be after 24 hours. Drying of the synthetic paint depends on the thickness of the layer and the ambient temperature.