

929387-1 ✓ ACTIVE

AMP | MQS

TE Internal #: 929387-1

Automotive Terminals, Receptacle, Mating Tab Width .63 mm [.025 in], Tab Thickness .63 mm [.025 in], Tin (Sn) Interface Plating, MQS

[View on TE.com >](#)



Terminals & Splices > Automotive Terminals > MQS, RECEPTACLE AND TAB



Terminal Type: **Receptacle**

Mating Tab Width: **.63 mm [.025 in]**

Mating Tab Thickness: **.63 mm [.025 in]**

Terminal Transmits: **0 – 24 A (Low Power)**

Sealable: **No**

[All MQS, RECEPTACLE AND TAB \(126\)](#)

Features

Product Type Features

Sealable	No
Primary Locking Feature	Locking Lance

Contact Features

Contact Size	.63mm
Contact Fabrication	Stamped & Formed
Wire Contact Termination Area Plating Material	Tin
Typical Current Rating	7.5 A
Crimp Type	FFC
Terminal Type	Receptacle
Mating Tab Width	.63 mm[.025 in]
Mating Tab Thickness	.63 mm[.025 in]
Interface Plating	Tin (Sn)

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire

Dimensions

--	--



Wire Size Search	20 AWG, 21 AWG, 22 AWG, 23 AWG
------------------	--------------------------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature (Max)	80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Quantity	12500
Packaging Method	Reel

Other

Terminal Transmits	0 – 24 A (Low Power)
--------------------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits

as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 91092-1
ET FFC




TE Part # 1-528013-1
FFC PISTOL GRIP HAND TOOL CASE



TE Part # 1579001-4
DIE SET MQS 1.2



TE Part # 2329120-1
12POS,0.63X0.63,TAB HSG,UNSLD, COD 1



TE Part # 91093-1
ET FFC



TE Part # 2394880-3
FFC BASE MACHINE MARK II, ENGLISH



TE Part # 1-91047-0
ET FFC CARD EDGE 10 POS



TE Part # 1-91047-2
ET FFC CARD EDGE 35 POS



TE Part # 1-91047-4
ET FFC CARD EDGE 12 POS



TE Part # 1-91047-5
ET FFC CARD EDGE 14 POS



TE Part # 1-91047-6
ET FFC CARD EDGE



TE Part # 1-91047-8
ET FFC CARD EDGE



TE Part # 1-91047-9
EXTR. TOOL, 3 BLADES




TE Part # 2-91047-6
FFC EXTRACTION TOOL









TE Part # 5-528441-3
FFC APPLICATOR MQS TERMINALS



TE Part # 91047-1
ET FFC CONN 9 POS



Also in the Series | **MQS**



Customers Also Bought





Documents

Product Drawings

MQS0,63 Sn rec LL unseal. FFC

English

CAD Files

Customer View Model

[ENG_CVM_929387-1_A2.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_929387-1_A2.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_929387-1_A2.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Micro Quadlok Interconnection System (MQS)

English

Product Specifications

Application Specification

English