



Features:

- Silicon Planar Power Zener Diodes
- Standard Zener Voltage Tolerance is $\pm 5\%$ with a "B" Suffix, and $\pm 10\%$ with a "A" Suffix. other Tolerances are Available Upon Request

Mechanical Data

- Case: JEDEC MINI-MELF, Glass Case
- Terminals: Solderable per MILSTD-202, Method 208
- Polarity: Colour Band Denotes cathodes end
- Weight: Approx. 0.031g
- Mounting Position: Any

Maximum Ratings and Thermal Characteristics

(T_A=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Power dissipation at T _a =75°C (Note 1)	P _{tot}	500	mW
Maximum thermal resistance junction to ambient (Note 1)	R _{θJA}	300	k/W
Junction and Storage temperature range	T _J , T _{STG}	-55 to +175	°C

Notes:

(1) Valid provided that electrodes are kept at ambient temperature.

Electrical Characteristics:


(Ratings at 25°C ambient temperature unless otherwise specified).

Part Number	Nominal Zener Voltage		Maximum Zener Impedance		Typical Temperature Coefficient	Maximum Reverse Leakage Current		Maximum DC Zener Current
	V _Z @ I _{ZT}	I _{ZT}	Z _{ZT} @ I _{ZT}	Z _{ZK} @ I _{ZK} (Note 1)	αV _Z	I _R @ V _R		I _{ZM}
	(V)	(mA)	(Ω)	(Ω)	%/°C	(μA)	(V)	(mA)
ZMM5232B-7	5.6	20	11	1,600	+0.038	5	3	81
ZMM5236B-7	7.5		6	500	+0.058	3	6	61
ZMM5248B-7	18	7	21	600	+0.085	0.1	14	25
ZMM5265B-7	62	2	185	1,400	+0.097		47	-

Notes:

(1) I_{ZK}=0.25mA

Package Outline Dimensions



MINI-MELF

Dimensions : Millimetres

Part Number Table

Description	Part Number
Zener Diode	ZMM5232B-7
	ZMM5236B-7
	ZMM5248B-7
	ZMM5265B-7

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro