



As supplied (a)



After unrestricted recovery (b)



Applications

Use in conjunction with Raychem adapters to provide strain relief for harness systems using circular connectors.

Boot is compatible with all Raychem grooved adapters of the appropriate shell size.

Materials Available

Material*	Material description	Precoating no.	Adhesive part no.**
-3	Semirigid polyolefin	/42 or /86	S-1017 or S-1048
-4	Flexible polyolefin	/42 or /86	S-1017 or S-1048
-12	Viton		
-25	Fluid-resistant elastomer	/42 or /86 or /225	S-1017 or S-1048
-100	Polyolefin, Zerohal	/86 or /180	S-1030 or S-1048

*For more information, please see the appropriate material page in this section.

**For more information, please see Section 5 of this catalog.

Product Dimensions (mm/in)

Part number	H		J		Min. -100	Max.	P	R
	Min. -3, -4, -12, -25	Max.	Min. -3, -4, -25	Min. -12				
202K121	24.0 (.95)	10.4 (.41)	24.0 (.95)	13.0 (.51)	14.0 (.55)	5.6 (.22)	38.0 (1.50)	21.0 (.83)
202K132	30.0 (1.18)	14.2 (.56)	30.0 (1.18)	14.0 (.55)	15.0 (.59)	5.9 (.23)	55.0 (2.17)	32.0 (1.26)
202K142	31.0 (1.22)	18.0 (.71)	31.0 (1.22)	16.0 (.63)	18.0 (.71)	7.1 (.28)	67.0 (2.64)	35.0 (1.38)
202K153	36.0 (1.42)	22.4 (.88)	36.0 (1.42)	19.0 (.75)	21.0 (.83)	8.4 (.33)	80.0 (3.15)	42.0 (1.65)
202K163	43.0 (1.69)	28.2 (1.11)	43.0 (1.69)	22.0 (.87)	25.0 (.98)	9.9 (.39)	99.0 (3.90)	61.0 (2.40)
202K174	60.0 (2.36)	35.1 (1.38)	60.0 (2.36)	35.0 (1.38)	39.0 (1.54)	15.7 (.62)	130.0 (5.12)	72.0 (2.83)
202K185	66.0 (2.60)	44.5 (1.75)	66.0 (2.60)	38.0 (1.50)	42.0 (1.65)	16.8 (.66)	170.0 (6.69)	90.0 (3.54)

	U	JO	HW	JW	X	Y
	±10% b	±10% b	±20% b	Min. b	±20% b	±20% b
202K121	12.0 (.47)	8.5 (.33)	1.6 (.06)	.41 (.016)	24.0 (.94)	13.0 (.51)
202K132	12.0 (.47)	11.5 (.45)	1.8 (.07)	.81 (.032)	24.0 (.94)	18.0 (.71)
202K142	20.0 (.79)	17.0 (.67)	1.8 (.07)	.81 (.032)	32.0 (1.26)	25.0 (.98)
202K153	20.0 (.79)	19.5 (.76)	2.0 (.08)	.81 (.032)	32.0 (1.26)	30.0 (1.18)
202K163	20.0 (.79)	21.0 (.82)	2.2 (.08)	.81 (.032)	52.0 (2.05)	30.0 (1.18)
202K174	20.0 (.79)	39.0 (1.53)	3.3 (.13)	1.02 (.040)	52.0 (2.05)	50.0 (1.97)
202K185	20.0 (.79)	51.5 (2.02)	3.8 (.15)	1.63 (.064)	52.0 (2.05)	70.0 (2.76)