

Specification for Speaker		Page	2/9
Model No. : KP2415SP3-E581-BOX-5873		Revision No.	1.0
		Drawing No.	KFC5873
<h2>CONTENTS</h2> <ol style="list-style-type: none"> <li>1. Scope</li> <li>2. General</li> <li>3. Electrical and Acoustic Characteristics.</li> <li>4. Reliability Test</li> <li>5. Measurement Block Diagram &amp; Response curve</li> <li>6. Structure</li> <li>7. Dimensions</li> <li>8. Packing</li> <li>9. Revision</li> </ol>			

Specification for Speaker		Page	3/9
Model No. : KP2415SP3-E581-BOX-5873		Revision No.	1.0
		Drawing No.	KFC5873

### 1. Scope

This specification is applied to the dynamic speaker which is used all of the electrical acoustic product.

-- compact, rich sound

-- applications: mobile phone, PDA, notebook computer, etc. ...

### 2. General

2.1 Out-Diameter : 54x18 mm

2.2 Height : 4.1 mm

2.3 Weight : 6 g

2.4 Operating Temperature range:

-20~+50℃ without loss of function


2.5 Store Temperature range:

-30~+60℃ without loss of function

### 3. Electrical and Acoustic Characteristics.

Test condition : 15 ~ 35 ℃, 25% ~ 85% RH, 860~1060 mbar

No	Items	Specification
1	Impedance	8 Ω ± 15% (1Vrms at 2KHz)
2	Sound Pressure Level	88 dB ± 3dB (0.1w/0.1m at 1.0;1.2;1.5;2.0kHz average)
3	Resonance Frequency	550 Hz ± 20%
4	Frequency Range	Fo ~20KHz
5	Input Power	Rated 0.8 W / Max. 1 W
6	Distortion	10% Max. at 1kHz/1Vrms
7	Buzz and Rattle	Should not be audible buzzers,rattles when the 2.53V sine wave signal swept at frequency range.
8	Polarity	When supplied plus D.C. voltage to (+) terminal, the cone diaphragm must move to forward.

Specification for Speaker		Page	4/9
Model No. : KP2415SP3-E581-BOX-5873		Revision No.	1.0
		Drawing No.	KFC5873
<h2>4. Reliability Test</h2> <p>After test(1~7item), the speaker S.P.L . difference shall be within <math>\pm 3\text{dB}</math>, and the appearance not exist any change to be harmful to normal operation (e.g. cracks,rusts,damages and especially distortion).</p>			
No	Items	Specification	
1	High Temperature Test	After being placed in a chamber with $+60\pm 3\text{ }^{\circ}\text{C}$ for 96 hours and then being placed in natural condition for 1 hour, speaker shall be measured.	
2	Low Temperature Test	After being placed in a chamber with $-30\pm 3\text{ }^{\circ}\text{C}$ for 96 hours and then being placed in natural condition for 1 hour, speaker shall be measured.	
3	Humidity Test	After being placed in a chamber with 85 to 90%R.H. at $+40\pm 2\text{ }^{\circ}\text{C}$ for 96 hours and then being placed in natural condition for 1 hour, speaker shall be measured.	
4	Thermal Shock Test	<p>After being placed in a chamber at <math>+50^{\circ}\text{C}</math> for 1 hour, then speaker shall be placed in a chamber at <math>-20^{\circ}\text{C}</math> for 1 hour(1 cycle is the below diagram).</p> <p>After 4 above cycles, speaker shall be measured after being placed in natural condition for 10 Sec..</p> 	
5	Vibration Test	After being applied vibration of amplitude of 1.5mm with 10 to 55Hz band of vibration frequency to each of 3 perpendicular directions for 1 hour, then placed in natural condition for 1 hour, speaker shall be measured.	
6	Drop Test	The speaker when mounted in the jig which weight 85g~100g, shall with stand 15 times random drops from a height of 1.5 meter to a concrete floor faced with 5mm thick hard wood board.and be nothing mechanical damage.	
7	Load test	After being applied loading white noise with input power 0.8W(2.53Vrms.) for 96 hours, then placed in natural condition for 1 hour, speaker shall be measured.	
8	Insulation test	When they are measured with DC 100V the insulation resistance between v.c. terminal and frame must be more than 1 MΩ	

# Specification for Speaker

Page

5/9

Model No. : KP2415SP3-E581-BOX-5873


Revision No.

1.0

Drawing No.

KFC5873


## 5. Measurement Block Diagram & Response curve



[dB/20.0u Pa]


Output Response (Signal) - Input Magnitude

Working : Input : Input : SSR Analyzer



Specification for Speaker		Page	6/9
Model No. : KP2415SP3-E581-BOX-5873		Revision No.	1.0
		Drawing No.	KFC5873

6. Structure



9	YOKE	1	SPCC	
8	Terminal	1	Epoxy PCB	
7	Gasket	1	PE	
6	Frame	1	ABS	
5	Magnet	1	Nd-Fe-B	
4	Plate	1	SPC	
3	Voice Coil	1	Copper	
2	Diaphragm	1	PEN	
1	Shell	1set	ABS	
No.	Part Name	Q'ty	Material	Remarks



Specification for Speaker		Page	8/9
Model No. : KP2415SP3-E581-BOX-5873		Revision No.	1.0
		Drawing No.	KFC5873
<h2>8. Packing</h2> <p>Each minimum package unit of products shall be in a carton box and it shall be clearly marked with Part Number ,quantity and outgoing inspection number.</p> <p>There shall be no mechanical damage on products during transportation and/or in storage.</p>			

[illegible]