


Capacitor, film, Metallized Polypropylene, 10 uF, +/-5% Tol, -40/+85C, DC Link



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	42.5	NOM
H	37	NOM
T	28	NOM
S	37.5	+/-0.4
S1	10.2	+/-0.4
LL	6	-2

Notes:

-F = 1.2 nom

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	DC Link
Style:	Radial Box
RoHS:	Yes

Specifications	
Capacitance:	10 uF
Voltage:	1100 V
Tolerance:	+/-5%
Rated Temperature:	70C
Temperature Range:	-40/+85C
Maximum dVdT:	20 v/us
Current/Ripple Current:	11 Amps (10kHz 70C)
Current/Ripple Current:	196 Amps (Peak)
Resistance/ESR:	6.3 mOhms (10kHz 70C)
Inductance:	30 nH
Miscellaneous:	Thermal Resistance = 44 C/W

Packaging Specifications	
Package Kind:	Bulk