

## 8.89mmx3.81mm LED LIGHT BAR

Part Number: KB-2500SGW SUPER BRIGHT GREEN


### **Features**


- •UNIFORM LIGHT EMITTING AREA.
- •LOW CURRENT OPERATION.
- ●EASILY MOUNTED ON P.C. BOARDS.
- •FLUSH MOUNTABLE.
- ●EXCELLENT ON/OFF CONTRAST.
- •CAN BE USED WITH PANELS AND LEGEND MOUNTS.
- •CATEGORIZED FOR LUMINOUS INTENSITY.
- RoHS COMPLIANT.


## **Description**


The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

## Package Dimensions & Internal Circuit Diagram









### Notes:

- 1. All dimensions are in millimeters (inches), Tolerance is  $\pm 0.25 (0.01")$  unless otherwise noted.
- 2. Specifications are subject to change without notice.

SPEC NO: DSAA4640 REV NO: V.5 DATE: AUG/15/2006 PAGE: 1 OF 3

APPROVED: J. Lu CHECKED: Joe Lee DRAWN: Z.Z.YANG

# **Kingbright**

## **Selection Guide**

Part No.	Dice	Lens Type	lv (ucd) [1] @ 20mA	
			Min.	Тур.
KB-2500SGW	SUPER BRIGHT GREEN (GaP)	WHITE DIFFUSED	12000	40000

#### Note:

## Electrical / Optical Characteristics at Ta=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Green	565		nm	I <sub>F</sub> =20mA
λD [1]	Dominant Wavelength	Super Bright Green	568		nm	I=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Green	30		nm	I <sub>F</sub> =20mA
С	Capacitance	Super Bright Green	15		pF	V <sub>F</sub> =0V;f=1MHz
V <sub>F</sub> [2]	Forward Voltage	Super Bright Green	2.2	2.5	V	I=20mA
IR	Reverse Current	Super Bright Green		10	uA	V <sub>R</sub> = 5V

## Notes:

1.Wavelength: +/-1nm.

## Absolute Maximum Ratings at Ta=25°C

Parameter	Super Bright Green	Units		
Power dissipation	105	mW		
DC Forward Current	25	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 5 Seconds			

## Notes:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.


2. 2mm below package base.

SPEC NO: DSAA4640 REV NO: V.5 DATE: AUG/15/2006 PAGE: 2 OF 3
APPROVED: J. Lu CHECKED: Joe Lee DRAWN: Z.Z.YANG

<sup>1.</sup> Luminous intensity / luminous Flux: +/-15%.


<sup>2.</sup> Forward Voltage: +/-0.1V.


# Kingbright





**Super Bright Green** 

**KB-2500SGW** 









SPEC NO: DSAA4640 APPROVED: J. Lu REV NO: V.5 CHECKED: Joe Lee DATE: AUG/15/2006 DRAWN: Z.Z.YANG PAGE: 3 OF 3