



1810
SLEEVE NUT METRIC

maximum working pressure	bar 80	MPa 8,0	psi 1160
working temperature	°C (Celsius) From -40 to 250	F (Fahrenheit) From -40 to 482	K (Kelvin) From 233 to 523
body	stainless steel 316L		

	legris connectic	ØD (mm)	C	F (mm)	L (mm)	(kg)
1810 06 00		6	M10x1	13,0	11,0	0,007
1810 08 00		8	M12x1	14,0	13,0	0,007
1810 10 00		10	M16x1,5	19,0	15,0	0,017
1810 12 00		12	M18x1,5	22,0	15,0	0,024
1810 16 00		16	M22x1,5	27,0	17,0	0,040

