308TX-N Industrial Ethernet Switch

N-Tron Networking Series



Unmanaged Industrial Ethernet Switch

The N-TRON[®] 308TX is an unmanaged, four port Industrial Ethernet Switch. It is housed in a ruggedized DIN-RAIL enclosure, and is designed for use in industrial data acquisition, control, and Ethernet I/O applications.

PRODUCT FEATURES

- Compact Size, Small Footprint
- Full IEEE 802.3 and 1613 Compliance
- NEMA TS1/TS2 Compliance
- · American Bureau of Shipping (ABS) Type Approval
- · Extended Environmental Specifications
- · Eight 10/100 BaseTX RJ-45 Ports
- · Supports Full/Half Duplex Operation
- LED Link/Activity Status Indication
- · Store-and-Forward Technology
- · Auto Senses Speed and Flow Control
- MDIX Auto Cable Sensing (RJ-45)
- Up to 1.0 Gb/s Maximum Throughput
- Rugged Industrial DIN-RAIL Enclosure
- Redundant Power Inputs (10-30 VDC)
- N-View[™] OPC Switch Monitoring Option

PRODUCT OVERVIEW

The 308TX Industrial Network Switch is designed to meet and exceed the most demanding industrial communication requirements while providing high throughput and minimum downtime.

The 308TX provides eight RJ-45 auto sensing 10/100BaseTX ports. All ports are full/half duplex capable, using state-of-the-art Ethernet switching technology. The 308TX auto-negotiates the speed and flow control capabilities of the TX copper port connection, and configures itself automatically.

The 308TX is auto sensing, so there will be no need to make extensive wiring changes if upgrades are made to host computers, plant systems, or Ethernet I/O modules. The switching fabric simply scales up or down automatically to match network environments.

The 308TX supports up to 4,000 MAC addresses, enabling these products to support extremely sophisticated and complex network architectures.

The 308TX is an ideal candidate for upgrading existing hubs and repeaters to increase bandwidth and determinism by virtually eliminating network collisions. The product provides a cost effective solution while maintaining the plug & play simplicity of an unmanaged hub.



The 308TX simplifies plant wiring by eliminating the need to bring data acquisition and control network connections back to a climate controlled environment. The 308TX has extended operating environmental specifications to meet the harsh needs of the industrial environment. For cost savings and convenience the network switch can be DIN-RAIL mounted alongside Ethernet I/O or other Industrial Equipment.

The unique compact size provides a small footprint, conserving space in the most critical dimension. The 308TX can also be panel mounted if desired.

To increase reliability, the 308TX contains redundant power inputs. LED's are provided to display power on/off status as well as the link status and activity of each port.

N-VIEW OPC PORT MONITORING (With -N Option Only)

The N-TRON N-View OLE for Process Control (OPC) Server Software can be combined with popular HMI software packages to add network traffic monitoring, trending and alarming to any application using N-TRON switches configured with the N-View option. N-TRON's N-View OPC Server collects 41 different traffic variables per port and 5 system level variables per switch. This information can provide a complete overview of the network load, service quality, and packet traffic. OPC client software can use N-View OPC Server data to resolve network problems quickly and improve system reliability.



SPECIFICATIONS

Case Dimensions

Height:	3.5"	(8.8 cm)
Width:	2.1"	(5.4 cm)
Depth:	3.4"	(8.6 cm)
Weight:	0.75 lbs	(0.34 kg)

Electrical

Input Voltage: Input Current: Inrush:

Environmental

Operating Temperature: Storage Temperature: Operating Humidity: Operating Altitude: -40°C to 70°C -40°C to 85°C 10% to 95% (Non Condensing) 0 to 10,000 ft.

Shock and Vibration (bulkhead mounting)

Shock: Vibration/Seismic: 200g @ 10ms 50g, 5-200Hz, Triaxial

Network Media 10BaseT: 100BaseTX:

≥Cat3 Cable ≥Cat5 Cable

10-30 VDC

250 mA@24V

9.0Amp/0.5ms@24V

Connectors

10/100BaseTX:	Eight (8) RJ-45 TX
10/100800170	

Recommended Wiring Clearance

Front: Top: 2" (5.08 cm) 1" (2.54 cm) Ports

Regulatory Approvals

FCC Part 15 Class A UL Listed 1604 (US and Canada) CLASS I, DIV 2, GROUPS A,B,C,D,T4A CE: EN61000-6-2,4, EN55011, EN61000-4-2,3,4,5,6 ABS Type Approval for Shipboard Applications IEEE 1613 for Electric Utility Substations GOST-R Certified RoHS Compliant

BENEFITS

Industrial Network Switch

- Compact Size, Small Footprint
- · High Reliability/Availability
- · Extended Environmental Specifications
- Ruggedized DIN-RAIL Enclosure
- High Performance
- High MTBF >2M Hours (measured)


Ease of Use

- Plug & Play Operation
- Eight Auto Sensing 10/100BaseTX RJ-45 Ports
- Auto Sensing Duplex, Speed, and Cable Type
- Unmanaged Operation
- Compact DIN-RAIL Package

Increased Performance

- Full Wire Speed Capable
- Full Duplex Capable
- Eliminates Network Collisions
- Increases Network Determinism
- N-View Switch Viewing Option

ORDERING INFORMATION



Where: N = N-View Firmware Option


XX = ST for ST style fiber connector, SC for SC style fiber connector

YY = Segment length:

15 for 15km max. fiber segment length

40 for 40km max. fiber segment length

80 for 80km max. fiber segment length





Americas sales@redlion.net

Asia-Pacific asia@redlion.net

Europe Middle East Africa europe@redlion.net As the global experts in communication, monitoring and control for industrial automation and networking, Red Lion has been delivering innovative solutions for over forty years. Our award-winning technology enables companies worldwide to gain real-time data visibility that drives productivity. Product brands include Red Lion, N-Tron and Sixnet. With headquarters in York, Pennsylvania, the company has offices across the Americas, Asia-Pacific and Europe. For more information, please visit www.redlion.net. Red Lion is a Spectris company.