## MM3ZxxxT1G Series, SZMM3ZxxxT1G Series

# **Zener Voltage Regulators**

## 300 mW SOD-323 Surface Mount

This series of Zener diodes is packaged in a SOD-323 surface mount package that has a power dissipation of 300 mW. They are designed to provide voltage regulation protection and are especially attractive in situations where space is at a premium. They are well suited for applications such as cellular phones, hand held portables, and high density PC boards.

### **Specification Features:**

- Standard Zener Breakdown Voltage Range 2.4 V to 75 V
- Steady State Power Rating of 300 mW
- Small Body Outline Dimensions: 0.067" x 0.049" (1.7 mm x 1.25 mm)
- Low Body Height: 0.035" (0.9 mm)
- Package Weight: 4.507 mg/Unit
- ESD Rating of Class 3 (> 16 kV) per Human Body Model
- SZ Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These are Pb–Free Devices\*

### **Mechanical Characteristics:**

CASE: Void-free, Transfer-Molded Plastic
FINISH: All External Surfaces are Corrosion Resistant
MAXIMUM CASE TEMPERATURE FOR SOLDERING PURPOSES: 260°C for 10 Seconds
LEADS: Plated with Pb–Sn or Sn Only (Pb–Free)
POLARITY: Cathode Indicated by Polarity Band

FLAMMABILITY RATING: UL 94 V–0 MOUNTING POSITION: Any

### MAXIMUM RATINGS

Rating	Symbol	Max	Unit
Total Device Dissipation FR–4 Board, (Note 1) @ T <sub>A</sub> = 25°C Derate above 25°C	PD	300 2.4	mW mW/°C
Thermal Resistance, Junction-to-Ambient	$R_{\thetaJA}$	416	°C/W
Junction and Storage Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-65 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. FR-4 printed circuit board, single-sided copper, mounting pad 1 cm<sup>2</sup>.

\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.




### **ON Semiconductor®**

http://onsemi.com



SOD-323 CASE 477 STYLE 1



### MARKING DIAGRAM



xx = Specific Device Code

M = Date Code\*

= Pb-Free Package

(Note: Microdot may be in either location) \*Date Code orientation may vary depending upon manufacturing location.

### **ORDERING INFORMATION**

Device	Package	Shipping†
MM3ZxxxT1G	SOD-323 (Pb-Free)	3,000 / Tape & Reel
SZMM3ZxxxT1G	SOD-323 (Pb-Free)	3,000 / Tape & Reel

+For information on tape and reel specifications,

including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


#### **DEVICE MARKING INFORMATION**

See specific marking information in the device marking column of the Electrical Characteristics table on page 2 of this data sheet.

### MM3ZxxxT1G Series, SZMM3ZxxxT1G Series

### **ELECTRICAL CHARACTERISTICS**

Symbol	Parameter
VZ	Reverse Zener Voltage @ IZT
I <sub>ZT</sub>	Reverse Current
Z <sub>ZT</sub>	Maximum Zener Impedance @ IZT
I <sub>ZK</sub>	Reverse Current
Z <sub>ZK</sub>	Maximum Zener Impedance @ IZK
I <sub>R</sub>	Reverse Leakage Current @ V <sub>R</sub>
V <sub>R</sub>	Reverse Voltage
١ <sub>F</sub>	Forward Current
V <sub>F</sub>	Forward Voltage @ I <sub>F</sub>
ΘVz	Maximum Temperature Coefficient of VZ
С	Max. Capacitance $@V_R = 0$ and f = 1 MHz




**ELECTRICAL CHARACTERISTICS** ( $T_A = 25^{\circ}C$  unless otherwise noted,  $V_F = 0.9$  V Max. @  $I_F = 10$  mA for all types)

		Zer	er Volta	ige (No	te 2)	Zene	r Imped	lance	Leakage	Current	A	V <sub>z</sub>	с
						Z <sub>ZT</sub>					(m\	//k)	@ V <sub>R</sub> = 0
	Device	<u>۱</u>	Z (Volts	5)	@ I <sub>ZT</sub>	@ I <sub>ZT</sub>	Z <sub>ZK</sub>	@ I <sub>ZK</sub>	I <sub>R</sub> @ V <sub>R</sub>		@ I <sub>ZT</sub>		f = 1 MHz
Device*	Marking	Min	Nom	Мах	mA	Ω	Ω	mA	μA	Volts	Min	Max	pF
MM3Z2V4T1G	00	2.2	2.4	2.6	5	100	1000	0.5	50	1.0	-3.5	0	450
MM3Z2V7T1G	01	2.5	2.7	2.9	5	100	1000	0.5	20	1.0	-3.5	0	450
MM3Z3V0T1G	02	2.8	3.0	3.2	5	100	1000	0.5	10	1.0	-3.5	0	450
MM3Z3V3T1G	05	3.1	3.3	3.5	5	95	1000	0.5	5	1.0	-3.5	0	450
MM3Z3V6T1G	06	3.4	3.6	3.8	5	90	1000	0.5	5	1.0	-3.5	0	450
MM3Z3V9T1G	07	3.7	3.9	4.1	5	90	1000	0.5	3	1.0	-3.5	-2.5	450
MM3Z4V3T1G	08	4.0	4.3	4.6	5	90	1000	0.5	3	1.0	-3.5	0	450
MM3Z4V7T1G	09	4.4	4.7	5.0	5	80	800	0.5	3	2.0	-3.5	0.2	260
MM3Z5V1T1G	0A	4.8	5.1	5.4	5	60	500	0.5	2	2.0	-2.7	1.2	225
MM3Z5V6T1G	0C	5.2	5.6	6.0	5	40	200	0.5	1	2.0	-2.0	2.5	200
MM3Z6V2T1G	0E	5.8	6.2	6.6	5	10	100	0.5	3	4.0	0.4	3.7	185
MM3Z6V8T1G	0F	6.4	6.8	7.2	5	15	160	0.5	2	4.0	1.2	4.5	155
MM3Z7V5T1G	0G	7.0	7.5	7.9	5	15	160	0.5	1	5.0	2.5	5.3	140
MM3Z8V2T1G	0H	7.7	8.2	8.7	5	15	160	0.5	0.7	5.0	3.2	6.2	135
MM3Z9V1T1G	0K	8.5	9.1	9.6	5	15	160	0.5	0.2	7.0	3.8	7.0	130
MM3Z10VT1G	0L	9.4	10	10.6	5	20	160	0.5	0.1	8.0	4.5	8.0	130
MM3Z11VT1G	OM	10.4	11	11.6	5	20	160	0.5	0.1	8.0	5.4	9.0	130
MM3Z12VT1G	0N	11.4	12	12.7	5	25	80	0.5	0.1	8.0	6.0	10	130
MM3Z13VT1G	0P	12.4	13.25	14.1	5	30	80	0.5	0.1	8.0	7.0	11	120
MM3Z15VT1G	0T	14.3	15	15.8	5	30	80	0.5	0.05	10.5	9.2	13	110
MM3Z16VT1G	0U	15.3	16.2	17.1	5	40	80	0.5	0.05	11.2	10.4	14	105
MM3Z18VT1G	0W	16.8	18	19.1	5	45	80	0.5	0.05	12.6	12.4	16	100
MM3Z20VT1G	0Z	18.8	20	21.2	5	55	100	0.5	0.05	14.0	14.4	18	85
MM3Z22VT1G	10	20.8	22	23.3	5	55	100	0.5	0.05	15.4	16.4	20	85
MM3Z24VT1G	11	22.8	24.2	25.6	5	70	120	0.5	0.05	16.8	18.4	22	80
MM3Z27VT1G	12	25.1	27	28.9	2	80	300	0.5	0.05	18.9	21.4	25.3	70
MM3Z30VT1G	14	28	30	32	2	80	300	0.5	0.05	21.0	24.4	29.4	70
MM3Z33VT1G	18	31	33	35	2	80	300	0.5	0.05	23.2	27.4	33.4	70
MM3Z36VT1G	19	34	36	38	2	90	500	0.5	0.05	25.2	30.4	37.4	70
MM3Z39VT1G	20	37	39	41	2	130	500	0.5	0.05	27.3	33.4	41.2	45
MM3Z43VT1G	21	40	43	46	2	150	500	0.5	0.05	30.1	37.6	46.6	40
MM3Z47VT1G	1A	44	47	50	2	170	500	0.5	0.05	32.9	42.0	51.8	40
MM3Z51VT1G	1C	48	51	54	2	180	500	0.5	0.05	35.7	46.6	57.2	40
MM3Z56VT1G	1D	52	56	60	2	200	500	0.5	0.05	39.2	52.2	63.8	40
MM3Z62VT1G	2A	58	62	66	2	215	500	0.5	0.05	43.4	58.9	71.8	35
MM3Z68VT1G	1F	64	68	72	2	240	500	0.5	0.05	47.6	65.6	79.8	35
MM3Z75VT1G	1G	70	75	79	2	255	500	0.5	0.05	52.5	73.4	88.6	35

\*Includes SZ-prefix devices where applicable.
2. Zener voltage is measured with a pulse test current I<sub>Z</sub> at an ambient temperature of 25°C.

### MM3ZxxxT1G Series, SZMM3ZxxxT1G Series

### **TYPICAL CHARACTERISTICS**



### MM3ZxxxT1G Series, SZMM3ZxxxT1G Series

### **TYPICAL CHARACTERISTICS**






Figure 7. Steady State Power Derating












#### **SOLDERING FOOTPRINT\***




\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DATE 13 MAR 2007

- NOTES:
   DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
   CONTROLLING DIMENSION: MILLIMETERS.
   LEAD THICKNESS SPECIFIED PER L/F DRAWING WITH SOLDER PLATING.
   DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
   DIMENSION L IS MEASURED FROM END OF RADIUS.

	MIL	LIMETE	RS	INCHES			
DIM	MIN	NOM	MAX	MIN	NOM	MAX	
Α	0.80	0.90	1.00	0.031	0.035	0.040	
A1	0.00	0.05	0.10	0.000	0.002	0.004	
A3	0	).15 REI	-	0.006 REF			
b	0.25	0.32	0.4	0.010	0.012	0.016	
С	0.089	0.12	0.177	0.003	0.005	0.007	
D	1.60	1.70	1.80	0.062	0.066	0.070	
Е	1.15	1.25	1.35	0.045	0.049	0.053	
L	0.08			0.003			
HE	2.30	2.50	2.70	0.090	0.098	0.105	

#### GENERIC **MARKING DIAGRAM\***



\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present.

STYLE 1: PIN 1. CATHODE (POLARITY BAND) 2. ANODE STYLE 2: NO POLARITY

DOCUMENT NUMBER:	98ASB17533C	Electronic versions are uncontrolled except when accessed directly from the Document Repository Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	SOD-323		PAGE 1 OF 1			
ON Semiconductor reserves the right the suitability of its products for any pa	to make changes without further notice to an articular purpose, nor does ON Semiconducto	stries, LLC dba ON Semiconductor or its subsidiaries in the United States y products herein. ON Semiconductor makes no warranty, representation r assume any liability arising out of the application or use of any product or rcidental damages. ON Semiconductor does not convey any license under	or guarantee regarding circuit, and specifically			

SOD-323 CASE 477-02

**ISSUE H** 

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ON Semiconductor:

MM3Z10VT1 MM3Z10VT1G MM3Z11VT1 MM3Z11VT1G MM3Z12VT1 MM3Z12VT1G MM3Z13VT1
MM3Z13VT1G MM3Z15VT1 MM3Z15VT1G MM3Z16VT1 MM3Z16VT1G MM3Z18VT1 MM3Z18VT1G
MM3Z20VT1 MM3Z20VT1G MM3Z22VT1 MM3Z22VT1G MM3Z24VT1 MM3Z24VT1G MM3Z27VT1
MM3Z27VT1G MM3Z2V4T1 MM3Z2V4T1G MM3Z2V7T1 MM3Z2V7T1G MM3Z30VT1 MM3Z30VT1G
MM3Z33VT1 MM3Z33VT1G MM3Z36VT1 MM3Z36VT1G MM3Z39VT1 MM3Z39VT1G MM3Z3V0T1
MM3Z3V0T1G MM3Z3V3T1 MM3Z3V3T1G MM3Z3V6T1 MM3Z3V6T1G MM3Z3V9T1 MM3Z3V9T1G
MM3Z43VT1 MM3Z43VT1G MM3Z4V3T1 MM3Z4V3T1G MM3Z4V7T1 MM3Z4V7T1G MM3Z5V1T1
MM3Z5V1T1G MM3Z5V6T1 MM3Z5V6T1G MM3Z6V2T1 MM3Z6V2T1G MM3Z6V8T1 MM3Z6V8T1G
MM3Z7V5T1 MM3Z7V5T1G MM3Z8V2T1 MM3Z8V2T1G MM3Z9V1T1 MM3Z9V1T1G SZMM3Z10VT1G
SZMM3Z15VT1G SZMM3Z18VT1G SZMM3Z33VT1G SZMM3Z43VT1G SZMM3Z4V7T1G SZMM3Z5V1T1G
SZMM3Z5V6T1G SZMM3Z6V2T1G SZMM3Z12VT1G MM3Z33VT3G SZMM3Z7V5T1G SZMM3Z3V6T1G
MM3Z9V1T3G SZMM3Z24VT1G SZMM3Z2V4T1G SZMM3Z16VT1G SZMM3Z8V2T1G SZMM3Z4V3T1G
SZMM3Z6V8T1G SZMM3Z9V1T1G MM3Z27VT3G MM3Z51VT1G MM3Z68VT1G MM3Z62VT1G MM3Z56VT1G
SZMM3Z75VT1G SZMM3Z47VT1G SZMM3Z20VT1G SZMM3Z27VT1G SZMM3Z3V0T1G SZMM3Z3V3T1G
MM3Z75VT1G SZMM3Z36VT1G SZMM3Z13VT1G SZMM3Z68VT1G SZMM3Z22VT1G SZMM3Z11VT1G