QOU220

Mini circuit breaker, QOU, 20A, 2 pole, 120/240 VAC, 10kA





Main

| Mani | |
|-----------------------------|-------------------------------|
| Product or component type | Miniature circuit-breaker |
| Range of product | QOU |
| Circuit breaker type | Standard |
| Circuit breaker application | HACR and Switching Duty rated |

Complementary

| Complementary | | |
|--------------------------------|-----------------------------------|--|
| Line Rated Current | 20 A | |
| Electrical connection | Slotted box lugs, line side | |
| | Slotted box lugs, load side | |
| [Ue] rated operational voltage | 120/240 V AC | |
| | 120 V AC | |
| | 48 V DC | |
| Mounting mode | Unit mount | |
| AWG gauge | AWG 14AWG 2 aluminium/copper | |
| Height | 4.05 in (102.87 mm) | |
| Depth | 2.95 in (74.93 mm) | |
| Maximum Width | 1.5 in (38.10 mm) | |
| Tightening torque | 45 lbf.in (5.08 N.m) AWG 14AWG 2) | |
| | | |

Environment

| Product certifications | CSA |
|------------------------|-----------|
| | IEC |
| | UL Listed |

Ordering and shipping details

| Category | 00900 - QOU BREAKERS & SWITCH |
|-----------------------|-------------------------------|
| Discount Schedule | DE2 |
| GTIN | 00785901418689 |
| Nbr. of units in pkg. | 24 |
| Package weight(Lbs) | 0.75 lb(US) (0.34 kg) |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| PCE | |
|---------------------|--|
| 3.60 in (9.144 cm) | |
| 4.90 in (12.446 cm) | |
| 2.10 in (5.334 cm) | |
| CAR | |
| 24 | |
| - | 3.60 in (9.144 cm) 4.90 in (12.446 cm) 2.10 in (5.334 cm) CAR |

| Package 2 Weight | 18.85 lb(US) (8.55 kg) | |
|------------------|------------------------|--|
| Package 2 Height | 4.00 in (10.16 cm) | |
| Package 2 width | 13.90 in (35.306 cm) | |
| Package 2 Length | 21.00 in (53.34 cm) | |

Offer Sustainability

| Sustainable offer status | Green Premium product |
|-----------------------------|--------------------------------|
| REACh Regulation | ☑ REACh Declaration |
| REACh free of SVHC | Yes |
| EU RoHS Directive | Compliant EEU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | €Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Halogen content performance | Halogen free product |

Contractual warranty