


PRODUCT NUMBER
75915-YXXXXLF


RoHS COMPATIBLE, SEE NOTE 6
OPTIONAL LETTER.
G: HIGH TEMPERATURE BLACK PRODUCT.
H: HIGH TEMPERATURE GREY PRODUCT.
NUMBER OF POSITIONS: 02 TO 50.
PLATING CODE
3= 0.76µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
4= 2µm MIN MATTE TIN FULL PLATED

8= 0.38µm GOLD ON CONTACT AREA.
2µm MIN MATTE TIN ON TAIL.
1.27µm Ni MIN UNDERPLATING



NOTES:

- 1 - HOUSING MAT'L: THERMOPLASTIC GLASS FILLED FLAME RETARDANT PER UL 94 V-0.
LOW TEMPERATURE: COLOR BLUE.
HIGH TEMPERATURE: COLOR GREY OR BLACK.
- 2 - TERMINAL MATERIAL: PHOSPHOR BRONZE.
- 3 - 2 UP TO 4 POSITIONS PRODUCT PACKED IN PLASTIC BOX.
5 UP TO 50 POSITIONS PRODUCT PACKED IN TUBE.
- 4 - TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS
EXAMPLE: 8 POS: (N×2.54)-0.08=20.24 mm
- 5 - HE13 PRINTING ON 75915-3xx PRODUCT.
- 6 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C ±5°C SOLDER BATH TEMPERATURE FOR
5 SECONDS IN A WAVE SOLDER APPLICATION
WITH A 1.6mm MIN THICK CIRCUIT BOARD.
 - c - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 7 - PRINTING & HOLE PATTERN SEE NEXT SHEET.



mat'l. code SEE NOTE 1		surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family DUBOX
ltr	ecn no	dr	date	tolerances unless otherwise specified	title
AD	F06-0204	DLE	06.06.20	angles	BtB RECEPT. VERT SR TMT
AE	F07-0109	DLE	07.01.16	linear	
AF	F09-0030	LMU	09.03.16	±2'	scale 5:1
AG	B-19123	LMU	14.10.21	dr	FCJ
				enr	
AB	F05-0230	DLE	05.08.08	chr	dwg no 75915 sheet 1 of 2 size A3
AC	F06-0150	DLE	06.03.17	appd	
sheet	revision	AG	D		type CUSTOMER
index	sheet	1	2		Drawing

2.54 ± 0.08
NON-ACCUM. TYP

$\phi 0.75$ MINI

RECOMMENDED HOLE PATTERN



Copyright FCI

mat'l. code SEE SHEET 1				surface ISO 1302 ✓			tolerance ISO 406 ISO 1101		projection 		product family DUBOX	
ltr	ecn no	dr	date	tolerances unless otherwise specified					title BtB RECEPT. VERT SR TMT			
A	F04-0347	DLE	04.09.23	angles	linear			mm				
B	F05-0230	DLE	05.08.08					±0.3				scale N/A
C	F06-0204	DLE	06.06.20	±2'	dr		D.LEGRAND					dwg no
D	F07-0109	DLE	07.01.16	dr		D.LEGRAND		04.09.23		sheet 2 of - size		
				enr		P.NIZZI		04.09.23		75915		
				chr		D.LEGRAND		04.09.23		A4		
				appd		P.NIZZI		04.09.23		type CUSTOMER Drawing		
sheet index	revision sheet											