

Han D F Crimp Contact Au AWG 20



| | |
|--------------------|---|
| Part number | 09 15 000 6223 |
| Specification | Han D F Crimp Contact Au AWG 20 |
| HARTING eCatalogue | https://b2b.harting.com/09150006223 |

Identification

| | |
|-----------------|--------------------|
| Category | Contacts |
| Series | Han D [®] |
| Type of contact | Crimp contact |

Version

| | |
|--------|--------|
| Gender | Female |
|--------|--------|

Technical characteristics

| | |
|-------------------------|---------------------|
| Conductor cross-section | 0.5 mm ² |
| Conductor cross-section | AWG 20 |
| Operating current | ≤10 A |
| Contact resistance | ≤3 mΩ |
| Stripping length | 8 mm |

Material properties

| | |
|-----------------------------|--|
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |



Pushing Performance

Material properties

| | |
|-----------------------|------|
| REACH SVHC substances | Lead |
|-----------------------|------|

Specifications and approvals

| | |
|----------------|-------------------------|
| Specifications | EN 60664-1 IEC 61984 |
|----------------|-------------------------|

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 100 |
| Net weight | 0.7 g |
| Country of origin | Germany |
| European customs tariff number | 85366990 |
| eCl@ss | 27440204 Contact for industrial connectors |