

How true pro's measure



PRODUCTS CATALOG

STABILA Defined.

We are a German manufacturer of specialty measuring and layout tools.

Our products are the preferred choice of professionals around the world. STABILA precision measuring tools perform faster and easier allowing you to be more profitable.

The STABILA line of products are factory tested and are job site durable. Our tools are able to handle real construction site conditions all the while providing tradespeople the dependability and consistent accuracy they expect and deserve.

STABILA Accuracy.

All accuracy tolerances stated by STABILA are absolute values. STABILA products will never perform below their stated accuracy.



STABILA Warranty.

SPIRIT LEVELS

STABILA levels remain accurate indefinitely. Vials on all STABILA levels will not fog, leak, or become inaccurate. Levels with inaccurate vials are replaced. (Damaged frames void warranty.)

LASERS and TECH LEVELS

We repair, without charge, any defects due to faulty materials or workmanship for 2 years from date of purchase. 48 hours service turnaround time.

ACCESSORIES


Tape Measures, Tripods, Cases, Grade Rods, Etc. 30 day warranty against manufacturer defects from the date of purchase.

STABILA requires original proof of purchase receipt from a U.S.A./Canada dealer for warranty coverage to be effective.



Table	of	Contents:
ubic	~	contents.

Spirit Levels 4
Tech Levels 12
Special Levels 14
Laser Levels24
Laser Distance Measuring 38
Receivers, Tripods, Tapes and Rules 42



	Spirit levels					
	Туре R. 300	Туре 196	Туре 96 М	Type 196 LED	Туре 196-2 К	Type 106 T / 106 TM
	1·10+ =.	- 0	-0· -	-0	* (J) *	The Ca
Profile	Torsion-resistant 5-chamber 'R.' profile	Ultra-rigid aluminum rectangular profile reinforcing ribs	Ultra-rigid aluminum rectangular profile reinforcing ribs	Ultra-rigid aluminum rectangular profile reinforcing ribs	Ultra-rigid aluminum rectangular profile reinforcing ribs	3-chamber aluminum rectangular profile reinforcing ribs
Accuracy - top read	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"
Accuracy - bottom read	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 3/64" @ 72"	± 3/64" @ 72"
End caps	Anti-slip stopper/ Shock-absorbing/ Removable	Anti-slip stopper/ Shock-absorbing/ Removable	Anti-slip stopper/ Shock-absorbing/ Removable	Anti-slip stopper/ Shock-absorbing/ Removable	Anti-slip stopper/ Shock-absorbing/ Removable	Standard
Lengths	48", 72", 96"	16" through 96"	16" through 96"	24", 48"	16", 24", 36", 48"	6'»»10', 7'»»12'
Additional features						
Magnetic system	-	-	Recessed magnets	-	-	Type 106TM Recessed magnets
Lighting	-	-	-	2 LED Lights	-	-
Protection	-	-	-	_	Dead Blow Shields	-





STABILA levels are manufactured with German precision.

The quality built into our levels proves they will withstand the job site.

Tools need to perform on the construction site. You need to rely on your tools day in and day out. Just imagine this scenario one day on the job site: your spirit level accidentally falls from the scaffolding and takes a hard bounce. But when you retrieve it you notice its okay and just as accurate as it was the first day it was purchased. That is the STABILA quality!

STABILA spirit levels are constructed with a fixed molded vial which measures absolutely accurately even under demanding conditions – no readjustment necessary. For this reason craftsmen worldwide trust our spirit levels.

At STABILA, we offer craftsman a variety of levels specific to their trade: depending on their requirements and trade needs we have manufactured levels ranging from lightweight or rugged, short or long, and levels which were designed for a particular trade.

	Spirit levels					
	Туре 8о Т	Type 80 A / 80 AM	Туре 70 А	Measuring Stick	Torpedoes	Pocket Levels
	m () =	1. 4	0. 2	Contract of the second		
Profile	Smooth aluminum rectangular profile	Aluminum profile with reinforcing ribs	Smooth aluminum rectangular profile	Smooth aluminum rectangular profile	Die-cast aluminum	Plastic profile with aluminum housing
Accuracy - top read	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/16" @ 60"
Accuracy - bottom read	± 3/64" @ 72"	± 3/64" @ 72"	± 3/64" @ 72"	± 3/64" @ 72"	± 3/64" @ 72"	-
End caps	Anti-slip wall grips	Standard	Standard	Anti-slip wall grips	-	-
Lengths	25" »> 41", 36" »> 59"	24", 32", 58",48", 72"	24", 48"	24", 48"	10"	1 5/8" X 2 5/8"


Additional features

Magnetic system	-	Recessed magnets	-	-	25100, 25245, 25360	Rare-earth magnet
Extension	Telescopic system	-	-	-	-	-
Measure	Printed scale	-	-	Printed scales	-	-



Engineered with micrometer precision

When STABILA spirit levels are manufactured, vials, vial block holders, and measuring surfaces are adjusted precisely to each other before being permanently bonded together with synthetic resin. STABILA's meticulous production processes ensure all components are parallel and unshakably aligned to one another so that spirit levels measure accurately after many years of rugged use.



STABILA installation technology

The unique installation technology ensures long-term accuracy. In a special casting process, the components of the spirit level are firmly bonded forever. You can trust that your spirit level will maintain its accuracy for life. It remains accurate, just as it was on the first day. No readjustments, no doubts. Always accurate measurements – even under the most difficult job conditions.

- 1 Vial
- 2 Vial Block Holder

3

- High Strength Epoxy
- 4 Level Frame






STABILA vials

The vial block is made of high-quality, shatterproof and easy-to-clean acrylic glass. The exterior surfaces must be as flat as possible to prevent light refracting when reading the vial. The interior walls of the vial are precisionground and the corrosion-free reference rings are flush with the surface - this allows the vial bubble to move freely and unhindered, ensuring maximum measuring precision.



Anti-static factor: STABILA vials prevent the movement of the vial being influenced by static loading or mechanical influences.


UV protection: The fluorescent vial liquid has high resistance against UV rays. This prevents the liquid from fading. The color contrast allows for good readability in all types of light.



Optimum readability

STABILA spirit levels are extremely temperature-resistant. The bubble size and reference rings are designed to ensure optimum readability, even at high and low temperatures. This guarantees exact readings from -20°C to 50°C. The size of the vial bubble is always within the reference rings; from (a) at -20°C to (b) at 50°C."

Temperature-stable



Туре **R** 300

- STABILA's strongest, twist-resistant R-frame built for the most demanding job sites.
- Extra wide measuring surface for increased stability no tip overs.
- Three straight edges for marking and cutting.
- Continuous grip over the entire length.
- Bridge over the horizontal vial increases the strength of the frame.
- Easy to clean fender smooth finish.
- Shock absorbing endcaps protect frame when dropped.
- STABILA vial installation technology delivers long-term accuracy.

















Type R 300 - Specifications

Туре
Accuracy - top read
Accuracy - bottom read
Vial type

End caps

Special feature

nath

engui	
₁ 8"	
72"	
96"	

R 300
1/32" @ 72"
1/32" @ 72"
1 x horizontal 2 x vertical
Anti-slip end caps / Shock absorbing / Removable
Strong R-Beam frame

Part No.

STABILA

41048	
41072	
41096	





Extremely durable: Twist resistant five-chamber "R" frame. Developed for the most demanding jobs.



Continuous grip: Handrail with finger hold over the full length. Continuous bridge over the horizontal vial.



Extremely stable: Extra wide measuring surface. High level of protection from tipping over.



Removable end caps: Allows exact positioning and transferring lines tight into corners.



Precision marking: 3 accurate marking and cutting edges over the full length.

Type 196 / 96 M / 196 LED

- Strong aluminum profile with reinforcing ribs for stability and secure hold.
- End caps with an anti-slip feature for a firm grip when marking walls.
- Shock absorbing endcaps protect frame when dropped.
- Removable end caps allow exact positioning and marking right up into corners.
- Easy to clean.
- Spirit level with two precision-milled measuring surfaces. (up to 48", coated from 72")
- STABILA vial installation technology ensures long-term accuracy – suitable for measuring in normal and upside down positions.



Type 196 / 96 M / 196 LED - Specifications

Туре	Sec. 1	196		96 M		196 LED
Accuracy - top read	10 10	1/32" @ 72"	1 C	1/32" @ 72"	0	1/32" @ 72"
Accuracy - bottom read	1	1/32" @ 72"	-	1/32" @ 72"	100	1/32" @ 72"
Vial type	-	1 x horizontal		1 x horizontal	-	1 x horizontal
	- 0	2 x vertical	0	2 x vertical	-	2 x vertical
End caps	-	Anti-slip / Shock		Anti-slip / Shock	\sim	Anti-slip / Shock
		absorbing / Removable		absorbing / Removable		absorbing / Removable
Special feature	13 18	-		Rare-earth magnets	-	2 LED Lights
	3 8					
Length	B 8	Part No.		Part No.		Part No.
16"	- R S	37416		38616	0	-
24"		37424		38624		39324
32"	STAB	37432	STAB	38632	STAR	-
36"		37436	STABLA S	38636	STABILA S	-
48"	-	37448	1.000	38648	-	39340
58"	-	37459		-	\bigcirc	-
48" & 16" Set	- 8 3	37816		-	8 8	-
58" * & 32" Set	- 8 8	37832		-	8 8	-
72" *	- 8 8	37472		38672	8 8	-
78" *		37478		38678	\mathbf{O}	-
78" & 32" Set	-	37532 Jamber® Set		38532 Mag. Jamber® Set	U	-
96" *	12.	37496		38696	in the	-
			(110)		()	
	-		111		1	
	0					

* Levels \geq 58" have a continuous bridge over the horizontal vial.








Application / Additional features



Type 196 and Type 96 M: For progressive contractors who subject their tools to extremely demanding conditions and need to

measure in all positions – for example: bricklaying, carpentry, concrete, window installation, road construction, and landscaping.



Type 196 and Type 96 M: Dual material handholes for comfort and grip.



Type 96 M: Rare-earth magnet system - for extra-strong grip to metal objects. The magnets in the 78" level are positioned to grab hinge leaves in pre-hung doors.



Vials read the same in all positions





Type 196 LED: For craftsmen who often work in dark or in poor visibility conditions.



Type 196 LED: Removable battery replacement packs.


Type 196 / 196 M TECH

- The gold standard of electronic spirit levels.
- Designed for the most difficult construction site conditions.
- #1 for ADA Ramps.
- Optimal protection waterproof and dust proof in accordance with class IP 65 certification.
- The spirit level is completely washable.
- Two digital displays which can be read easily regardless of application conditions.
- The acoustic guidance allows materials to be positioned quickly without looking at the level (3 different signals).
- Digital display rotates in reverse position.
- Reference angle mode allows an angle measurement to be accepted, saved and then transferred.
- Feature lock
- Display modes: °, %, mm/m, in/ft decimal and as fraction; can choose between precision (0.05°) and rough display (0.1°) in degree mode.
- Around 150 hours of operation.
- Includes case



IP 65

TABILA LA MADE IN GERMAN





Application / Additional features



TECH 196 electronic IP65: 2 displays light up. Dust and waterproof. Easy to re-calibrate. Display reads correctly when positioned upside down.



Type 196 M TECH IP 65: Especially suitable for metal construction – allows the craftsman to work hands free

Rare-earth magnet system – for extra strong grip to metal objects.

Type 196 / 196 M TECH - Specifications

, . , .
Accuracy - top read
Accuracy - bottom read
Accuracy with electronic inclination measurement
Vial type
End Caps

Display Modules

Special feature

Length	
14"	
24"	
48"	
72"	

-	TECH 196 electronic IP 65
0	1/32"@ 72"
	1/32" @ 72"
	at o° and $90^\circ = \pm 0.05^\circ$
	from 1° to 89° = ± 0.20°
0	1 x horizontal
J	2 x vertical
- 24	Anti-slip stopper / Shock
- 21	absorbing / Removable
- 21	°, %, mm/m, in./ft. –
- 81	decimal and fraction
5	-
STA .	
BILA	Part No.
	36514 *
1000	26526 **

36524 ** 36548 ** 36572 ***

72" TECH level does not come with a case

	TECH 196 M electronic IP 65
Î	1/32" @ 72"
l	1/32" @ 72"
1	at 0° and $90^{\circ} = \pm 0.05^{\circ}$
l	from 1° to $89^{\circ} = \pm 0.20^{\circ}$
I	1 x horizontal
I	2 x vertical
I	Anti-slip stopper / Shock
l	absorbing / Removable
I	°, %, mm/m, in./ft. –
1	decimal and fraction
I	Rare earth magnets
l	
î	
	Part No.

1	-
1	36520 *
I	36540 **
	_

Without handholes


** One handhole

*** Two handholes

Туре 96-2К / 196-2 К

- Great for bricklayers.
- Strong aluminum frame with patented "Dead Blow Shields" designed to protect frame and transfer energy from trowel impacts to work surfaces.
- Precision-milled measuring surface.
- Easy to clean with water and brush.
- One vertical vial is offset towards the center of the frame, which makes this level easy to read in measuring positions.
- Reinforcing ribs for enhanced strength and secure grip while working.
- Shock absorbing end caps protect frame when dropped.





Type 96-2 K / 196-2 K - Specifications

0

STABILA DE

1110

Туре

Accuracy - top read
Accuracy - bottom read
Vial type

End caps

Special feature

16"	
24"	
36"	
48"	

96-2 K

/32" @ 72"	
/32" @ 72"	
x horizontal x vertical	
nti-slip stopper / Shoc bsorbing / Removable	k
npact protection	


Part No.

36416	
36424	
-	
-	

Application / Additional features



Type 196-2 K: Especially suitable for masonry and hardscaping



Type 196-2 K: Dual material handholes for comfort and grip



Type 196-2 K: Easy water and brush clean up

196-2 K
1/32" @ 72"
1/32" @ 72"
1 x horizontal 2 x vertical
Anti-slip / Shock absorbing / Removable
Impact protection, Handholes
-

Part No.

ð

_		
-		
- 1		
3	6436	
3	6448	



Type 80 A-2 - The Measuring Stick



- Three layout scales
- Double sided wall grips
- Uninterrupted frame
- Slope indication rings

100	1	
8	1	~
1		-
1	and a	-
88	a.	5. 1
_	1	
1	de-	Sa
5		-
	100	
-		
		the second
1	No.	- P
10-11		
A AN		

Туре	-
Accuracy - top read	-
Accuracy - bottom read	
Vial type	- 14-
End caps	- O
Special feature	EME
	ASUR
	ING
Length	SIL
24"	- *
48"	119-
	B

80 A-2
± 1/32" @ 72"
± 3/64" @ 72"
1 x horizontal 2 x vertical
Standard w/ wall grips
Printed Scales
Part No.
29124
29124
29140



Туре 8о А-2 / 8о А-2 М

• STABILA's general construction level

• Perfect for tile installers and all job site applications

Type 80 A-2 / 80 A-2 M / 70 A-2

TypeAccuracy - top readAccuracy - bottom readVial typeEnd capsSpecial feature	•	80 A-2 ± 1/32" @ 72" ± 3/64" @ 72" 1 x horizontal 2 x vertical Standard -	• 0 •	80 A-2 M ± 1/32" @ 72" ± 3/64" @ 72" 1 x horizontal 2 x vertical Standard Rare-earth magnets	• 🕕 •	70 A-2 ± 1/32" @ 72" ± 3/64" @ 72" 1 x horizontal 2 x vertical Standard -
Length 24" 48" 72" 58" & 32" Combo 48", 24", & Torpedo	STABILA S Man n Girman	Part No. 29024 29048 29072 29532 29824 ProSet	STABLA	Part No. 29224 29248 29272 - 29924 Mag. ProSet	STABILA E	Part No. 22924 22948 - - - 70 A-2 • STABILA's entry price point
	0		•		0	



TECH 700 DA

- Functions as an angle finder, a miter gauge, and a classic spirit level.
- Quickly determine and transfer angles from 0° 270°.
- Digital display lights up.
- LOCK function enables angles to be transferred.
- Two side contact edges for accurate and reliable marking.
- REF function allows users to quickly return to a previously recorded setting.
- Save measured values with the HOLD function.
- Displays the angle bisection at the touch of a button.
- Precise measuring results with an accuracy of ± 0.1°.
- Protection class IP 54.
- Includes carrying case.
- 1 digital display, 1 horizontal vial, 1 vertical vial, 2 coated measuring surfaces.

TECH 700 DA - Specifications



Application



Туре	TECH 700 DA
Accuracy - top read	± 1/32" @ 72"
Accuracy - bottom read	± 3/64" @ 72"
Accuracy with electronic inclination measurement	± 0.1°
Measuring range	from 0° to 270°
Vial type	1 x horizontal 1 x vertical
End caps	Standard
Digital mode	Degrees

Length	Part No.
18"	39018
32"	39032



TECH 700 DA: Designed for measuring and transferring angles, e.g. when installing cabinets, aligning built-ins, positioning elaborate tiles, transferring angles when cutting tiles and setting up for precise miter cuts.

Type 106 T - Plate Level®

- Extendable spirit level with strong multi-chamber aluminum frame and removable stand-offs that can reach around braces.
- Plumb vial always at eye level.
- Handholes for comfort and grip.
- Reinforcing ribs for high strength.
- Continuous bridge over horizontal vial increases frame strength.
- Plastic end caps protect the profile against impact.
- Two measuring surfaces for measuring in normal and reverse positions.
- STABILA vial technology delivers long-term accuracy.
- Scales printed on both sides of extension pole for fast set ups.





Type 106 T: Removable **1** 5/8" stand-offs reach around braces. **Simply twist on and off.**

Especially suitable for wood frame construction and reinforced concrete construction.



Type 106 TM -Magnetic Plate Level®

- Strong rare-earth magnets grab steel. Work hands-free.
- Extendable spirit level with strong 3-chamber frame.
- Plumb vial always at eye level.
- Extremely long measuring surface thanks to a unique telescope system.
- Handholes for comfort and grip.
- Reinforcing ribs for high strength.
- Continuous bridge over horizontal vial increases frame strength.
- Plastic end caps protect the profile against impact.
- Two measuring surfaces for measuring in normal and reverse positions.
- STABILA vial technology delivers long-term accuracy.
- Scales printed on both sides of extension pole for fast set ups.

Type 106 T

Туре

Accuracy - top read

Accuracy - bottom read

Vial type

End caps Special features

Length

6' - 10'	
7' - 12'	

106 T ± 1/32" @ 72" ± 1/8" @ 120" (extended) ± 3/64" @ 72" (closed) 1 x horizontal 2 x vertical Standard Telescopic system, Stand-Offs

Part No. 35610 35712

Type 106 TM

Type Accuracy - top read

Accuracy - bottom read


Vial type

End caps

Special features

Length 6' - 10' 7' - 12'

Application



Type 106 TM: Strong flush mounted rare-earth magnets grab steel. Work hands-free



106 TM ± 1/32" @ 72" ± 1/8" @ 120" (extended) ± 3/64" @ 72" (closed) 1 x horizontal 2 x vertical Standard Telescopic system, rare-earth magnets

Part No. 34610 34712

-

Type 8o T

- A strong telescopic system for extending the measuring surface enables this spirit level to adjust to various different lengths.
- A continuous marking and cutting edge along the entire length of this level allows users to measure and mark simultaneously.
- Printed scale on the top of the frame helps users determine internal dimensions and clearances.
- Prevent inadvertent adjustments and fix the level at a specific length by using the LOCK feature.
- Anti-slip grips on the back of the level allow for a firm hold on walls.
- German engineered extension mechanism ensures highly accurate measurements. Accuracy tolerances are: ± 0.5 mm/m for normal position, ± 0.75 mm/m for reverse position, and ± 1.0 mm/m when extended.















Application / Additional features



Printed scale to determine internal dimensions and clearances.



Extension LOCK system secures the set length.



Marking and cutting edge along the entire length – measure and mark simultaneously, even when extended.

Type 8o T - Specifications

Туре	80 T
Accuracy - top read	± 1/32" @ 72" ± 1/16" @ 60"(extended)
Accuracy - bottom read	± 3/64" @ 72" ± 1/16" @ 60"(extended)
Vial type	1 x horizontal 1 x vertical
End caps	Anti-slip wall grips
Special features	Telescopic system, LOCK system

Length	Part No.
25" - 41"	29441
36" – 59"	29459



Anti-slip red grips allow for a firm hold when marking on walls.

Type 81 S Die-cast Torpedoes

- Tough die-cast aluminum frame with a slender shape, providing a firm grip.
- Big, bright crystal clear vials.
- One precision-milled measuring surface.
- STABILA vial installation technology ensures long-term accuracy – suitable for measuring in normal and upside down position.

Type 81 S Torpedoes - Specifications				
Туре	81 S Torpedo	81 SM Torpedo	81 SV REM w. 45 Torpedo	81 SV REM w. 360 Torpedo
Accuracy - top read	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"	± 1/32" @ 72"
Accuracy - bottom read	± 3/64" @ 72"	± 3/64" @ 72"	± 3/64" @ 72"	± 3/64" @ 72"
Vial type	1 x horizontal 1 x vertical –	1 x horizontal 1 x vertical –	1 x horizontal 1 x vertical 1 x fixed 45° vial	1 x horizontal 1 x vertical 1 x rotating 360° vial
Special feature	-	Strong rare-earth magnet	Extra-strong rare-earth magnet	Extra-strong rare-earth magnet
Length	Part No.	Part No.	Part No.	Part No.
10"	25010 *	25100	25245	25360

* Non-magnetic

Additional features



Type 81 SV features V-groove rare earth magnets and six-ring vial for 1% and 2% slope measurements.



11111

Pocket PRO Levels


- Professional quality with square edges.
- Measures plumb and level.
- Takes up very little space and can be easily carried.
- Vials are big, bright, and easy to read.
- Designed for properly positioning interior trim, electrical boxes, switch plates, thermostats, warning signs, wall lights and appliances.

Pocket PRO Magnetic - Specifications



Туре	Pocket PRO Magnetic	
Accuracy - top read	± 1/16" @ 60"	
Vial type	1 x horizontal	
Special features	Rare-earth magnet, Belt Holster	

Length	Part No.
1 5/8" x 2 5/8"	11901
=); 0 , 1 =); 0)*-





STABILA

POCKET PRO MAGNETIC



STABILA produces laser measuring equipment for various areas of use.

- Save time
- Eliminate errors
- Reduce costs

Laser levels and laser distance measures (LDMs) are essential tools for any trade in construction due to their high level of accuracy and vast measuring ranges. LDMs are most popular among those desiring accurate, quick, and simple distance measuring. Rotation lasers are suitable for accurate leveling over great distances due to their working range of up to 1,800'.

Rotation lasers can level horizontal, level vertical, and create slopes. Alternatively, point and line lasers are often used at close ranges so marks can be made directly on visible laser lines and points.



Laser recommendations



Civil engineering and pipeline	LAR 350	LA 180 L
Laying out areas		
leveling horizontally	•	•
leveling vertically	•	•
inclination / slope	•	
Transferring heights		
leveling horizontally	•	•



Landscapers and gardeners	LAR 350	LA 180 L
Laying out paths		
leveling horizontally	•	•
inclination / slope	•	
Laying out gardens		
leveling horizontally	•	•
Positioning fences		
leveling horizontally	•	•
leveling vertically	•	•



Steel and concrete workers	LAR 350	LA 180 L
Casing and concreting		
leveling horizontally	•	•
leveling vertically	•	•
inclination / slope	•	
Earthworks		
leveling horizontally	•	•
Stair installation		
leveling horizontally	•	•
leveling vertically	•	•



Bricklayers	LAR 350	LA 180 L
Building walls		
leveling horizontally	•	•
leveling vertically	•	٠
right angle (90°)	•	•
Creating the leveling layer		
leveling horizontally	•	•
Concreting		
leveling horizontally	•	•



Carpenters	LAR 350	LA 180 L	LA-5 PG
Positioning frames			
leveling horizontally	•	٠	
leveling vertically	•	٠	
right angle (90°)	•	•	•
Roof truss construction			
leveling horizontally	•	٠	
Mounting cladding and facades			
leveling vertically	•	•	



Metal workers	LAR 350	LA 180 L	LA-5 PG
Positioning steel beams			
leveling horizontally	•	٠	
leveling vertically	•	٠	
right angle (90°)	•	٠	•
Positioning fences			
leveling horizontally	•	٠	
leveling vertically	•	٠	
Installing balconies & staircases			
leveling horizontally	•	٠	
leveling vertically	•	٠	
plumb line	•	•	•





Tilers	LAX 400	LAX 50 G	FLS 90
Laying wall tiles			
leveling horizontally	•	٠	
leveling vertically	•	٠	
Laying floor tiles			
right angle (90°)	•		•



Drywallers	LAX 400	LAX 300 G	LA-5 PG
Marking out partition walls			
right angle (90°)	•		•
Positioning partition walls			
leveling vertically	•	٠	
Suspending ceilings			
leveling horizontally	•	•	



Carpenters	LAX 400	LAX 300 G	LAX 50 G
Installing kitchens			
leveling horizontally	•	•	•
leveling vertically	•	•	•
right angle (90°)	•		
Installing stairs			
leveling horizontally	•	•	•
leveling vertically	•	•	•
plumb line	•	٠	
Installing windows			
leveling horizontally	•	•	•



Electricians	LAX 400	LAX 300 G	LAX 50 G
Installing switches and			
plug sockets			
leveling horizontally	٠	•	•
Installing cable ducts			
leveling horizontally	•	•	•
leveling vertically	•	•	•
Installing lighting equipment			
leveling horizontally	•	•	•
leveling vertically	•	•	•
plumb line	•	•	
right angle (90°)	•		



Plumbers / heating engineers	LAX 400	LAX 300 G	LAX 50 G
Installing radiators/sanitary			
fittings			
leveling horizontally	•	٠	•
Installing pipes and ducts			
leveling horizontally	•	•	•
leveling vertically	•	٠	•
Installing ventilators			
leveling horizontally	•	٠	•
leveling vertically	•	•	•
right angle (90°)	•		


Product recommendations for professionals

On construction sites there are many specific measurement jobs that need to be solved. To meet this need, STABILA has compiled a selection of products designed to suit your exact requirements.

You can find all our product recommendations at: **stabila.com**

LA 180 L Layout Station

- Establish square layouts more efficiently than ever before.
- Self-leveling motor driven multi-line laser.
- 3 vertical and 1 horizontal continuous laser lines.
- Vertical plumb points up and down.
- AUTOALIGNMENT feature enables REC 410 receiver to automatically control the fine alignment of the LA 180 L up to 120'.
- Automatic axis transfer and creation of right angles.
- Pulsed laser lines for exact height measurements with the receiver (up to 300') indoors and outdoors.
- Bright and sharp easy-to-read laser beams for fast and effective direct work on laser lines that are clearly visible at up to 60' indoors.
- Unique housing shape for positioning in corners and over edges (e. g. concrete slab) – rapid checking of right angles.
- Shock-absorbing soft grip casing.
- One man operation.
- Protection certification: IP 54




- 1) Mark reference points A and B parallel to the wall.
- 2) Position the laser on point A and the receiver on point B.
- **3)** Roughly position the laser by hand.
- **4)** Point A and B are automatically connected by pressing the button on the receiver.



LA 180 L Laser Kit -Specifications Cat #: 02180

Includes: LA180L Laser, REC410 Line RF Receiver with Bracket, Laser Glasses, 2 Magnetic Target Plates, Manual, Batteries, Hard Shell Case.



Laser class	Outpu	ıt	Laser wavelength	Self-leveling range	Leveling accuracy					Line ghtness		90° angle precision
2	< 1 m\	N	635 nm	± 5.0°	± 3	± 3/32" @ 100'		" @ 100'	± 1	/4" @ 100'		
Laser beam accuracy			asuring range of visible line	Measuring rang of set receive		Battery life		Batterie include		Protection class		
± 3/32" @ 100'			65'	328'		approx. 20 hours		4 x D 1.5	۷	IP 54		

CAUTION LASER RADIATION DO NOT STARE INTO BEAM 630 nm - 660 nm / < 1 mW CLASS II LASER PRODUCT CFR 1040.10 AND CFR 1040.11



Applications

- Metal construction Erecting metal structures in industrial building construction.
- Reinforced concrete construction – Transferring points from batter boards, marking walls on the foundation slab.
- Bricklaying Transferring points from batterboards, marking walls on the foundation slab, marking partition walls in the basement.
- Carpentry Marking and aligning wood frame walls.
- Drywall construction Transferring layouts from the foundation slab to walls and ceilings, setting up and fixing U-profiles, setting partition walls, hanging ceilings.
- Plumbing and installation work Aligning pipe clips, positioning wires, heating pipes.

AUTOALIGNMENT for automatically transferring layout lines and creating right angles





Optional accessory – batterboard and form bracket for the laser: #07410



Optional accessory – rechargeable battery: Power NiMH battery for long periods of use #07000

LAR 350 Rotation Laser

- Features dual slope, interior, exterior, horizontal, vertical, and square leveling functions.
- Fully automatic motor-driven rotation laser for horizontal and vertical applications as well as manual inclination in two planes.
- Innovative MOTION CONTROL quick, reliable and convenient laser operation by rotating the remote control.
- DUAL SLOPE working area which can be limited as required in rotation mode. The laser beam is only emitted in a defined area.
- SECTION/MASKING MODE working area which can be limited as required in rotation mode. The laser beam is only "On" in a defined area.

- LED ASSIST system for easy operation and safety in the workplace. Integrated LEDs indicate, for example, which axis is currently tilted or is being tilted.
- MANUALALIGNMENT function pivoting an axis in vertical operation.
- Patented STABILA PROTECTOR system extreme drop protection, even when the laser is dropped from a tripod at a height of up to 6'.
- Waterproof and dust proof in accordance with protection Class IP 65.
- Large working area with REC 300 Digital Receiver, up to 2,600' in diameter.



LAR 350 Rotation Laser Kit - Specifications Cat #: 05700 TR

Includes: LAR350 Laser, DeTech Receiver with Clamp, Motion Control Remote, Fixed Head Tripod, Elevation Rod, Target Plate, Laser Glasses, Manual, Batteries, Hard Shell Case.



Applications

- Bricklaying creating the leveling layer
- Reinforced concrete construction – foundations or constructing batter boards
- Metal construction aligning and positioning steel beams in industrial building construction
- Hardscaping work laying out garden areas, paths and paving
- Carpentry construction attaching siding
- Civil engineering and pipeline construction – installing pipelines



STABILA

Laser class	Output	Laser wavelength	Self-leveling range horizontal + vertical		Leveling accuracy	Working area of set receiver	CAUTION LASER RADI
2	< 1 mW	635 nm	approx. ± 5	0	± 1/8" @ 100	2,600'	CLASS II LASER PRO
Operating life accuracy		icy Batteri	es included	Prote	ection class		
approx. 8o hours		2 x D 1.5 V	′-4 x AA 1.5 V		IP 65		



Optional accessory – AE-LAR350 Li-ion rechargeable battery unit: Li-ion rechargeable battery, mains adapter, 4 country-specific interchangeable adapters #07150








STABILA DROP PROTECTION – Set it up again after a fall, switch it on, and continue working. Colored LED light assistance.





MOTION CONTROL - an intuitive remote control with a built-in motion sensor. By moving the remote control left or right, the motion sensor accelerates or decelerates the chosen laser function. Intuitively control numerous functions and settings at a measuring range of up to 60'.

LAR 200 Rotation Laser

- Fully automatic motor-driven rotation laser for horizontal applications.
- Large working area with REC 300 digital receiver, up to 1,800' in diameter.
- 600 rpm rotation speed.
- Features plumb function.
- Patented STABILA PROTECTOR system extreme drop protection, even when the laser is dropped from a tripod at a height of up to 6'.
- Can effectively operate from -10°C (14°F) to 60°C (140°F).
- Colored LED light assistance.
- Waterproof and dustproof in accordance with protection class IP 65.









STABILA DROP PROTECTION – Set it up again after a fall, switch it on, and continue working.

LAR 200 Laser Kit - Specifications Cat #: 05500 TR

Includes: LAR 200 Rotating Laser, REC 300 digital receiver with clamp, fixed head tripod, Hi/Lo elevation rod, batteries, manual, hard shell case

CAUTION LASER RADIATION
DO NOT STARE INTO BEAM < 5mW @ 633nm - 670nm
CLASS IIIa LASER PRODUCT



Laser class	Output	Laser wavelength	Self-leveling range horizontal + vertical	Horizontal leveling accuracy	Diameter receiver range	Battery life	Batteries included	Protection class
2	< 1 mW	650 nm	± 5°	± 1/8" @ 100'	1,800' / 550m	120 hours	2 x D	IP 65



LAX 50 G Cross Line Laser with Pole

- Easy to use, one button simple.
- Laser connects onto pole at any height.
- Pole extends to 9' -6". (included)
- Self-leveling cross line laser with crisp green cross lines up to 60'.
- Work quickly and directly on the fine laser lines using STABILA **Green**BEAM technology.
- Energy saving laser diodes enable a constant on operating time of up to 7 hours.
- Pendulum technology built for the job site.
- Rotating multi-purpose base for positioning the laser onto the floor or tripods (1/4" and 5/8" threads).
- Strong rare-earth magnet for securely attaching to metal.
- Protection certification: IP 54



Put the laser where you need it - mounts to the pole, not your work







Includes: LAX 50 G Laser, telescopic pole, multi-purpose base, carrying pouch



- Remodel work

- New construction
- Trim
- Wall tile
- Drywall
- Cabinets
- Wall paper

- Paint
- Wainscot panels


ADIATION NTO BEAM

- Closet systems
- Glazers
- Framing
- Ceilings

Laser class	Output	Laser wavelength	Leveling accuracy	Measuring range of visible line	Battery life constant on	Protection class	CAUTION LASER R DO NOT STARE IN 510 nm - 530 nm
2	< 1 mW	510-530 nm	± 3/16" @ 25'	100'	7 hours	IP54	CLASS II LASER 1040.10 AND C

LAX 300 G Cross Line and Plumb Points Laser

- Bright and sharp green cross lines visible up to 100' indoors.
- Intense green plumb points up and down, can be seen outdoors.
- Work quickly and directly on the laser lines using STABILA GreenBEAM technology.
- Energy saving laser diodes enable an operating time of up to 15 hours when both beams are engaged and an operating time of up to 20 hours when only one beam is engaged.
- Pendulum technology built for the job site.
- Easy to change functions with single-button.
- Features many different positioning options. The LAX 300 G can be placed directly onto the floor, mounted onto any 1/4" thread tripod, attached to any metal surfaces via its built-in V-groove magnet, and fastened to walls with its wall bracket.
- Laser rotates inside housing for built-in protection.
- Protection certification: IP 54



Optimum visibility – crisp laser lines over the working surface.



LAX 300 G Laser Kit -**Specifications** Cat #: 03185 Includes: LAX 300 G Laser, framing base (#07471),

carrying belt pouch



Laser class	Outpu	t	Laser wavelength	Self-leveling range	5	Leveling accuracy			ne htness	Laser beam accuracy (up)
2	< 1 mV	V	510-530 nm	± 4.5°		± 3/16" @	50'	± 1/8'	'@ 50'	± 3/16" @ 50'
Laser beam accuracy (down)			easuring range of visible line	Battery life (1 beam)		Batteries included	-	tection lass	VI DO	DN LASER RADIATION NOT STARE INTO BEAN 10 nm - 530 nm / < 1 mV
± 1/4" (@ 50'		100'	20 hours	3	3 x AA 1.5 V	I	P 54	CI	ASS II LASER PRODUCT



 (\mathcal{H})


LA-5P G 5-Point Layout Laser

- 5 crisp green laser dots clearly visible at up to 60' indoors.
- Plumb points up and down for transferring layout points from floor to ceiling.
- With the 90° points, two right angles are created.
- Work quickly and directly on the fine laser points using STABILA GreenBEAM technology.
- Energy saving laser diodes enable an operating time of up to 15 hours.
- Pendulum technology built for the job site.
- Easily change functions with a single button.
- Features many different positioning options. The LA-5P G can be placed directly onto the floor, mounted onto any 1/4" thread tripod, attached to any metal surfaces via its built-in V-groove magnet, and fastened to walls with its wall bracket.
- Laser rotates inside housing for built-in protection.
- Protection certification: IP 54

Rotation, line and point lasers



Optimum visibility – perfect setting of 90° angles and transferring layout points



LAX 400 Multi-line Laser

- Multi-line red laser with a 360°
- MANUALALIGNMENT: fine adjustment knob pivots the right angle left and right.
- Built-in vertical elevation height adjustment.
- The laser pivots 360° inside the housing.
- Pulsed laser lines for use with optional receiver. (#07335)
- Features many different positioning options. The LAX 400 can be placed directly onto the floor, mounted onto any 5/8" thread tripod, attached to any metal surfaces via its built-in V-groove magnet, and fastened to walls with its wall bracket.
- Protection certification: IP 54



- 360° horizontal line covers the entire room.
- Magnetic V-groove sticks to metal.



MANUALALIGNMENT fine adjustment knob adjusts the position of the 2 vertical lines




LAX 400 Laser Kit - Specifications Cat #: 03360 Includes: LAX400 Mulit-Line Laser, Target Diata, Wall Bracket, Laser,

Target Plate, Wall Bracket, Laser Glasses, Batteries, Manual, Kit Box

Optional accessory: REC 220 receiver (part #07335)




Two adjustable feet aligns laser to track





FLS 90 Floor Line Laser

- Compact housing designed to position the tool inside corners to quickly check for square.
- Patented STABILA optics deliver bright square lines that can easily be seen at up to 50' indoors.
- Can be used with Stabila REC210 audio receiver to extend usable range to 490'. (#07335)
- Unique dual purpose base allows laser to grip tile and transfer 90°.





FLS 90 Laser Kit - Specifications Cat #: 04490

Includes: Target Plate for easier daylight use,dual purpose base and belt pouch carrying case

Optional accessory: REC 220 receiver (part #07335)





On tiles position claws downward



Positions inside corners to check for square




On flat surfaces position claws upward




Laser class	0	utput		ser ength		angle cision	Measuring range of visible line
2	2 <1 mW 63		635	nm ± 3/16" @ 50'		o" @ 50'	50'
Batter life	y	Batte inclu		Prote cla			ON LASER RADIATION O NOT STARE INTO BEAM 630 nm - 660 nm / < 1 mW
20 hours		3x AA	1.5 V	IP	54	CF	CLASS II LASER PRODUCT R 1040.10 AND CFR 1040.11

Laser distance measurer: Overview of functions







- 1) Length measurement
- 2) Area measurement
- 3) Volume measurement
- 4) Continuous measurement
- 5) Chain dimensions
- 6) Pythagoras function 1: Determines a distance using two related measurements.
- **7)** Pythagoras function 2: Determines a distance using three related measurements.
- 8) Minimum tracking: Minimum continuous measurement to determine (e.g. the minimum diagonal measurement).
- **9)** Maximum Tracking: Maximum continuous measurement to determine (e.g. the maximum diagonal measurement).
- **10)** Timer: Self-timer function (e.g. for shake-free measurements on a tripod).
- **11)** Stake out distances

- Inclination measurement: Inclination sensor measures inclinations in a range of ± 180°.
- **13)** Indirect distance measurement: Allows measurement of a horizontal line that cannot be directly accessed.
- 14) Indirect height measurement: Determines a height (e.g. of a building) that does not offer a suitable reflection point.
- **15)** Measurement of inclined objects: Enables inclined distances that are not directly accessible to be measured (e.g. the slope of a roof).
- **16)** Elevation profile measurement: Determines the difference in height between a reference point and other measurement points.
- **17)** Trapezoidal measurement: Allows measurement of oblique lines that are not directly accessible.
- **18)** Triangular area measurement: Calculates the area of a triangle by measuring the sides of the triangle.

LD 520 Laser Distance Measurer

- Camera with high image resolution for long range and outdoor measuring.
- High-contrast 2.4" color display.
- Digital target feature with crosshairs and 4x zoom.
- Integrated Bluetooth® Smart 4.0 technology for transferring measurement data.
- 360° inclination sensor for flexible measurements and positioning.
- Memory function saves previous measurements.
- Comprehensive function package 18 functions (including MIN and MAX tracking, indirect distances and heights, and elevation profiles).
- Free STABILA Measures app lets you transfer measurements directly to photos or drawings.
- ISO-certified distance measurer adheres to international standard ISO 16331-1.
- Can mount to 1/4" thread tripods.
- Built-in calculator
- Protection certification: IP 54

Measure distances up to 660' away outdoors





LD 520 Laser Measurer Kit - Specifications Cat #: 06520 Includes: Belt pouch and wrist strap



The STABILA Measures app saves time when taking measurements and preparing quotes. This app features an intuitive interface and a wide range of functions. Use the STABILA Measures app to make sketches, take pictures, or draw blueprints on a mobile device and directly transfer measurements over to the app from a LD 520. This direct measurement transfer feature enables users to document and communicate more efficiently.

up to 5,000 measurements		2 x AA	IP 54	CLASS II LASER PRODUCT CFR 1040.10 AND CFR 1040.11	
Battery Life			Batteries included	Protection	CAUTION LASER RADIATION
2	< 1 mW	635 nm	± 1/16"	660'	
Laser class	Output	Laser wavelength	Accuracy	Measuring distance	



LD 250 BT Laser Distance Measurer

- Measure distances up to 165' away.
- Compact and easy-to-use laser distance measurer.
- Integrated Bluetooth[®] Smart 4.0 technology enables measurement data to be wirelessly transferred from the laser to a mobile device.
- Four measurement functions: length, area, volume, and continuous measurement mode.
- Large digits and backlit display make the LD 250 very easy to read.
- ISO-certified distance measurer adheres to international standard ISO 16331-1.
- Free STABILA Measures app lets users transfer measurements directly to an image or a sketch on a mobile device.
- The LD 250 delivers very fast measurement results, which assists users in their daily work (e.g. when calculating how much material is needed).
- Protection certification: IP 54



LD 250 BT Laser Measurer -Specifications Cat #: 06250

Laser class	Output	Laser wavelength	Accuracy	Measuring distance
2 < 1 mW 635 nm			± 3/32"	165'
	Battery	Life	Batteries included	Protection
up to r		asurements	2 X AAA	IP 54

Laser distance measurers

AUTION LASER RADIATION



	metudeu		630 nm - 660 nm / < 1 mW	
up to 5,000 measurements	2 x AAA	IP 54	CLASS II LASER PRODUCT CFR 1040.10 AND CFR 1040.11	
STREET, NY V	L S Y J	DE	XXX	It.
	- hel	and a	A A A A	
Shift		The start	And And And And	-
NO TO A				1
		5		
ALL LAND				
ALCON .	1000			1.00
	No.	7		
	15			
	fall.			
	1 1			
The second	613			
Contract of the second	B A.			
	2100			10.00



LD 220 Laser Measurer -Specifications Cat #: 06220

	Laser class	Output	Laser wavelength	Accuracy	Measuring distance
	2	< 1 mW	635 nm	± 1/8"	100'
		Battery I	_ife	Batteries included	Protection
Γ	up to 5	,ooo mea	surements	2 x AAA	IP 54

CAUTION LASER RADIATION DO NOT STARE INTO BEAM 630 nm - 660 nm / < 1 mW CLASS II LASER PRODUCT CHR 1040.10 AND CFR 1040.11

LD 220 Laser Distance Measurer

- Measure distances up to 100' away.
- The LD 220 delivers very fast measurement results, which assists users in their daily work (e.g. when calculating how much material is needed).
- Four measurement functions: length, area, volume, and continuous measurement mode.
- ISO-certified distance measurer adheres to international standard ISO 16331-1.

Expanding the working area





REC 410 RF Digital Line Receiver Part No. 07350

- AUTOALIGNMENT: REC 410 receiver uses radio frequency to control the LA 180 L Laser.
- Working leveling range of up to 300'.
- Features visual and acoustic guidance.
- Double-sided digital display for fast work.
- Dust and water proof: IP 54
- Bracket for attaching to grade rods.
- Working leveling range: 300'



REC 150 Digital Receiver Part No. 07460

- Digital receiver for rotation lasers with red diodes.
- Double-sided digital display for fast work.
- Features visual and acoustic guidance.
- Completely waterproof and dustproof protection class IP 67.
- Bracket for attaching to grade rods



REC 300 Digital Receiver Part No. 07430

- Digital receiver for rotation lasers with red diodes.
- Double-sided digital display for fast work.
- Features visual and acoustic guidance.
- Digital read-out shows exact distance from grade in imperial or metric units.
- Completely waterproof and dustproof protection class IP 67.
- Bracket for attaching to grade rods.
- Can withstand drops of up to 10'.



REC 220 Digital Line Receiver Part No. 07335

- Receiver for line lasers with red diodes.
- Display on the front and LED indicator on the side for reading from any position
- Features visual and acoustic guidance.
- Completely waterproof and dustproof protection class IP 67.
- Features imbedded magnets.
- Bracket for attaching to grade rods





Series BST-K-M lifting column construction tripod 28" - 66" Part No. 08560

- Aluminum construction tripod with lifting column exact positioning of the laser at the desired working height
- Lift system enables air-cushioned movement
- Tripod legs have spikes to insure good stability outdoors and rotatable hard rubber shoes to prevent scratches when used indoors
- Rapid locking mechanism
- 5/8" threaded screw

BM 40 tape measures



BST-S construction tripod 39" - 63" Part No. 07498

- Aluminum construction tripod
- Tripod legs have spikes to insure good stability
- Rapid locking mechanism for aligning quickly

Non-Slip Hook

- Spread stopper chain
- Carrying pouch for easy transport
- 5/8" threaded screw



Length	16'	27'	33'	5 m / 16'	8 m / 27'	10 m / 33'
Part No.	30316	30327	30333	30416	30427	30433

Scale on 2 sides

- Rocker Blade Lock
- The wide, smooth underside of the housing provides outstanding stability
- The straight rear side of the housing ensures a clean stop and allows working hands-free
- Metal belt clip

Series 600 folding rules



Туре	Description	Part No.
Masons	1/16ths - both edges - outside	80001
Oversize Brick	1/16ths - both edges - outside	80005
Modular Spacing	1/16ths - both edges - outside	80010
Engineers	1/16ths - 1/10ths - 1/100ths	80015



- Hardened steel springs and steel joints ensure durability, smoothness and exact locking
- Fully sealed rivets with abrasion protection
- Large digits for better readability

STABILA, Inc.

332 Industrial Drive P.O. Box 402 South Elgin, IL 60177-0402 Phone: 800.869.7460 In IL: 847.488.0050 Fax: 847.488.0051 E-mail: custservice@stabila.com



stabila.com

Specifications and products are subject to change without notice. STABILA is not responsible for typographical errors.