

1-1718093-1 ✓ ACTIVE


### Timer Connector System

TE Internal #: 1-1718093-1

TE Internal Description: MIXED TAB HEADER,42POS

Low & Medium Power Header

[View on TE.com >](#)



### All Low & Medium Power Header (103)

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-967281-1  
MICRO-T2/JPT GEH42P



TE Part # 963225-1  
DICHTUNG F 42P GEH




TE Part # 962920-2  
MICRO TIM STIFT 1,6

## Also in the Series | Timer Connector System



Automotive Connector Caps & Covers  
(14)



Automotive Connector Locks &  
Position Assurance(15)



Automotive Housings(215)



Automotive Terminals(135)



Connector Seals & Cavity Plugs(36)



Crimp Terminal Housings(13)



Insertion & Extraction Tools(18)



Other Automotive Connector  
Accessories(1)



PCB Headers & Receptacles(40)



Quick Disconnects(4)


## Customers Also Bought



TE Part #1-967281-1  
Timer Connector Housing




TE Part #6-1879233-5  
SMW5 47R 5%



TE Part #1623783-6  
SQM7 220R 5% (WIRE)




TE Part #1-1579007-6  
EXTRACTION TOOL



TE Part #213933-1  
CPC, STRAIN RELIEF, SIZE 17



TE Part #1564411-1  
SLIDE, TAB HSG GROUP E



TE Part #1-216604-7  
2X17P HV190FEDERLEI



TE Part #474320-E  
SMCQ 12 M AB VV 8-03 CL \* H007 137  
E005



TE Part #534183-E  
SMCQ 16 M AB VV 8-13 CL \* H007 137  
E005

## Documents

### Product Drawings

MIXED TAB HEADER,42POS

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1718093-1\\_A.2d\\_dxf.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1718093-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1718093-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications



42 POS. Coupling For JUNIOR-POWER-TIMER / MICRO-TIMER and STITCH-TAB

English

**Product Specification**

English