


FEATURES

- Low Cost
- Wide Range of Band Width
-

APPLICATIONS

- Telecommunications



© TGS CRYSTALS LTD.

SPECIFICATION FOR 450KHz *


Characteristics Part Number	Centre Frequency (KHz)	Insertion Loss (dB Max.)	Passband Ripple (dB Max.)	6dB Bandwidth (KHz)Min	50dB Bandwidth (KHz)Max	Stop band Att ±100KHz (dB)Min	Input/output Impedance (Ω)
CFM450BW	fo±2.0	4	2	±15.0	±30.0	40	1500
CFM450CW	±	4	2	±12.5	±24.0	40	1500
CFM450DW	±	4	2	±10.0	±20.0	40	1500
CFM450EW	±	6	2	±7.5	±15.0	40	1500
CFM450FW	±	4	2	±6.0	±12.5	40	2000
CFM450GW	±	6	2	±4.5	±10.0	40	2000
CFM450HW	±	6	2	±3.0	±9.0	40	2000
CFM450IW	±	6	2	±2.0	±7.5	40	2000
CFM450HTW	±	6	2	±3.0	±9.0	60	2000
CFM450ITW	±	6	2	±2.0	±7.5	60	2000

SPECIFICATION FOR 455KHz *


Characteristics Part Number	Centre Frequency (KHz)	Insertion Loss (dB Max.)	Passband Ripple (dB Max.)	6dB Bandwidth (KHz)Min	50dB Bandwidth (KHz)Max	Stop band Att ±100KHz (dB)Min	Input/output Impedance (Ω)
CFM455BW	fo±2.0	4	2	±15.0	±30.0	40	1500
CFM455CW	±	4	2	±12.5	±24.0	40	1500
CFM455DW	±	4	2	±10.0	±20.0	40	1500
CFM455EW	±	6	2	±7.5	±15.0	40	1500
CFM455FW	±	4	2	±6.0	±12.5	40	2000
CFM455GW	±	6	2	±4.5	±10.0	40	2000
CFM455HW	±	6	2	±3.0	±9.0	40	2000
CFM455IW	±	6	2	±2.0	±7.5	40	2000
CFM455HTW	±	6	2	±3.0	±9.0	60	2000
CFM455ITW	±	6	2	±2.0	±7.5	60	2000

* Specifications Subject to Change Without Notice


DIMENSIONS



TEST CIRCUIT



FREQUENCY CHARACTERISTICS



PACKAGE

- Standard package in bulk: 1000 pcs/ box, 10 box/carton

PART NUMBER GUIDE

TGS	CF	M	455	E	W
Mark	Ceramic Filter	M:Height-6.3mm	Centre Freq.	Grade	W: 5 Pin

e.g. Full P/N.: TGS CFM 455E W