

This document was generated on 03/18/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0430451427		
Status: Overview: Description:	Active verview: Micro-Fit 3.0 Connector System Product Family		
	<u>n PS-43045 (PDF)</u> n PS-43045-001 (PDF) n TS-43045-001-001 (PDF)	Product Specification TS-46235-001-001 (PDF) Packaging Specification PK-70873-0314-001 (PDF) Test Summary 430450004-TS-000 (PDF) RoHS Certificate of Compliance (PDF) Product Literature (PDF)	Series image - Reference only
Agency Certification CSA UL General Product Family Series Application Comments	Din in the second se	LR19980 E29179 PCB Headers 43045 Power, Wire-to-Board """"This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <p> If it is determined higher performance is required, please contact Molex for possible product options."""""" This Molex for possible product options.""""" This Molex for gossible product options."""""" This Molex for gossible product options."""""" This Molex for possible product options."""""" the following ratings, tested by independent agencies: a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13 b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <p><p> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <p> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""""""""</p></p></p></p></p></p>	EU ELV Not Relevant EU RoHS Compliant REACH SVHC Not Contained Per -ED/88/2018 (15 January 2019) Halogen-Free Status Low-Halogen For more information, please visit <u>Contact US</u> China ROHS ELV Not Relevant ROHS Phthalates Not Contained Search Parts in this Series 43045 Series Mates With Micro-Fit 3.0 Receptacle Housing 43025 -br>Micro-Fit 3.0 TPA Receptacle Housing 172952

Overview Product Literature Order No Product Name UPC

Micro-Fit 3.0 Connector System Product Family 987650-5984 Micro-Fit 3.0 800753834170

Physical	
Breakaway	No
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Capable	Yes
Lock to Mating Part	Yes
Mated Height	17.64mm
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.944/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.18mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	0.254µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Electrical	0.54
Current - Maximum per Contact	8.5A 600V
Voltage - Maximum	600 v
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-70873-0314-001
Product Specification	PS-43045, PS-43045-001, TS-430
· · · · · · · · · · · · · · · · · · ·	TO 40005 004 004

Sales Drawing Symbol/Footprint Data Test Summary PK-70873-0314-001 PS-43045, PS-43045-001, TS-43045-001-001, TS-46235-001-001 SD-43045-010 SYM-43045-1427 430450004-TS-000

This document was generated on 03/18/2019 PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION