
KEMET Part Number: C0805C221J5GACAUTO



SMD Auto C0G, Ceramic, 220 pF, 5%, 50 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Automotive Grade, 0805



Dimensions	
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
Т	0.78mm +/-0.10mm
S	0.75mm MIN
В	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

General Information		
Supplier:	KEMET	
Series:	SMD Auto C0G	
Style:	SMD Chip	
Description:	SMD, MLCC, Ultra-Stable, Low Loss, Automotive Grade	
Features:	Ultra-Stable, Low Loss, Automotive Grade	
RoHS:	Yes	
Termination:	Tin	
Marking:	No	
Qualifications:	AEC-Q200	
AEC-Q200:	Yes	
Miscellaneous:	Note: KEMET 50V rated parts may be operated at 63 Volts	
Chip Size:	0805	
Shelf Life:	78 Weeks	
MSL:	1	

Specifications		
Capacitance:	220 pF	
Capacitance Tolerance:	5%	
Voltage DC:	50 VDC	
Dielectric Withstanding Voltage:	125 V	
Temperature Range:	-55/+125C	
Temperature Coefficient:	COG	
Dissipation Factor:	0.10% 1MHz 25C	
Aging Rate:	0% Loss/Decade Hour	
Insulation Resistance:	100 GOhms	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

