



DCD999H2T-GB

18V XR XRP Hammer Drill Driver With 5.0Ah Powerstack Battery

Take advantage of more power using 18V XR tools with selected batteries. A unique electronic module with pack identification technology enables the tool to recognise when a compatible battery is attached and unlock even more power. The DCD999 delivers up to 42% more power when paired with a DCB546 XR FLEXVOLT 6Ah battery versus a DCB184 18V XR 5Ah battery. Engineered for speed and durability, other features include an all metal 3 speed transmission, DEWALT built brushless motor and full metal ratcheting chuck with carbide inserts.

- Uses intelligent electronics to sense what battery is in the tool and increase power & torque when paired with selected batteries
- All metal chuck for improved grip on drilling and screwdriving accessories
- Electronic Clutch with 11 position adjustable torque control for optimised precision when screwdriving
- Foot LED with delay feature for improved visibility and flashlight functionality
- Efficient intelligent trigger allowing total control over all applications
- Chuck Capacity: 1.5-13mm
- Max Drilling Capacity (Wood): 55mm

Contents

- Combi Drill
- Side Handle
- 2 x 5.0Ah Powerstack Batteries
- Multi-Voltage Charger
- T-Stack Case

BATTERY VOLTAGE	18 V
BATTERY AMPS	5.0Ah
MAX DRILLING CAPACITY – METAL	15mm
MAX DRILLING CAPACITY – MASONRY	11 Bar / 160PSI
MAX TORQUE	66/112Nm (Soft/Hard)
NO LOAD SPEED	0-500/1500/2250rpm
HAMMER BPM	38250 BPM
OUTPUT	2.3Kg

1 YEAR LIMITED WARRANTY, 3 YEAR LIMITED WARRANTY WHEN REGISTERED

We're confident of the quality of our products and we'll repair, without charge, any defects due to faulty materials or workmanship within the specified warranty.